

ALFAAB21072

## 4-Aminobutyaldehyde dimethyl acetal

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 4-氨基丁醛二甲基缩醛  
4-Aminobutyaldehyde dimethyl acetal

Cat No. : B21072  
CAS No 19060-15-2  
Molecular Formula C6 H15 N O2

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
Colorless

**Odor**  
No information available

#### Emergency Overview

Flammable liquid and vapor. Harmful if swallowed. Causes severe skin burns and eye damage. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Harmful to aquatic life with long lasting effects.

#### Classification of the substance or mixture

Flammable liquids.	Category 3
Acute Oral Toxicity	Category 4
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1
Respiratory Sensitization	Category 1
Chronic aquatic toxicity	Category 3

#### Label Elements

# SAFETY DATA SHEET

## 4-Aminobutyaldehyde dimethyl acetal

**Signal Word****Danger****Hazard Statements**

H226 - Flammable liquid and vapor  
H302 - Harmful if swallowed  
H314 - Causes severe skin burns and eye damage  
H334 - May cause allergy or asthma symptoms or breathing difficulties if inhaled  
H412 - Harmful to aquatic life with long lasting effects

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P240 - Ground and bond container and receiving equipment  
P242 - Use non-sparking tools  
P243 - Take action to prevent static discharges  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection  
P284 - In case of inadequate ventilation wear respiratory protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P310 - Immediately call a POISON CENTER or doctor  
P330 - Rinse mouth  
P331 - Do NOT induce vomiting  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Flammable liquid. Vapors may cause flash fire or explosion.

**Health Hazards**

Harmful if swallowed. Corrosive. Causes skin and eye burns. May cause allergy or asthma symptoms or breathing difficulties if inhaled.

**Environmental hazards**

Harmful to aquatic life with long lasting effects. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
1-Butanamine, 4,4-dimethoxy-	19060-15-2	<=100

**SECTION 4. FIRST AID MEASURES**

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Call a physician immediately.

**Inhalation**

If not breathing, give artificial respiration. Remove from exposure, lie down. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Call a physician immediately.

**Ingestion**

Do NOT induce vomiting. Clean mouth with water. Never give anything by mouth to an unconscious person. Call a physician immediately.

**Most important symptoms and effects**

Causes burns by all exposure routes. Difficulty in breathing. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

### SECTION 5. FIRE-FIGHTING MEASURES

**Suitable Extinguishing Media**

CO<sub>2</sub>, dry chemical, dry sand, alcohol-resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors. The product causes burns of eyes, skin and mucous membranes. Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

Do not flush into surface water or sanitary sewer system. Should not be released into the environment. See Section 12 for additional Ecological Information. Avoid release to the environment. Collect spillage.

### Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

### Storage

Keep away from heat, sparks and flame. Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

### Exposure Controls

### Engineering Measures

Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

of cuts, abrasion.  
 Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Long sleeved clothing
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Organic gases and vapours filter Type A Brown conforming to EN14387
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	Prevent product from entering drains.

### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Colorless	
<b>Physical State</b>	Liquid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	85 °C / 185 °F	
<b>Flash Point</b>	59 °C / 138.2 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		explosive air/vapour mixtures possible
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C6 H15 N O2	
<b>Molecular Weight</b>	133.19	

### SECTION 10. STABILITY AND REACTIVITY

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	No information available.
<b>Hazardous Decomposition Products</b>	None under normal use conditions.

### SECTION 11. TOXICOLOGICAL INFORMATION

#### Product Information

(a) acute toxicity;

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory	Category 1
Skin	No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available  
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; No data available

**Symptoms / effects, both acute and delayed** Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

### SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

<b>Persistence and Degradability</b>	No information available
<b>Persistence</b>	Persistence is unlikely, based on information available.
<b>Degradation in sewage treatment plant</b>	Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.
<b>Bioaccumulative Potential</b>	Bioaccumulation is unlikely
<b>Mobility in soil</b>	The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air.
<b>Endocrine Disruptor Information</b>	This product does not contain any known or suspected endocrine disruptors
<b>Persistent Organic Pollutant</b>	This product does not contain any known or suspected substance
<b>Ozone Depletion Potential</b>	This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

<b>Waste from Residues/Unused Products</b>	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.
<b>Other Information</b>	Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms. Do not let this chemical enter the environment.

### SECTION 14. TRANSPORT INFORMATION

#### Road and Rail Transport

<b>UN-No</b>	UN2734
<b>Proper Shipping Name</b>	AMINES, LIQUID, CORROSIVE, FLAMMABLE, N.O.S.
<b>Technical Shipping Name</b>	(4-Aminobutyraldehyde dimethyl acetal)
<b>Hazard Class</b>	8
<b>Subsidiary Hazard Class</b>	3
<b>Packing Group</b>	II

#### IMDG/IMO

<b>UN-No</b>	UN2734
<b>Proper Shipping Name</b>	AMINES, LIQUID, CORROSIVE, FLAMMABLE, N.O.S.
<b>Technical Shipping Name</b>	(4-Aminobutyraldehyde dimethyl acetal)
<b>Hazard Class</b>	8
<b>Subsidiary Hazard Class</b>	3
<b>Packing Group</b>	II

#### IATA

<b>UN-No</b>	UN2734
<b>Proper Shipping Name</b>	AMINES, LIQUID, CORROSIVE, FLAMMABLE, N.O.S.*
<b>Technical Shipping Name</b>	(4-Aminobutyraldehyde dimethyl acetal)
<b>Hazard Class</b>	8

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

**Subsidiary Hazard Class** 3  
**Packing Group** II

**Special Precautions for User** No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
1-Butanamine, 4,4-dimethoxy-	-	-	X	-	-	X	-	-	-	-	-	-

#### National Regulations

### SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 03-May-2024  
**Revision Summary** New emergency telephone response service provider.

#### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

#### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

# SAFETY DATA SHEET

## 4-Aminobutyraldehyde dimethyl acetal

---

**BCF** - Bioconcentration factor**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**