

ALFAAB21842

## Methyl 4-morpholineacetate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 4-吗啉基乙酸甲酯  
Methyl 4-morpholineacetate

Cat No. : B21842  
CAS No 35855-10-8  
Molecular Formula C7 H13 N O3

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State  
Liquid

Appearance  
Light yellow

Odor  
No information available

**Emergency Overview**  
Causes severe skin burns and eye damage.

#### Classification of the substance or mixture

Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

#### Label Elements



Signal Word

**Danger**

#### Hazard Statements

H314 - Causes severe skin burns and eye damage

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Corrosive. Causes skin and eye burns.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Methyl morpholinoacetate	35855-10-8	> 99

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Immediate medical attention is required.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Immediate medical attention is required.

**Ingestion**

Do NOT induce vomiting. Call a physician immediately.

**Most important symptoms and effects**

Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Do not breathe mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not ingest. If swallowed then seek immediate medical assistance. Handle product only in closed system or provide appropriate exhaust ventilation.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

## Methyl 4-morpholineacetate

## Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.  
(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Organic gases and vapours filter Type A Brown conforming to EN14387

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Light yellow	
<b>Physical State</b>	Liquid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	No information available	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	5.49	(Air = 1.0)
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	Not applicable	Liquid

**SAFETY DATA SHEET****Methyl 4-morpholineacetate**

<b>Water Solubility</b>	No information available
<b>Solubility in other solvents</b>	No information available
<b>Partition Coefficient (n-octanol/water)</b>	
<b>Autoignition Temperature</b>	No data available
<b>Decomposition Temperature</b>	No data available
<b>Viscosity</b>	No data available
<b>Explosive Properties</b>	No information available
<b>Oxidizing Properties</b>	No information available

<b>Molecular Formula</b>	C7 H13 N O3
<b>Molecular Weight</b>	159.19

**SECTION 10. STABILITY AND REACTIVITY**

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Incompatible products.
<b>Materials to avoid</b>	Strong oxidizing agents.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).**SECTION 11. TOXICOLOGICAL INFORMATION**

<b>Product Information</b>	No acute toxicity information is available for this product
<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	Category 1 B
<b>(c) serious eye damage/irritation;</b>	Category 1
<b>(d) respiratory or skin sensitization;</b>	
<b>Respiratory</b>	No data available
<b>Skin</b>	No data available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available
<b>Target Organs</b>	No information available.

## Methyl 4-morpholineacetate

(j) aspiration hazard; No data available

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**SECTION 12. ECOLOGICAL INFORMATION**

**Ecotoxicity effects** Do not empty into drains.

**Persistence and Degradability** No information available

**Bioaccumulative Potential** No information available

**Mobility in soil** No information available

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN2735  
**Proper Shipping Name** AMINES, LIQUID, CORROSIVE, N.O.S.  
**Hazard Class** 8  
**Packing Group** III

**IMDG/IMO**

**UN-No** UN2735  
**Proper Shipping Name** AMINES, LIQUID, CORROSIVE, N.O.S.  
**Hazard Class** 8  
**Packing Group** III

**IATA**

**UN-No** UN2735  
**Proper Shipping Name** AMINES, LIQUID, CORROSIVE, N.O.S.

## Methyl 4-morpholineacetate

**Hazard Class** 8  
**Packing Group** III

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

## Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**