

ALFAAB22578

## 3,4,5-Trifluorobenzyl bromide

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 3,4,5-三氟苄基溴  
3,4,5-Trifluorobenzyl bromide

Cat No. : B22578  
CAS No 220141-72-0  
Molecular Formula C7 H4 BrF3

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State  
Liquid

Appearance  
No information available

Odor  
No information available

**Emergency Overview**  
Combustible liquid. Causes severe skin burns and eye damage.

#### Classification of the substance or mixture

Flammable liquids.	Category 4
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

#### Label Elements



Signal Word

**Danger**

Hazard Statements

## 3,4,5-Trifluorobenzyl bromide

H227 - Combustible liquid

H314 - Causes severe skin burns and eye damage

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

P264 - Wash face, hands and any exposed skin thoroughly after handling

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Combustible material.

**Health Hazards**

Corrosive. Causes skin and eye burns.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
3,4,5-Trifluorobenzyl bromide	220141-72-0	<=100

**SECTION 4. FIRST AID MEASURES****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Call a physician immediately.

**Inhalation**

If not breathing, give artificial respiration. Remove from exposure, lie down. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Call a physician immediately.

**Ingestion**

Do NOT induce vomiting. Clean mouth with water. Never give anything by mouth to an unconscious person. Call a physician immediately.

**Most important symptoms and effects**

Causes burns by all exposure routes. Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness,

**3,4,5-Trifluorobenzyl bromide**

nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

CO<sub>2</sub>, dry chemical, dry sand, alcohol-resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors. The product causes burns of eyes, skin and mucous membranes. Combustible material. Containers may explode when heated.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition.

**Storage**

Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks and flame.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

## 3,4,5-Trifluorobenzyl bromide

## Control Parameters

## Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

## Exposure Controls

## Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

## Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Organic gases and vapours filter Type A Brown conforming to EN14387

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

## Appearance

**Physical State** Liquid

## SAFETY DATA SHEET

## 3,4,5-Trifluorobenzyl bromide

Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	44 - 46 °C / 111.2 - 114.8 °F	@ 1mmHg
Flash Point	65 °C / 149 °F	<b>Method -</b> No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	1.689 g/cm3	@ 20 °C
Bulk Density	Not applicable	Liquid
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C7 H4 BrF3	
Molecular Weight	225.01	

## SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition.
Materials to avoid	Strong bases.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Hydrogen fluoride. Hydrogen bromide.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

(a) acute toxicity;	
(b) skin corrosion/irritation;	Category 1 B
(c) serious eye damage/irritation;	Category 1
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available

## 3,4,5-Trifluorobenzyl bromide

(f) carcinogenicity;	No data available There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	No data available
Symptoms / effects, both acute and delayed	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

## SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
Persistence and Degradability	No information available
Bioaccumulative Potential	No information available
Mobility in soil	No information available
Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant	This product does not contain any known or suspected substance
Ozone Depletion Potential	This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

## SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN3265
Proper Shipping Name	Corrosive liquid, acidic, organic, n.o.s.

## SAFETY DATA SHEET

## 3,4,5-Trifluorobenzyl bromide

**Technical Shipping Name** (3,4,5-Trifluorobenzyl bromide)  
**Hazard Class** 8  
**Packing Group** II

IMDG/IMO

**UN-No** UN3265  
**Proper Shipping Name** Corrosive liquid, acidic, organic, n.o.s.  
**Technical Shipping Name** (3,4,5-Trifluorobenzyl bromide)  
**Hazard Class** 8  
**Packing Group** II

IATA

**UN-No** UN3265  
**Proper Shipping Name** Corrosive liquid, acidic, organic, n.o.s.  
**Technical Shipping Name** (3,4,5-Trifluorobenzyl bromide)  
**Hazard Class** 8  
**Packing Group** II

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
3,4,5-Trifluorobenzyl bromide	-	-	X	-	-	-	-	-	-	-	-	-

**National Regulations**

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 04-May-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

## 3,4,5-Trifluorobenzyl bromide

---

**CAS** - Chemical Abstracts Service**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances**PICCS** - Philippines Inventory of Chemicals and Chemical Substances**IECSC** - Chinese Inventory of Existing Chemical Substances**KECL** - Korean Existing and Evaluated Chemical Substances**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List**ENCS** - Japanese Existing and New Chemical Substances**AICS** - Australian Inventory of Chemical Substances**NZIoC** - New Zealand Inventory of Chemicals**WEL** - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**