

ALFAAB22871

1,4-Diisopropylbenzene

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	1,4-二异丙基苯, 99% 1,4-Diisopropylbenzene
Cat No. :	B22871
Synonyms	Benzene, 1,4,Bis(1-Methylethyl)-(9CI)
CAS No	100-18-5
Molecular Formula	C12 H18
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Liquid	Appearance Colorless	Odor Odorless
Emergency Overview Combustible liquid. Causes skin irritation.		

Classification of the substance or mixture

Flammable liquids.	Category 4
Skin Corrosion/Irritation	Category 2

Label Elements



Signal Word

Warning

Hazard Statements

1,4-Diisopropylbenzene

H227 - Combustible liquid
H315 - Causes skin irritation

Precautionary Statements**Prevention**

P271 - Use only outdoors or in a well-ventilated area
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a POISON CENTER or doctor if you feel unwell
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material.

Health Hazards

Causes skin irritation.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product is insoluble and floats on water. The product evaporates slowly.

Other Hazards

May form explosive peroxides on prolonged storage. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Benzene, 1,4-bis(1-methylethyl)-	100-18-5	>95

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If breathing is difficult, give oxygen. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SAFETY DATA SHEET

1,4-Diisopropylbenzene

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Combustible material. Containers may explode when heated.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Should not be released into the environment.

Methods for Containment and Clean Up

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Ensure adequate ventilation. Keep away from open flames, hot surfaces and sources of ignition. Handle under an inert atmosphere.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Keep containers tightly closed in a dry, cool and well-ventilated place. May form explosive peroxides. Containers should be dated when opened and tested periodically for the presence of peroxides. Should crystals form in a peroxidizable liquid, peroxidation may have occurred and the product should be considered extremely dangerous. In this instance, the container should only be opened remotely by professionals.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

1,4-Diisopropylbenzene

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

Exposure Controls

Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Organic gases and vapours filter Type A Brown conforming to EN14387

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance Colorless
Physical State Liquid

1,4-Diisopropylbenzene

Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	-17 °C / 1.4 °F	
Softening Point	No data available	
Boiling Point/Range	203 °C / 397 °F	@ 760 mmHg
Flash Point	76 °C / 168 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	0.25 mmHg @ 20 °C	
Vapor Density	5.6	(Air = 1.0)
Specific Gravity / Density	0.86	
Bulk Density	Not applicable	Liquid
Water Solubility	Insoluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Benzene, 1,4-bis(1-methylethyl)-	5.23	
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C12 H18	
Molecular Weight	162.27	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	Incompatible products. Keep away from open flames, hot surfaces and sources of ignition.
Materials to avoid	Strong oxidizing agents. Oxidizing agent.
Hazardous Decomposition Products	Thermal decomposition can lead to release of irritating gases and vapors. Carbon monoxide (CO). Carbon dioxide (CO ₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Benzene, 1,4-bis(1-methylethyl)-	LD50 > 3200 mg/kg (Rat)		

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

1,4-Diisopropylbenzene

Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	No data available
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.	
Persistence and Degradability		
Persistence	Insoluble in water, May persist, based on information available.	
Bioaccumulative Potential	May have some potential to bioaccumulate	
Component	log Pow	Bioconcentration factor (BCF)
Benzene, 1,4-bis(1-methylethyl)-	5.23	No data available
Mobility in soil	Spillage unlikely to penetrate soil The product is insoluble and floats on water The product evaporates slowly Is not likely mobile in the environment due its low water solubility Spillage unlikely to penetrate soil	
Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors	
Persistent Organic Pollutant	This product does not contain any known or suspected substance	
Ozone Depletion Potential	This product does not contain any known or suspected substance	

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.

SAFETY DATA SHEET**1,4-Diisopropylbenzene****Other Information**

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

Not Regulated

IMDG/IMO

Not regulated

IATA

Not regulated

Special Precautions for User

No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Benzene, 1,4-bis(1-methylethyl)-	-	-	X	X	202-826-9	X	X	-	X	X	-	-

National Regulations**SECTION 16. OTHER INFORMATION****Prepared By**

Health, Safety and Environmental Department

Creation Date

16-Jul-1996

Revision Date

22-Apr-2024

Revision Summary

New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

PICCS - Philippines Inventory of Chemicals and Chemical Substances

ENCS - Japanese Existing and New Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

AICS - Australian Inventory of Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

1,4-Diisopropylbenzene

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet