

ALFAAB22341

## (S)-(-)-Propylene oxide

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:** (S)-(-)-环氧丙烷, 99%  
**Product Description:** (S)-(-)-Propylene oxide

**Cat No. :** B22341  
**Synonyms** (S)-(-)-1,2-Epoxypropane  
**CAS No** 16088-62-3  
**Molecular Formula** C3 H6 O

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State	Appearance	Odor
Liquid	Colorless	aromatic
<b>Emergency Overview</b> Highly flammable liquid and vapor. Extremely flammable liquid and vapor. Harmful if swallowed. Toxic in contact with skin. Causes serious eye irritation. Toxic if inhaled. May cause respiratory irritation. May cause genetic defects. May cause cancer.		

#### Classification of the substance or mixture

Flammable liquids.	Category 1
Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 3
Acute Inhalation Toxicity - Vapors	Category 3
Serious Eye Damage/Eye Irritation	Category 2
Germ Cell Mutagenicity	Category 1B
Carcinogenicity	Category 1B
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements

**Signal Word****Danger****Hazard Statements**

H224 - Extremely flammable liquid and vapor  
H302 - Harmful if swallowed  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation  
H340 - May cause genetic defects  
H350 - May cause cancer  
H311 + H331 - Toxic in contact with skin or if inhaled

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use  
P202 - Do not handle until all safety precautions have been read and understood  
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P240 - Ground and bond container and receiving equipment  
P241 - Use explosion-proof electrical/ ventilating/ lighting equipment  
P242 - Use non-sparking tools  
P243 - Take action to prevent static discharges  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear eye protection/ face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P311 - Call a POISON CENTER or doctor  
P330 - Rinse mouth  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed  
P405 - Store locked up

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Highly flammable. Vapors may cause flash fire or explosion. Extremely flammable.

**Health Hazards**

Harmful if swallowed. Toxic in contact with skin. Causes serious eye irritation. Toxic if inhaled. May cause respiratory irritation. May cause genetic defects. May cause cancer.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

**SAFETY DATA SHEET****(S)-(-)-Propylene oxide**

Component	CAS No	Weight %
(S)-1,2-Epoxypropane	16088-62-3	>95

**SECTION 4. FIRST AID MEASURES****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately.

**Most important symptoms and effects**

. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically. Symptoms may be delayed.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Extremely flammable. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Should not be released into the environment.

**Methods for Containment and Clean Up**

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Do not get in eyes, on skin, or on clothing. Wear personal protective equipment/face protection. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

**Storage**

Keep away from heat, sparks and flame. Flammables area. Keep container tightly closed in a dry and well-ventilated place.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection**

Long sleeved clothing

## (S)-(-)-Propylene oxide

<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> low boiling organic solvent Type AX Brown conforming to EN371
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Colorless	
<b>Physical State</b>	Liquid	
<b>Odor</b>	aromatic	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	35 °C / 95 °F	
<b>Flash Point</b>	-37 °C / -34.6 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 2 Vol% <b>Upper</b> 22 Vol%	
<b>Vapor Pressure</b>	585 hPa @ 20 °C	
<b>Vapor Density</b>	2.0 (Air = 1.0)	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.820	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	40g/100ml (20°C)	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
(S)-1,2-Epoxypropane	0.085	
<b>Autoignition Temperature</b>	420 °C / 788 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C3 H6 O	
<b>Molecular Weight</b>	58.08	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
------------------	---------------------------------

## (S)-(-)-Propylene oxide

<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization may occur.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition. Excess heat. Incompatible products.
<b>Materials to avoid</b>	Acids. Bases. Metals. copper.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

**SECTION 11. TOXICOLOGICAL INFORMATION****Product Information**

(a) acute toxicity;

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;

Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; Category 1B

May cause heritable genetic damage

(f) carcinogenicity; Category 1B

May cause cancer

(g) reproductive toxicity; No data available

(h) STOT-single exposure; Category 3

Results / Target organs	Respiratory system
-------------------------	--------------------

(i) STOT-repeated exposure; No data available

Target Organs	No information available.
---------------	---------------------------

(j) aspiration hazard; No data available

**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

**SECTION 12. ECOLOGICAL INFORMATION**

<b>Ecotoxicity effects</b>	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
----------------------------	---

**Persistence and Degradability**

**SAFETY DATA SHEET****(S)-(-)-Propylene oxide****Persistence**

Persistence is unlikely, based on information available.

**Bioaccumulative Potential**

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
(S)-1,2-Epoxypropane	0.085	No data available

**Mobility in soil**

The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air.

**Endocrine Disruptor Information**  
**Persistent Organic Pollutant**  
**Ozone Depletion Potential**This product does not contain any known or suspected endocrine disruptors.  
This product does not contain any known or suspected substance.  
This product does not contain any known or suspected substance.**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information**

Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

<b>UN-No</b>	UN1280
<b>Proper Shipping Name</b>	PROPYLENE OXIDE
<b>Hazard Class</b>	3
<b>Packing Group</b>	I

**IMDG/IMO**

<b>UN-No</b>	UN1280
<b>Proper Shipping Name</b>	PROPYLENE OXIDE
<b>Hazard Class</b>	3
<b>Packing Group</b>	I

**IATA**

<b>UN-No</b>	UN1280
<b>Proper Shipping Name</b>	PROPYLENE OXIDE
<b>Hazard Class</b>	3
<b>Packing Group</b>	I

**Special Precautions for User**

No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

**SAFETY DATA SHEET****(S)-(-)-Propylene oxide**

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
(S)-1,2-Epoxypropane	-	-	X	-	240-241-0	-	-	X	-		X	-

**National Regulations****SECTION 16. OTHER INFORMATION**

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 25-Oct-2017  
**Revision Date** 22-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadviser - LOLI, Merck index, RTECS



**SAFETY DATA SHEET****(S)-(-)-Propylene oxide**

---

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**