

ALFAAB22584

## 5-Methoxy-2-methylbenzothiazole

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 5-甲氧基-2-甲基苯噻唑  
5-Methoxy-2-methylbenzothiazole

Cat No. : B22584  
CAS No 2941-69-7  
Molecular Formula C9 H9 N O S

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State  
Solid

Appearance  
Light brown

Odor  
Rotten-egg like

#### Emergency Overview

The product contains no substances which at their given concentration are considered to be hazardous to health.

#### Classification of the substance or mixture

Based on available data, the classification criteria are not met

#### Label Elements

None required

#### Physical and Chemical Hazards

None identified.

#### Health Hazards

The product contains no substances which at their given concentration are considered to be hazardous to health.

#### Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Benzothiazole, 5-methoxy-2-methyl-	2941-69-7	98

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention. Take off contaminated clothing and shoes immediately.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Immediate medical attention is required.

**Ingestion**

Never give anything by mouth to an unconscious person. Drink plenty of water. Call a physician immediately. If possible drink milk afterwards.

**Most important symptoms and effects**

No information available.

**Self-Protection of the First Aider**

No special precautions required.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Wash thoroughly after handling.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep refrigerated.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

None under normal use conditions.

**Personal protective equipment**

<b>Eye Protection</b>	Wear safety glasses with side shields (or goggles) (European standard - EN 166)
<b>Hand Protection</b>	Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Wear appropriate protective gloves and clothing to prevent skin exposure
---------------------------------	--

<b>Respiratory Protection</b>	No protective equipment is needed under normal use conditions.
-------------------------------	--

<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Particle filter
----------------------------------	--

Small scale/Laboratory use      Maintain adequate ventilation

Hygiene Measures      Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls      No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Light brown	
Physical State	Solid	
Odor	Rotten-egg like	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	34 - 38 °C / 93.2 - 100.4 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C9 H9 N O S	
Molecular Weight	179.24	

## SECTION 10. STABILITY AND REACTIVITY

Stability      Stable under normal conditions.

Hazardous Reactions      No information available.  
Hazardous Polymerization      No information available.

Conditions to Avoid      Incompatible products.

Materials to avoid      Strong oxidizing agents.

Hazardous Decomposition Products      Thermal decomposition can lead to release of irritating gases and vapors.

## SECTION 11. TOXICOLOGICAL INFORMATION

Product Information      No acute toxicity information is available for this product

(a) acute toxicity;

**SAFETY DATA SHEET**  
**5-Methoxy-2-methylbenzothiazole**

<b>(b) skin corrosion/irritation;</b>	No data available
<b>(c) serious eye damage/irritation;</b>	No data available
<b>(d) respiratory or skin sensitization;</b>	
Respiratory	No data available
Skin	No data available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available
Target Organs	No information available.
<b>(j) aspiration hazard;</b>	Not applicable
	Solid
<b>Other Adverse Effects</b>	The toxicological properties have not been fully investigated.
<b>Symptoms / effects,both acute and delayed</b>	No information available

**SECTION 12. ECOLOGICAL INFORMATION**

<b>Ecotoxicity effects</b>	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
<b>Persistence and Degradability</b>	No information available
<b>Bioaccumulative Potential</b>	No information available
<b>Mobility in soil</b>	No information available
<b>Endocrine Disruptor Information</b>	This product does not contain any known or suspected endocrine disruptors
<b>Persistent Organic Pollutant</b>	This product does not contain any known or suspected substance
<b>Ozone Depletion Potential</b>	This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

<b>Waste from Residues/Unused</b>	Chemical waste generators must determine whether a discarded chemical is classified as a
-----------------------------------	--

**SAFETY DATA SHEET****5-Methoxy-2-methylbenzothiazole**

<b>Products</b>	hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.
<b>Contaminated Packaging</b>	Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.
<b>Other Information</b>	Waste codes should be assigned by the user based on the application for which the product was used.

**SECTION 14. TRANSPORT INFORMATION**

<b>Road and Rail Transport</b>	Not Regulated
<b>IMDG/IMO</b>	Not regulated
<b>IATA</b>	Not regulated
<b>Special Precautions for User</b>	No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Benzothiazole, 5-methoxy-2-methyl-	-	-	X	X	220-929-7	X	-	-	-	X	-	-

**National Regulations****SECTION 16. OTHER INFORMATION**

<b>Prepared By</b>	Health, Safety and Environmental Department
<b>Revision Date</b>	22-Apr-2024
<b>Revision Summary</b>	New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

**Legend****CAS** - Chemical Abstracts Service**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

## 5-Methoxy-2-methylbenzothiazole

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances  
**IECSC** - Chinese Inventory of Existing Chemical Substances  
**KECL** - Korean Existing and Evaluated Chemical Substances

**ENCS** - Japanese Existing and New Chemical Substances  
**AICS** - Australian Inventory of Chemical Substances  
**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit  
**ACGIH** - American Conference of Governmental Industrial Hygienists  
**DNEL** - Derived No Effect Level  
**RPE** - Respiratory Protective Equipment  
**LC50** - Lethal Concentration 50%  
**NOEC** - No Observed Effect Concentration  
**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average  
**IARC** - International Agency for Research on Cancer  
**PNEC** - Predicted No Effect Concentration  
**LD50** - Lethal Dose 50%  
**EC50** - Effective Concentration 50%  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association  
**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road  
**OECD** - Organisation for Economic Co-operation and Development  
**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code  
**MARPOL** - International Convention for the Prevention of Pollution from Ships  
**ATE** - Acute Toxicity Estimate  
**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>  
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**