

ALFAAB23028

## Hexamethylcyclotrisiloxane

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:**  
**Product Description:** 六甲基环三硅氧烷  
Hexamethylcyclotrisiloxane

**Cat No. :** B23028  
**CAS No** 541-05-9  
**Molecular Formula** C<sub>6</sub> H<sub>18</sub> O<sub>3</sub> Si<sub>3</sub>

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
White

**Odor**  
No information available

**Emergency Overview**  
Flammable liquid and vapor. Flammable solid.

#### Classification of the substance or mixture

Flammable liquids. Flammable solids.

Category 3 Category 1

#### Label Elements



**Signal Word**

**Danger**

#### Hazard Statements

H226 - Flammable liquid and vapor

H228 - Flammable solid

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

P240 - Ground and bond container and receiving equipment

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Flammable liquid. Vapors may cause flash fire or explosion. Combustible material.

**Health Hazards**

The product contains no substances which at their given concentration are considered to be hazardous to health.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment. Decomposes in contact with water.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Cyclotrisiloxane, hexamethyl-	541-05-9	> 95

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air.

**Ingestion**

Clean mouth with water. Get medical attention.

**Most important symptoms and effects**

No information available.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Flammable. Combustible material.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment. Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Do not breathe dust. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Flammables area.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection**

Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection**

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use**

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Recommended Filter type:** Particulates filter conforming to EN 143**Small scale/Laboratory use**

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

**Recommended half mask:-** Particle filtering: EN149:2001

When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls**

No information available.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES****Appearance**  
**Physical State**White  
Solid**Odor**

No information available

**Odor Threshold**

No data available

**pH**

Not applicable

**Melting Point/Range**

63 - 67 °C / 145.4 - 152.6 °F

**Softening Point**

No data available

**Boiling Point/Range**

134 °C / 273.2 °F

@ 760 mmHg

**Flash Point**

35 °C / 95 °F

**Method -** No information available**Evaporation Rate**

Not applicable

Solid

**Flammability (solid,gas)**

No information available

**Explosion Limits**

No data available

**Vapor Pressure**

No data available

**Vapor Density**

Not applicable

Solid

**Specific Gravity / Density**

No data available

**Bulk Density**

No data available

**Water Solubility**

Decomposes in contact with water

**Solubility in other solvents**

No information available

**Partition Coefficient (n-octanol/water)****Autoignition Temperature**

No data available

**Decomposition Temperature**

No data available

**SAFETY DATA SHEET****Hexamethylcyclotrisiloxane**

<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	

<b>Molecular Formula</b>	C6 H18 O3 Si3
<b>Molecular Weight</b>	222.47

**SECTION 10. STABILITY AND REACTIVITY**

<b>Stability</b>	Stable under recommended storage conditions.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition. Incompatible products. Exposure to moist air or water.
<b>Materials to avoid</b>	Strong oxidizing agents. Strong acids.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Silicon dioxide.

**SECTION 11. TOXICOLOGICAL INFORMATION**

<b>Product Information</b>	No acute toxicity information is available for this product
<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	No data available
<b>(c) serious eye damage/irritation;</b>	No data available
<b>(d) respiratory or skin sensitization;</b>	
<b>Respiratory</b>	No data available
<b>Skin</b>	No data available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available
<b>Target Organs</b>	No information available.
<b>(j) aspiration hazard;</b>	Not applicable
	Solid

**SAFETY DATA SHEET****Hexamethylcyclotrisiloxane****Other Adverse Effects** The toxicological properties have not been fully investigated.**Symptoms / effects, both acute and delayed** No information available**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects** Reacts with water so no ecotoxicity data for the substance is available.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Cyclotrisiloxane, hexamethyl-	LC50: > 1.6 mg/L, 96h flow-through (Oncorhynchus mykiss)			

**Persistence and Degradability** No information available  
**Persistence** No information available, Persistence is unlikely, based on information available.  
**Degradability** Decomposes in contact with water.  
**Degradation in sewage treatment plant** No information available. Decomposes in contact with water.

**Bioaccumulative Potential** Product does not bioaccumulate due to reaction with water**Mobility in soil** Decomposes in contact with water Is not likely mobile in the environment

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations.**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN1325  
**Proper Shipping Name** Flammable solid, organic, n.o.s.  
**Technical Shipping Name** Cyclotrisiloxane, hexamethyl-  
**Hazard Class** 4.1  
**Packing Group** III

**IMDG/IMO**

**UN-No** UN1325  
**Proper Shipping Name** Flammable solid, organic, n.o.s.

**SAFETY DATA SHEET****Hexamethylcyclotrisiloxane**

**Technical Shipping Name** Cyclotrisiloxane, hexamethyl-  
**Hazard Class** 4.1  
**Packing Group** III

**IATA**

**UN-No** UN1325  
**Proper Shipping Name** Flammable solid, organic, n.o.s.  
**Technical Shipping Name** Cyclotrisiloxane, hexamethyl-  
**Hazard Class** 4.1  
**Packing Group** III

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Cyclotrisiloxane, hexamethyl-	-	-	X	X	208-765-4	X	X	X	X	X	X	KE-18604

**National Regulations****SECTION 16. OTHER INFORMATION**

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 26-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

## Hexamethylcyclotrisiloxane

**RPE** - Respiratory Protective Equipment  
**LC50** - Lethal Concentration 50%  
**NOEC** - No Observed Effect Concentration  
**PBT** - Persistent, Bioaccumulative, Toxic

**LD50** - Lethal Dose 50%  
**EC50** - Effective Concentration 50%  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**