

ALFAAB24198

## Phenolphthalein disulfate tripotassium salt hydrate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:**  
**Product Description:** 酞酞二硫酸三钾水合物  
**Phenolphthalein disulfate tripotassium salt hydrate**

**Cat No. :** B24198  
**CAS No** 1080664-81-8  
**Molecular Formula** C20 H13 K3 O11 S2 . 3 H2 O

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
Off-white

**Odor**  
No information available

#### Emergency Overview

The product contains no substances which at their given concentration are considered to be hazardous to health.

#### Classification of the substance or mixture

Based on available data, the classification criteria are not met

#### Label Elements

None required

#### Physical and Chemical Hazards

None identified.

#### Health Hazards

The product contains no substances which at their given concentration are considered to be hazardous to health.

#### Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. .

# SAFETY DATA SHEET

## Phenolphthalein disulfate tripotassium salt hydrate

This product does not contain any known or suspected endocrine disruptors.

### SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component   | CAS No       | Weight % |
|---|--------------|----------|
| Benzoic acid, 2-[hydroxybis[4-(sulfooxy)phenyl]methyl]-, tripotassium salt trihydrate | 1080664-81-8 | >95      |
| Benzoic acid, 2-[hydroxybis[4-(sulfooxy)phenyl]methyl]-, tripotassium salt            | 62625-16-5   | -        |

### SECTION 4. FIRST AID MEASURES

#### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

#### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.

#### Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

#### Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

#### Most important symptoms and effects

None reasonably foreseeable.

#### Self-Protection of the First Aider

No special precautions required.

#### Notes to Physician

Treat symptomatically.

### SECTION 5. FIRE-FIGHTING MEASURES

#### Suitable Extinguishing Media

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

#### Extinguishing media which must not be used for safety reasons

No information available.

#### Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

#### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

#### Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

#### Environmental Precautions

Should not be released into the environment.

#### Methods for Containment and Clean Up

# SAFETY DATA SHEET

## Phenolphthalein disulfate tripotassium salt hydrate

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

### SECTION 7. HANDLING AND STORAGE

#### Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid dust formation.

#### Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. To maintain product quality: Keep refrigerated.

#### Specific Use(s)

Use in laboratories

### SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

#### Control Parameters

#### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

#### Exposure Controls

#### Engineering Measures

None under normal use conditions. .

#### Personal protective equipment

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time                 | Glove thickness | EU standard | Glove comments        |
|----------------|-----------------------------------|-----------------|-------------|-----------------------|
| Nitrile rubber | See manufacturers recommendations | -               | EN 374      | (minimum requirement) |
| Neoprene       |                                   |                 |             |                       |
| Natural rubber |                                   |                 |             |                       |
| PVC            |                                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particle filter

**Small scale/Laboratory use** Maintain adequate ventilation

## Phenolphthalein disulfate tripotassium salt hydrate

|                                 |  |
|---------------------------------|--|
| Hygiene Measures                | Handle in accordance with good industrial hygiene and safety practice. |
| Environmental exposure controls | No information available.  |

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

|   |                            |                                   |
|---|----------------------------|-----------------------------------|
| Appearance                              | Off-white                  |                                   |
| Physical State                          | Solid                      |                                   |
| Odor                                    | No information available   |                                   |
| Odor Threshold                          | No data available          |                                   |
| pH                                      | No information available   |                                   |
| Melting Point/Range                     | 230 °C / 446 °F            |                                   |
| Softening Point                         | No data available          |                                   |
| Boiling Point/Range                     | No information available   |                                   |
| Flash Point                             | No information available   | Method - No information available |
| Evaporation Rate                        | Not applicable             | Solid                             |
| Flammability (solid,gas)                | No information available   |                                   |
| Explosion Limits                        | No data available          |                                   |
| Vapor Pressure                          | No data available          |                                   |
| Vapor Density                           | Not applicable             | Solid                             |
| Specific Gravity / Density              | No data available          |                                   |
| Bulk Density                            | No data available          |                                   |
| Water Solubility                        | Slightly soluble           |                                   |
| Solubility in other solvents            | No information available   |                                   |
| Partition Coefficient (n-octanol/water) |                            |                                   |
| Autoignition Temperature                | No data available          |                                   |
| Decomposition Temperature               | No data available          |                                   |
| Viscosity                               | Not applicable             | Solid                             |
| Explosive Properties                    | No information available   |                                   |
| Oxidizing Properties                    | No information available   |                                   |
| Molecular Formula                       | C20 H13 K3 O11 S2 . 3 H2 O |                                   |
| Molecular Weight                        | 664.78                     |                                   |

## SECTION 10. STABILITY AND REACTIVITY

|                          |   |
|--------------------------|---|
| Stability                | Stable under normal conditions.                           |
| Hazardous Reactions      | None under normal processing.                             |
| Hazardous Polymerization | Hazardous polymerization does not occur.                  |
| Conditions to Avoid      | Incompatible products. Excess heat. Avoid dust formation. |
| Materials to avoid       | Strong oxidizing agents.                                  |

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

|                                |   |
|--------------------------------|---|
| Product Information            | No acute toxicity information is available for this product |
| (a) acute toxicity;            |   |
| (b) skin corrosion/irritation; | No data available   |

# SAFETY DATA SHEET

## Phenolphthalein disulfate tripotassium salt hydrate

|  |  |
|--|--|
| (c) serious eye damage/irritation;         | No data available  |
| (d) respiratory or skin sensitization;     |  |
| Respiratory                                | No data available  |
| Skin                                       | No data available  |
| (e) germ cell mutagenicity;                | No data available  |
| (f) carcinogenicity;                       | No data available<br>There are no known carcinogenic chemicals in this product |
| (g) reproductive toxicity;                 | No data available  |
| (h) STOT-single exposure;                  | No data available  |
| (i) STOT-repeated exposure;                | No data available  |
| Target Organs                              | No information available.  |
| (j) aspiration hazard;                     | Not applicable<br>Solid  |
| Other Adverse Effects                      | The toxicological properties have not been fully investigated.                 |
| Symptoms / effects, both acute and delayed | No information available   |

### SECTION 12. ECOLOGICAL INFORMATION

|                                 |   |
|---------------------------------|---|
| Ecotoxicity effects             | Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants. |
| Persistence and Degradability   |   |
| Persistence                     | May persist, based on information available.  |
| Bioaccumulative Potential       | May have some potential to bioaccumulate  |
| Mobility in soil                | Is not likely mobile in the environment due its low water solubility  |
| Endocrine Disruptor Information | This product does not contain any known or suspected endocrine disruptors   |
| Persistent Organic Pollutant    | This product does not contain any known or suspected substance  |
| Ozone Depletion Potential       | This product does not contain any known or suspected substance  |

### SECTION 13. DISPOSAL CONSIDERATIONS

|                                     |  |
|-------------------------------------|--|
| Waste from Residues/Unused Products | Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to |
|-------------------------------------|--|

## Phenolphthalein disulfate tripotassium salt hydrate

ensure complete and accurate classification.

**Contaminated Packaging**

Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

**Other Information**

Waste codes should be assigned by the user based on the application for which the product was used.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

Not Regulated

**IMDG/IMO**

Not regulated

**IATA**

Not regulated

**Special Precautions for User**

No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component  | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS    | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|--|---|---|------|-------|-----------|------|-----|-------|------|------|------|------|
| Benzoic acid, 2-[hydroxybis[4-(sulfooxy)phenyl]methyl]-, tripotassium salt | -   | -                                       | X    | -     | 263-648-5 | X    | X   | -     | -    |      | -    | -    |

**National Regulations****SECTION 16. OTHER INFORMATION****Prepared By**

Health, Safety and Environmental Department

**Creation Date**

30-Apr-2010

**Revision Date**

22-Apr-2024

**Revision Summary**

New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

**Legend**

CAS - Chemical Abstracts Service

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

EINECS/ELINCS - European Inventory of Existing Commercial Chemical

## Phenolphthalein disulfate tripotassium salt hydrate

---

Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances  
**IECSC** - Chinese Inventory of Existing Chemical Substances  
**KECL** - Korean Existing and Evaluated Chemical Substances

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances  
**AICS** - Australian Inventory of Chemical Substances  
**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**