

ALFAAL04202

4-Chloro-2,5-dimethoxyaniline

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 4-氯-2,5-二甲氧基苯胺
4-Chloro-2,5-dimethoxyaniline

Cat No. : L04202
CAS No 6358-64-1
Molecular Formula C8 H10 Cl N O2

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid

Appearance
No information available

Odor
No information available

Emergency Overview
Harmful if swallowed.

Classification of the substance or mixture

Acute Oral Toxicity

Category 4

Label Elements



Signal Word

Warning

Hazard Statements
H302 - Harmful if swallowed

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

Response

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell

P330 - Rinse mouth

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Benzenamine, 4-chloro-2,5-dimethoxy-	6358-64-1	>95

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

Most important symptoms and effects

None reasonably foreseeable.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid dust formation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

4-Chloro-2,5-dimethoxyaniline

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Long sleeved clothing

Respiratory Protection

No protective equipment is needed under normal use conditions.

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Small scale/Laboratory use

Maintain adequate ventilation

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls

No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical State

Solid

Odor

No information available

Odor Threshold

No data available

pH

No data available

Melting Point/Range

118 - 120 °C / 244.4 - 248 °F

Softening Point

No data available

Boiling Point/Range

No information available

Flash Point

163 °C / 325.4 °F

Method - No information available

Evaporation Rate

Not applicable

Solid

Flammability (solid,gas)

No information available

Explosion Limits

No data available

Vapor Pressure

No data available

Vapor Density

Not applicable

Solid

Specific Gravity / Density

No data available

Bulk Density

No data available

Water Solubility

4 g/L (20°C)

Solubility in other solvents

No information available

Partition Coefficient (n-octanol/water)

Component

log Pow

Benzenamine, 4-chloro-2,5-dimethoxy- 1.8

Autoignition Temperature

395 °C / 743 °F

Decomposition Temperature

No data available

Viscosity

Not applicable

Solid

Explosive Properties

No information available

Oxidizing Properties

No information available

4-Chloro-2,5-dimethoxyaniline

Molecular Formula C8 H10 Cl N O2
Molecular Weight 187.62

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.

Hazardous Reactions None under normal processing.

Hazardous Polymerization No information available.

Conditions to Avoid Avoid dust formation. Incompatible products. Excess heat.

Materials to avoid No information available.

Hazardous Decomposition Products Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Benzenamine, 4-chloro-2,5-dimethoxy-	LD50 = 1260 mg/kg (Rat)	LD50 > 2000 mg/kg (Rat)	

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

The table below indicates whether each agency has listed any ingredient as a carcinogen

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; Not applicable
Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

4-Chloro-2,5-dimethoxyaniline

Symptoms / effects, both acute and delayed No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Do not empty into drains. .

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Benzenamine, 4-chloro-2,5-dimethoxy-	LC50: = 111 mg/L, 96h static (Brachydanio rerio)			

Persistence and Degradability
Persistence Persistence is unlikely.

Bioaccumulative Potential Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Benzenamine, 4-chloro-2,5-dimethoxy-	1.8	No data available

Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport Not Regulated

IMDG/IMO Not regulated

IATA Not regulated

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan

4-Chloro-2,5-dimethoxyaniline

(ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Benzenamine, 4-chloro-2,5-dimethoxy -	-	-	X	-	228-782-0	X	-	X	X	X	-	-

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 25-Oct-2010
Revision Date 22-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet