

ALFAAL05596

2-Octyn-1-ol

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

| | |
|-------------------------------|--|
| 产品说明: Product Description: | 2-辛炔-1-醇 2-Octyn-1-ol |
| Cat No. : | L05596 |
| CAS No | 20739-58-6 |
| Molecular Formula | C8 H14 O |
| Supplier | Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608 |
| Emergency Telephone Number | For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887 |
| E-mail address | begel.sdsdesk@thermofisher.com |
| Recommended Use | Laboratory chemicals. |
| Uses advised against | No Information available |

SECTION 2. HAZARD IDENTIFICATION

| | | |
|---|---------------------|----------------------------------|
| Physical State Liquid | Appearance Clear | Odor No information available |
| Emergency Overview Combustible liquid. Harmful if swallowed. Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. | | |

Classification of the substance or mixture

| | |
|--|------------|
| Flammable liquids. | Category 4 |
| Acute Oral Toxicity | Category 4 |
| Skin Corrosion/Irritation | Category 2 |
| Serious Eye Damage/Eye Irritation | Category 2 |
| Specific target organ toxicity - (single exposure) | Category 3 |

Label Elements



Signal Word

Warning

Hazard Statements

H227 - Combustible liquid
H302 - Harmful if swallowed
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H335 - May cause respiratory irritation

Precautionary Statements**Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a POISON CENTER or doctor if you feel unwell
P330 - Rinse mouth
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material.

Health Hazards

Harmful if swallowed. Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component | CAS No | Weight % |
|--------------|------------|----------|
| 2-OCTYN-1-OL | 20739-58-6 | 98 |

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

Inhalation

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

Ingestion

Clean mouth with water. Get medical attention.

Most important symptoms and effects

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Combustible material. Containers may explode when heated.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Do not let this chemical enter the environment. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments |
|----------------|-----------------------------------|-----------------|-------------|-----------------------|
| Viton (R) | See manufacturers recommendations | - | EN 374 | (minimum requirement) |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

| | |
|----------------------------|---|
| Appearance | Clear |
| Physical State | Liquid |
| Odor | No information available |
| Odor Threshold | No data available |
| pH | No information available |
| Melting Point/Range | No data available |
| Softening Point | No data available |
| Boiling Point/Range | 76 - 78 °C / 168.8 - 172.4 °F @ 2 mmHg |
| Flash Point | 91 °C / 195.8 °F Method - No information available |

| | | |
|---|--------------------------|--|
| Evaporation Rate | No data available | |
| Flammability (solid,gas) | Not applicable | Liquid |
| Explosion Limits | No data available | |
| Vapor Pressure | No data available | |
| Vapor Density | No data available | (Air = 1.0) |
| Specific Gravity / Density | 0.880 | |
| Bulk Density | Not applicable | Liquid |
| Water Solubility | No information available | |
| Solubility in other solvents | No information available | |
| Partition Coefficient (n-octanol/water) | | |
| Autoignition Temperature | No data available | |
| Decomposition Temperature | No data available | |
| Viscosity | No data available | |
| Explosive Properties | | explosive air/vapour mixtures possible |
| Oxidizing Properties | No information available | |
| Molecular Formula | C8 H14 O | |
| Molecular Weight | 126.2 | |

SECTION 10. STABILITY AND REACTIVITY

| | |
|----------------------------------|--|
| Stability | Stable under normal conditions. |
| Hazardous Reactions | No information available. |
| Hazardous Polymerization | Hazardous polymerization does not occur. |
| Conditions to Avoid | Incompatible products. Keep away from open flames, hot surfaces and sources of ignition. |
| Materials to avoid | Strong oxidizing agents. |
| Hazardous Decomposition Products | Carbon monoxide (CO). Carbon dioxide (CO ₂). |

SECTION 11. TOXICOLOGICAL INFORMATION**Product Information**

| | |
|--|---|
| (a) acute toxicity; | |
| (b) skin corrosion/irritation; | Category 2 |
| (c) serious eye damage/irritation; | Category 2 |
| (d) respiratory or skin sensitization; | |
| Respiratory | No data available |
| Skin | No data available |
| (e) germ cell mutagenicity; | No data available |
| (f) carcinogenicity; | No data available |
| | There are no known carcinogenic chemicals in this product |
| (g) reproductive toxicity; | No data available |

| | |
|--|---|
| (h) STOT-single exposure; | Category 3 |
| Results / Target organs | Respiratory system |
| (i) STOT-repeated exposure; | No data available |
| Target Organs | No information available. |
| (j) aspiration hazard; | No data available |
| Other Adverse Effects | The toxicological properties have not been fully investigated. |
| Symptoms / effects, both acute and delayed | Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting |

SECTION 12. ECOLOGICAL INFORMATION

| | |
|--|---|
| Ecotoxicity effects | Do not empty into drains. |
| Persistence and Degradability Persistence | No information available Persistence is unlikely, based on information available. |
| Bioaccumulative Potential | Bioaccumulation is unlikely |
| Mobility in soil | The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air. |
| Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential | This product does not contain any known or suspected endocrine disruptors This product does not contain any known or suspected substance This product does not contain any known or suspected substance |

SECTION 13. DISPOSAL CONSIDERATIONS

| | |
|-------------------------------------|--|
| Waste from Residues/Unused Products | Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. |
| Contaminated Packaging | Dispose of this container to hazardous or special waste collection point. |
| Other Information | Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. |

SECTION 14. TRANSPORT INFORMATION

| | |
|--------------------------------|---------------|
| <u>Road and Rail Transport</u> | Not Regulated |
| <u>IMDG/IMO</u> | Not regulated |
| <u>IATA</u> | Not regulated |

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|--------------|---|---|------|-------|--------|------|-----|-------|------|------|------|------|
| 2-OCTYN-1-OL | - | - | X | - | - | - | - | - | - | - | - | - |

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 27-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet