

ALFAAL12346

## 4-Amino-2-(trifluoromethyl)benzonitrile

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:**  
**Product Description:** 4-氨基-2-(三氟甲基)苯甲腈  
 4-Amino-2-(trifluoromethyl)benzonitrile

**Cat No. :** L12346  
**Synonyms** 5-Amino-2-cyanobenzotrifluoride; 4-Cyano-3-trifluoromethylaniline  
**Molecular Formula** C8 H5 F3 N2

**Supplier** Alfa Aesar  
 Avocado Research Chemicals, Ltd.  
 Shore Road  
 Port of Heysham Industrial Park  
 Heysham, Lancashire LA3 2XY  
 United Kingdom  
 Office Tel: +44 (0) 1524 850506  
 Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** Call Carechem 24 at  
 +44 (0) 1865 407333 (English only);  
 +44 (0) 1235 239670 (Multi-language)

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
Off-white

**Odor**  
No information available

#### Emergency Overview

Harmful if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation. Air sensitive.

#### Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Dusts and Mists	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements

# SAFETY DATA SHEET

## 4-Amino-2-(trifluoromethyl)benzonitrile

**Signal Word****Warning****Hazard Statements**

H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation  
H302 + H312 + H332 - Harmful if swallowed, in contact with skin or if inhaled

**Precautionary Statements****Prevention**

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P330 - Rinse mouth  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Harmful if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
4-Amino-2-(trifluoromethyl)benzonitrile	654-70-6	95

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

# SAFETY DATA SHEET

## 4-Amino-2-(trifluoromethyl)benzonitrile

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

Use personal protective equipment as required.

**Notes to Physician**

Treat symptomatically.

### SECTION 5. FIRE-FIGHTING MEASURES

**Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

### SECTION 7. HANDLING AND STORAGE

**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation. Ensure adequate ventilation.

**Storage**

Keep containers tightly closed in a dry, cool and well-ventilated place. Store under an inert atmosphere.

**Specific Use(s)**

Use in laboratories

# SAFETY DATA SHEET

## 4-Amino-2-(trifluoromethyl)benzonitrile

### SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

#### Control Parameters

#### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

#### Exposure Controls

#### Engineering Measures

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

#### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
 When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** When using do not eat, drink or smoke. Provide regular cleaning of equipment, work area and clothing.

**Environmental exposure controls** Do not allow material to contaminate ground water system.

### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

# SAFETY DATA SHEET

## 4-Amino-2-(trifluoromethyl)benzonitrile

<b>Appearance</b>	Off-white	
<b>Physical State</b>	Solid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	136 - 139 °C / 276.8 - 282.2 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	No information available	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	No information available	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C8 H5 F3 N2	
<b>Molecular Weight</b>	186.14	

### SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under recommended storage conditions. Air sensitive.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat. Avoid dust formation. Exposure to air.
<b>Materials to avoid</b>	Strong oxidizing agents. Strong acids. Strong reducing agents.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Nitrogen oxides (NO <sub>x</sub> ). Hydrogen fluoride. Fluorine.

### SECTION 11. TOXICOLOGICAL INFORMATION

#### Product Information

<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	Category 2
<b>(c) serious eye damage/irritation;</b>	Category 2
<b>(d) respiratory or skin sensitization;</b>	
Respiratory	No data available
Skin	No data available

**SAFETY DATA SHEET**  
**4-Amino-2-(trifluoromethyl)benzonitrile**

<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	Category 3
<b>Results / Target organs</b>	Respiratory system
<b>(i) STOT-repeated exposure;</b>	No data available
<b>Target Organs</b>	No information available.
<b>(j) aspiration hazard;</b>	Not applicable Solid
<b>Other Adverse Effects</b>	The hazards associated with nitriles may be seen in this product.
<b>Symptoms / effects,both acute and delayed</b>	No information available

**SECTION 12. ECOLOGICAL INFORMATION**

<b>Ecotoxicity effects</b>	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
<b>Persistence and Degradability</b>	No information available
<b>Bioaccumulative Potential</b>	No information available
<b>Mobility in soil</b>	No information available
<b>Endocrine Disruptor Information</b>	This product does not contain any known or suspected endocrine disruptors
<b>Persistent Organic Pollutant</b>	This product does not contain any known or suspected substance
<b>Ozone Depletion Potential</b>	This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

<b>Waste from Residues/Unused Products</b>	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point.
<b>Other Information</b>	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

**SECTION 14. TRANSPORT INFORMATION**

# SAFETY DATA SHEET

## 4-Amino-2-(trifluoromethyl)benzonitrile

### Road and Rail Transport

**UN-No** UN3439  
**Proper Shipping Name** NITRILES, SOLID, TOXIC, N.O.S.  
**Hazard Class** 6.1  
**Packing Group** III

### IMDG/IMO

**UN-No** UN3439  
**Proper Shipping Name** NITRILES, SOLID, TOXIC, N.O.S.  
**Hazard Class** 6.1  
**Packing Group** III

### IATA

**UN-No** UN3439  
**Proper Shipping Name** NITRILES, SOLID, TOXIC, N.O.S.  
**Hazard Class** 6.1  
**Packing Group** III

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
4-Amino-2-(trifluoromethyl)benzonitrile	-	-	X	-	-	-	-	-	-	X	-	-

### National Regulations

## SECTION 16. OTHER INFORMATION

**Creation Date** 12-Feb-2009  
**Revision Date** 27-Dec-2020  
**Revision Summary** Not applicable.

### Training Advice

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

### Legend

# SAFETY DATA SHEET

## 4-Amino-2-(trifluoromethyl)benzonitrile

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer  
Predicted No Effect Concentration (PNEC)

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**IMO/MDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

VOC (volatile organic compound)

### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**