

ALFAAL10386

## Diisopropyl azodicarboxylate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:**  
**Product Description:** 偶氮二甲酸二异丙酯  
Diisopropyl azodicarboxylate

**Cat No. :** L10386  
**Synonyms** DIAD  
**CAS No** 2446-83-5  
**Molecular Formula** C8 H14 N2 O4

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
Orange

**Odor**  
pungent

#### Emergency Overview

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. May cause damage to organs through prolonged or repeated exposure. Toxic to aquatic life with long lasting effects. Sensitivity to light.

#### Classification of the substance or mixture

|  |            |
|--|------------|
| Skin Corrosion/Irritation                            | Category 2 |
| Serious Eye Damage/Eye Irritation                    | Category 2 |
| Specific target organ toxicity - (single exposure)   | Category 3 |
| Specific target organ toxicity - (repeated exposure) | Category 2 |
| Chronic aquatic toxicity                             | Category 2 |

#### Label Elements



**Signal Word****Warning****Hazard Statements**

H315 - Causes skin irritation

H319 - Causes serious eye irritation

H335 - May cause respiratory irritation

H373 - May cause damage to organs through prolonged or repeated exposure

H411 - Toxic to aquatic life with long lasting effects

**Precautionary Statements****Prevention**

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

P264 - Wash face, hands and any exposed skin thoroughly after handling

**Response**

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P312 - Call a POISON CENTER or doctor if you feel unwell

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. May cause damage to organs through prolonged or repeated exposure.

**Environmental hazards**

Toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component                    | CAS No    | Weight % |
|------------------------------|-----------|----------|
| Diisopropyl azodicarboxylate | 2446-83-5 | > 94     |

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects**

No information available.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Containers may explode when heated.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system.

**Methods for Containment and Clean Up**

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation.

**Storage**

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat. Protect from direct sunlight. Containers should be vented periodically in order to overcome pressure buildup. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. To maintain product quality: Keep refrigerated. Keep under nitrogen.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

## Diisopropyl azodicarboxylate

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material                                      | Breakthrough time                    | Glove thickness | EU standard | Glove comments        |
|---|--------------------------------------|-----------------|-------------|-----------------------|
| Nitrile rubber<br>Neoprene<br>Natural rubber<br>PVC | See manufacturers<br>recommendations | -               | EN 374      | (minimum requirement) |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

|                            |                          |
|----------------------------|--------------------------|
| <b>Appearance</b>          | Orange                   |
| <b>Physical State</b>      | Liquid                   |
| <b>Odor</b>                | pungent                  |
| <b>Odor Threshold</b>      | No data available        |
| <b>pH</b>                  | No information available |
| <b>Melting Point/Range</b> | 3 - 5 °C / 37.4 - 41 °F  |
| <b>Softening Point</b>     | No data available        |

**SAFETY DATA SHEET****Diisopropyl azodicarboxylate**

|  |                          |  |
|--|--------------------------|--|
| <b>Boiling Point/Range</b>                     | 75 °C / 167 °F           | @ 0.2 mmHg                               |
| <b>Flash Point</b>                             | 106 °C / 222.8 °F        | <b>Method</b> - No information available |
| <b>Evaporation Rate</b>                        | No data available        |  |
| <b>Flammability (solid,gas)</b>                | Not applicable           | Liquid                                   |
| <b>Explosion Limits</b>                        | No data available        |  |
| <b>Vapor Pressure</b>                          | No data available        |  |
| <b>Vapor Density</b>                           | No data available        | (Air = 1.0)                              |
| <b>Specific Gravity / Density</b>              | 1.020                    |  |
| <b>Bulk Density</b>                            | Not applicable           | Liquid                                   |
| <b>Water Solubility</b>                        | Insoluble                |  |
| <b>Solubility in other solvents</b>            | No information available |  |
| <b>Partition Coefficient (n-octanol/water)</b> |                          |  |
| <b>Autoignition Temperature</b>                | No data available        |  |
| <b>Decomposition Temperature</b>               | No data available        |  |
| <b>Viscosity</b>                               | No data available        |  |
| <b>Explosive Properties</b>                    | No information available |  |
| <b>Oxidizing Properties</b>                    | No information available |  |
| <b>Molecular Formula</b>                       | C8 H14 N2 O4             |  |
| <b>Molecular Weight</b>                        | 202.21                   |  |

**SECTION 10. STABILITY AND REACTIVITY**

|   |  |
|---|--|
| <b>Stability</b>                        | Risk of explosion if heated under confinement. Stable up to 100°C. Volatile at high temperatures. heat sensitive. Light sensitive.                           |
| <b>Hazardous Reactions</b>              | None under normal processing.  |
| <b>Hazardous Polymerization</b>         | No information available.  |
| <b>Conditions to Avoid</b>              | To avoid thermal decomposition, do not overheat. Keep away from open flames, hot surfaces and sources of ignition. Exposure to light. Incompatible products. |
| <b>Materials to avoid</b>               | Strong oxidizing agents. Strong bases. Alcohols. Alkaline.   |
| <b>Hazardous Decomposition Products</b> | Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ).  |

**SECTION 11. TOXICOLOGICAL INFORMATION**

|   |   |
|---|---|
| <b>Product Information</b>  | No acute toxicity information is available for this product |
| <b>(a) acute toxicity;<br/>Toxicology data for the components</b> |   |
| <b>(b) skin corrosion/irritation;</b>                             | Category 2  |
| <b>(c) serious eye damage/irritation;</b>                         | Category 2  |
| <b>(d) respiratory or skin sensitization;</b>                     |   |
| <b>Respiratory</b>  | No data available   |
| <b>Skin</b>   | No data available   |
| <b>(e) germ cell mutagenicity;</b>                                | No data available   |
| <b>(f) carcinogenicity;</b>                                       | No data available   |

## Diisopropyl azodicarboxylate

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; Category 3

Results / Target organs Respiratory system

(i) STOT-repeated exposure; Category 2

Target Organs None known.

(j) aspiration hazard; No data available

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed No information available

**SECTION 12. ECOLOGICAL INFORMATION**

**Ecotoxicity effects** Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

**Persistence and Degradability** Not readily biodegradable  
**Persistence** Persistence is unlikely, based on information available.  
**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential** Bioaccumulation is unlikely

**Mobility in soil** The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air.

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

**SECTION 14. TRANSPORT INFORMATION**

## Diisopropyl azodicarboxylate

**Road and Rail Transport**

UN-No UN3082  
Proper Shipping Name Environmentally hazardous substances, liquid, n.o.s.  
Technical Shipping Name Diisopropyl azodicarboxylate  
Hazard Class 9  
Packing Group III

**IMDG/IMO**

UN-No UN3082  
Proper Shipping Name Environmentally hazardous substances, liquid, n.o.s.  
Technical Shipping Name Diisopropyl azodicarboxylate  
Hazard Class 9  
Packing Group III

**IATA**

UN-No UN3082  
Proper Shipping Name Environmentally hazardous substances, liquid, n.o.s.  
Technical Shipping Name Diisopropyl azodicarboxylate  
Hazard Class 9  
Packing Group III

Special Precautions for User No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component                    | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS    | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL      |
|------------------------------|---|---|------|-------|-----------|------|-----|-------|------|------|------|-----------|
| Diisopropyl azodicarboxylate | -   | -                                       | X    | X     | 219-502-8 | -    | -   | -     | X    | X    | -    | 99-3-1285 |

**National Regulations****SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department  
Creation Date 22-Nov-2004  
Revision Date 26-Apr-2024  
Revision Summary New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.  
Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

## Diisopropyl azodicarboxylate

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Physical hazards**

On basis of test data

**Health Hazards**

Calculation method

**Environmental hazards**

Calculation method

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**