

ALFAAL14010

Ethyl 5-fluoroindole-2-carboxylate

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	5-氟吲哚-2-甲酸乙酯 Ethyl 5-fluoroindole-2-carboxylate
Cat No. : Molecular Formula	L14010 C11 H10 F N O2
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use Uses advised against	Laboratory chemicals. No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Solid Crystalline	Appearance White	Odor No information available
Emergency Overview Moisture sensitive.		

Classification of the substance or mixture

Based on available data, the classification criteria are not met

Label Elements

None required

Physical and Chemical Hazards

None identified.

Health Hazards

The product contains no substances which at their given concentration are considered to be hazardous to health.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Ethyl 5-fluoroindole-2-carboxylate	348-36-7	<=100

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.

Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

Most important symptoms and effects

None reasonably foreseeable.

Self-Protection of the First Aider

No special precautions required.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid dust formation.

Storage

Protect from moisture.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Engineering Measures

None under normal use conditions. .

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particle filter

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	White	
Physical State	Solid Crystalline	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	147 - 152 °C / 296.6 - 305.6 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Insoluble in water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C11 H10 F N O2	
Molecular Weight	207.21	

SECTION 10. STABILITY AND REACTIVITY

Stability	Moisture sensitive.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	None known.
Materials to avoid	No information available.
Hazardous Decomposition Products	None under normal use conditions.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;	
(b) skin corrosion/irritation;	No data available

(c) serious eye damage/irritation;	No data available
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Not applicable
	Solid
Symptoms / effects, both acute and delayed	No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
Persistence and Degradability Persistence	Insoluble in water.
Bioaccumulative Potential	May have some potential to bioaccumulate
Mobility in soil	Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility
Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential	This product does not contain any known or suspected endocrine disruptors This product does not contain any known or suspected substance This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.
Contaminated Packaging	Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use

empty containers.

Other Information

Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

Not Regulated

IMDG/IMO

Not regulated

IATA

Not regulated

Special Precautions for User

No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

National Regulations**SECTION 16. OTHER INFORMATION****Prepared By**

Health, Safety and Environmental Department

Revision Date

08-May-2024

Revision Summary

New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet