

ALFAAL15533

## Benzyl tert-butyl malonate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	丙二酸叔丁酯苯甲酯 Benzyl tert-butyl malonate
Cat No. : Molecular Formula	L15533 C14 H18 O4
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use Uses advised against	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State Liquid	Appearance Colorless	Odor No information available
<b>Emergency Overview</b> The product contains no substances which at their given concentration are considered to be hazardous to health.		

#### Classification of the substance or mixture

Based on available data, the classification criteria are not met

#### Label Elements

None required

#### **Physical and Chemical Hazards**

None identified.

#### **Health Hazards**

The product contains no substances which at their given concentration are considered to be hazardous to health.

#### **Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Benzyl tert-butyl malonate	72594-86-6	<=100

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.

**Inhalation**

Remove to fresh air. Get medical attention immediately if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

No special precautions required.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation.

### Storage

Keep container tightly closed in a dry and well-ventilated place.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Exposure Controls

### Engineering Measures

None under normal use conditions.

### Personal protective equipment

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particle filter

**Small scale/Laboratory use** Maintain adequate ventilation  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Colorless	
Physical State	Liquid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	No data available	
Bulk Density	Not applicable	Liquid
Water Solubility	Immiscible	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C14 H18 O4	
Molecular Weight	250.30	

## SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	None known.
Materials to avoid	No information available.
Hazardous Decomposition Products	None under normal use conditions.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

(a) acute toxicity;	
(b) skin corrosion/irritation;	No data available
(c) serious eye damage/irritation;	No data available

**(d) respiratory or skin sensitization;**

Respiratory	No data available
Skin	No data available

**(e) germ cell mutagenicity;** No data available**(f) carcinogenicity;** No data available  
There are no known carcinogenic chemicals in this product**(g) reproductive toxicity;** No data available**(h) STOT-single exposure;** No data available**(i) STOT-repeated exposure;** No data available  
**Target Organs** No information available.**(j) aspiration hazard;** No data available**Symptoms / effects, both acute and delayed** No information available**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects** Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.**Persistence and Degradability**  
**Persistence** Immiscible with water.**Bioaccumulative Potential** May have some potential to bioaccumulate**Mobility in soil** Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products** Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.**Contaminated Packaging** Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.**Other Information** Waste codes should be assigned by the user based on the application for which the product was used.

**SECTION 14. TRANSPORT INFORMATION**

<b>Road and Rail Transport</b>	Not Regulated
<b>IMDG/IMO</b>	Not regulated
<b>IATA</b>	Not regulated
<b>Special Precautions for User</b>	No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

**National Regulations****SECTION 16. OTHER INFORMATION**

<b>Prepared By</b>	Health, Safety and Environmental Department
<b>Revision Date</b>	08-May-2024
<b>Revision Summary</b>	New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

**Legend**

<b>CAS</b> - Chemical Abstracts Service	<b>TSCA</b> - United States Toxic Substances Control Act Section 8(b) Inventory
<b>EINECS/ELINCS</b> - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances	<b>DSL/NDSL</b> - Canadian Domestic Substances List/Non-Domestic Substances List
<b>PICCS</b> - Philippines Inventory of Chemicals and Chemical Substances	<b>ENCS</b> - Japanese Existing and New Chemical Substances
<b>IECSC</b> - Chinese Inventory of Existing Chemical Substances	<b>AICS</b> - Australian Inventory of Chemical Substances
<b>KECL</b> - Korean Existing and Evaluated Chemical Substances	<b>NZIoC</b> - New Zealand Inventory of Chemicals
<b>WEL</b> - Workplace Exposure Limit	<b>TWA</b> - Time Weighted Average
<b>ACGIH</b> - American Conference of Governmental Industrial Hygienists	<b>IARC</b> - International Agency for Research on Cancer
<b>DNEL</b> - Derived No Effect Level	<b>PNEC</b> - Predicted No Effect Concentration
<b>RPE</b> - Respiratory Protective Equipment	<b>LD50</b> - Lethal Dose 50%
<b>LC50</b> - Lethal Concentration 50%	<b>EC50</b> - Effective Concentration 50%
<b>NOEC</b> - No Observed Effect Concentration	<b>POW</b> - Partition coefficient Octanol:Water
<b>PBT</b> - Persistent, Bioaccumulative, Toxic	<b>vPvB</b> - very Persistent, very Bioaccumulative
<b>ICAO/IATA</b> - International Civil Aviation Organization/International Air Transport Association	<b>IMO/IMDG</b> - International Maritime Organization/International Maritime Dangerous Goods Code
<b>ADR</b> - European Agreement Concerning the International Carriage of Dangerous Goods by Road	<b>MARPOL</b> - International Convention for the Prevention of Pollution from Ships

**Benzyl tert-butyl malonate**

**OECD** - Organisation for Economic Co-operation and Development  
**BCF** - Bioconcentration factor

**ATE** - Acute Toxicity Estimate  
**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**