

ALFAAL13792

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 2, 2, 2-三氯-1, 1-双(三氟甲基)乙醇  
 Product Description: 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

Cat No. : L13792  
 CAS No 7594-49-2  
 Molecular Formula C4 HCl3 F6 O

Supplier Avocado Research Chemicals Ltd.  
 (Part of Thermo Fisher Scientific)  
 Shore Road, Heysham  
 Lancashire, LA3 2XY,  
 United Kingdom  
 Office Tel: +44 (0) 1524 850506  
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
 Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State  
 Liquid

Appearance  
 Colorless

Odor  
 No information available

#### Emergency Overview

Harmful if swallowed. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

#### Classification of the substance or mixture

|  |            |
|--|------------|
| Acute Oral Toxicity                                | Category 4 |
| Acute Inhalation Toxicity - Vapors                 | Category 4 |
| Skin Corrosion/Irritation                          | Category 2 |
| Serious Eye Damage/Eye Irritation                  | Category 2 |
| Specific target organ toxicity - (single exposure) | Category 3 |

#### Label Elements



Signal Word

Warning

# SAFETY DATA SHEET

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

**Hazard Statements**

H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation  
H302 + H332 - Harmful if swallowed or if inhaled

**Precautionary Statements****Prevention**

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P330 - Rinse mouth  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Harmful if swallowed. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Will likely be mobile in the environment due to its volatility. Spillage unlikely to penetrate soil. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

This product does not contain any known or suspected endocrine disruptors.

### SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component                                       | CAS No    | Weight % |
|---|-----------|----------|
| 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol | 7594-49-2 | <=100    |

### SECTION 4. FIRST AID MEASURES

**General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water.

# SAFETY DATA SHEET

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

### SECTION 5. FIRE-FIGHTING MEASURES

**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

### SECTION 7. HANDLING AND STORAGE

**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation.

**Storage**

Keep refrigerated.

**Specific Use(s)**

Use in laboratories

### SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters**

# SAFETY DATA SHEET

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments        |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Nitrile rubber | See manufacturers | -               | EN 374      | (minimum requirement) |
| Neoprene       | recommendations   |                 |             |                       |
| Natural rubber |                   |                 |             |                       |
| PVC            |                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** conforming to EN14387 Organic gases and vapours filter Type A Brown

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

**Appearance** Colorless  
**Physical State** Liquid

**Odor** No information available  
**Odor Threshold** No data available  
**pH** No information available

## SAFETY DATA SHEET

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

|   |                          |                                   |
|---|--------------------------|-----------------------------------|
| Melting Point/Range                     | No data available        |                                   |
| Softening Point                         | No data available        |                                   |
| Boiling Point/Range                     | 139 °C / 282.2 °F        |                                   |
| Flash Point                             | No information available | Method - No information available |
| Evaporation Rate                        | No data available        |                                   |
| Flammability (solid,gas)                | Not applicable           | Liquid                            |
| Explosion Limits                        | No data available        |                                   |
| Vapor Pressure                          | No data available        |                                   |
| Vapor Density                           | No data available        | (Air = 1.0)                       |
| Specific Gravity / Density              | No data available        |                                   |
| Bulk Density                            | Not applicable           | Liquid                            |
| Water Solubility                        | Immiscible               |                                   |
| Solubility in other solvents            | No information available |                                   |
| Partition Coefficient (n-octanol/water) |                          |                                   |
| Autoignition Temperature                | No data available        |                                   |
| Decomposition Temperature               | No data available        |                                   |
| Viscosity                               | No data available        |                                   |
| Explosive Properties                    | No information available |                                   |
| Oxidizing Properties                    | No information available |                                   |
| Molecular Formula                       | C4 HCl3 F6 O             |                                   |
| Molecular Weight                        | 285.40                   |                                   |

## SECTION 10. STABILITY AND REACTIVITY

|                          |                                 |
|--------------------------|---------------------------------|
| Stability                | Stable under normal conditions. |
| Hazardous Reactions      | None under normal processing.   |
| Hazardous Polymerization | No information available.       |
| Conditions to Avoid      | None known.                     |
| Materials to avoid       | No information available.       |

Hazardous Decomposition Products None under normal use conditions.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

|  |   |
|--|---|
| (a) acute toxicity;                    |   |
| (b) skin corrosion/irritation;         | Category 2  |
| (c) serious eye damage/irritation;     | Category 2  |
| (d) respiratory or skin sensitization; |   |
| Respiratory                            | No data available   |
| Skin                                   | No data available   |
| (e) germ cell mutagenicity;            | No data available   |
| (f) carcinogenicity;                   | No data available   |
|  | There are no known carcinogenic chemicals in this product |

# SAFETY DATA SHEET

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

|  |                           |
|--|---------------------------|
| (g) reproductive toxicity;                 | No data available         |
| (h) STOT-single exposure;                  | Category 3                |
| Results / Target organs                    | Respiratory system        |
| (i) STOT-repeated exposure;                | No data available         |
| Target Organs                              | No information available. |
| (j) aspiration hazard;                     | No data available         |
| Symptoms / effects, both acute and delayed | No information available  |

### SECTION 12. ECOLOGICAL INFORMATION

|  |   |
|--|---|
| Ecotoxicity effects  | Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.   |
| Persistence and Degradability<br>Persistence   | Immiscible with water, Persistence is unlikely, based on information available.   |
| Bioaccumulative Potential  | May have some potential to bioaccumulate  |
| Mobility in soil   | Spillage unlikely to penetrate soil The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces Is not likely mobile in the environment due its low water solubility Will likely be mobile in the environment due to its volatility |
| Endocrine Disruptor Information<br>Persistent Organic Pollutant<br>Ozone Depletion Potential | This product does not contain any known or suspected endocrine disruptors<br>This product does not contain any known or suspected substance<br>This product does not contain any known or suspected substance   |

### SECTION 13. DISPOSAL CONSIDERATIONS

|                                     |  |
|-------------------------------------|--|
| Waste from Residues/Unused Products | Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. |
| Contaminated Packaging              | Dispose of this container to hazardous or special waste collection point.  |
| Other Information                   | Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.  |

### SECTION 14. TRANSPORT INFORMATION

|                         |               |
|-------------------------|---------------|
| Road and Rail Transport | Not Regulated |
| IMDG/IMO                | Not regulated |

# SAFETY DATA SHEET

## 2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

**IATA** Not regulated

**Special Precautions for User** No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

#### National Regulations

### SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 08-May-2024  
**Revision Summary** New emergency telephone response service provider.

#### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

#### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

#### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

# SAFETY DATA SHEET

2,2,2-Trichloro-1,1-bis(trifluoromethyl)ethanol

---

## Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**