

ALFAAL20196

3-(Phenylsulfonyl)propionitrile

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 3-(苯基磺酰基)丙腈
3-(Phenylsulfonyl)propionitrile

Cat No. : L20196
CAS No 10154-75-3
Molecular Formula C9 H9 N O2 S

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid Crystalline

Appearance
White

Odor
Odorless

Emergency Overview
Harmful if swallowed.

Classification of the substance or mixture

Acute Oral Toxicity

Category 4

Label Elements



Signal Word

Warning

Hazard Statements
H302 - Harmful if swallowed

SAFETY DATA SHEET

3-(Phenylsulfonyl)propionitrile

Precautionary Statements

Prevention

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

Response

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell

P330 - Rinse mouth

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
3-(Phenylsulphonyl)propionitrile	10154-75-3	<=100

SECTION 4. FIRST AID MEASURES

General Advice

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

Most important symptoms and effects

None reasonably foreseeable.

Self-Protection of the First Aider

No special precautions required.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid ingestion and inhalation. Avoid dust formation. Do not get in eyes, on skin, or on clothing.

Storage

Keep container tightly closed in a dry and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

None under normal use conditions.

Personal protective equipment**Eye Protection**

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

Protective gloves

SAFETY DATA SHEET

3-(Phenylsulfonyl)propionitrile

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particle filter

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	White	
Physical State	Solid Crystalline	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	94 - 96 °C / 201.2 - 204.8 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Insoluble in water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C9 H9 N O2 S	
Molecular Weight	195.24	

SAFETY DATA SHEET

3-(Phenylsulfonyl)propionitrile

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	None known.
Materials to avoid	No information available.
Hazardous Decomposition Products	Carbon monoxide (CO). Carbon dioxide (CO ₂). Nitrogen oxides (NO _x). Sulfur oxides. Hydrogen cyanide (hydrocyanic acid).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;	
(b) skin corrosion/irritation;	No data available
(c) serious eye damage/irritation;	No data available
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Not applicable Solid
Symptoms / effects, both acute and delayed	No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

SAFETY DATA SHEET

3-(Phenylsulfonyl)propionitrile

Persistence and Degradability
Persistence

Insoluble in water.

Bioaccumulative Potential

May have some potential to bioaccumulate

Mobility in soil

Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility

Endocrine Disruptor Information
Persistent Organic Pollutant
Ozone Depletion Potential

This product does not contain any known or suspected endocrine disruptors

This product does not contain any known or suspected substance

This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS**Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point.

Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

Not Regulated

IMDG/IMO

Not regulated

IATA

Not regulated

Special Precautions for User

No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
3-(Phenylsulphonyl)propionitrile	-	-		X	233-424-1	-	-	X	-		-	-

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 01-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet