

# Logger L2

## Simple and Effective Gas Monitoring

### Key Features

- **Specifically designed for harsh wastewater environments:** unique & proven robust design and double o-rings
- **Longer battery life:** single battery lasts up to 12 months
- **Simplifies record management:** increased memory up to 42,000 data points, proprietary OdaStat-G™ software free to download from website
- **Easy to read display:** large alpha numeric display
- **Two types of sensors:** LL (Long Term) Sensor or SL (Standard) Sensor
- **Certified intrinsically safe** to use in most commonly found hazardous environments
- **Real Time Data:** LL (Long Term) Sensor can be connected to the OdaTrak™ System to transmit gas data via a fibre optic cable

### Specifications

<b>Instrument Temp Range</b>	-20°C (-4°F) to 50°C (122°F)
<b>Sensor Temp Range</b>	-10°C (14°F) to 40°C (104°F)
<b>Instrument Relative Humidity Range</b>	15-90% non-condensing
<b>Ingress Protection</b>	IP66/68
<b>External Dimensions</b>	Diameter 62mm (2.44") x Height 196mm (7.72")
<b>Instrument Weight</b>	420 grams / 14.8 oz
<b>Power Supply</b>	Replaceable C-Size Lithium Battery (approved battery type/brand/ make only)
<b>Battery Life/Run Time</b>	Greater than 8 months (for life of lithium battery)
<b>Data Logging Capacity</b>	Up to 42,000 readings in total
<b>Interval</b>	Selectable from 1 second to 1 hour
<b>Data Logging</b>	Capacity > Logging interval of 1min = 29 days
<b>Duration Example</b>	Capacity > Logging interval of 5min = 6+ months



### Typical Applications

- Gas monitoring in manholes, drains and pits
- Odour monitoring in sewer and streaming water
- Ventilation pipes and rising mains
- Inside sewer collection lines
- Selected areas in treatment plants
- Asset management and odour control

## Models

Model	Gas	Part Number	Range	Resolution	Accuracy (Full Scale)	Accuracy (@ 20ppm gas, STP)
<b>Long Term Logger (LL)</b>	H <sub>2</sub> S Hydrogen Sulphide	ODALL-H2S-1000	0-1000 ppm	1 ppm	1% Full Scale	± 2ppm
		ODALL-H2S-200	0-200 ppm	0.1 ppm	1% Full Scale	
<b>Standard Logger (SL)</b>	H <sub>2</sub> S Hydrogen Sulphide	ODASL-H2S-2000	0-2000 ppm	1 ppm	2% Full Scale	
		ODASL-H2S-1000	0-1000 ppm	1 ppm	1% Full Scale	
		ODASL-H2S-200	0-200 ppm	0.1 ppm	1% Full Scale	
<b>Real Time Long Term Logger (LL)</b>	H <sub>2</sub> S Hydrogen Sulphide	ODASL-H2S-50	0-50 ppm	0.1 ppm	4% Full Scale	
		ODALLTF-H2S-1000	0-1000 ppm	1 ppm	1% Full Scale	
		ODALLTF-H2S-200	0-200 ppm	0.1 ppm	1% Full Scale	

Please refer to OdaTrak Data Sheet for further information on real time data access

**NOTE:** STP = Standard Temperature and Pressure: 20°C (68°F) @ absolute pressure 101.3 kPa (14.7 psi)

### Servicing

We recommend that the OdaLog® L2 is returned to an authorised OdaLog® service centre at least once every six months for a full inspection, calibration and linearity testing.

### Warranty

12 month warranty when used in accordance with the operator's manual (excluding calibration and freight costs).

### Software

The OdaLog® L2 needs to be used in conjunction with our proprietary software OdaStat-G™ for retrieval and analysis of all your logged data. The software may be downloaded, free-of-charge, from our website.

### Certification / Approval

IECEx ITA 08.0010X	Nemko08ATEX1270
Ex ia IIC T4 Ga	Ex II 2 G
(T <sub>AMB</sub> = -20°C to 50°C)	Ex ia IIC T4
IP66/68	IP66/68

In the interest of continued improvement, we reserve the right to change design features and specifications without prior notice.

Our ability to provide software and support is dependent on applicable export control laws (including those of the United States) and the export policy from time to time of Thermo Fisher Scientific Inc.

For more information, contact Thermo Fisher Scientific

**For Research Use Only. Not for use in diagnostic procedures.** © 2020 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **20200310-168rev2**

#### In Australia:

For customer service, call 1300-735-292  
To fax an order, use 1800-067-639  
To email an order: ordersANZ@thermofisher.com

#### In New Zealand:

For customer service, call 0800-933-966  
To fax an order, use 0800-329-246  
To email an order: ordersANZ@thermofisher.com

**ThermoFisher**  
SCIENTIFIC