

## Discover our organic peracids for oxidation chemistry

Organic peracids are reagents successfully used in a wide range of oxidizing reactions. They are mostly known for the oxidation of alkenes to epoxides (Prilezhaev reaction) and ketones into esters (Baeyer-Villiger reaction).

Amongst these peracids, *meta*-Chloroperbenzoic acid and Peracetic acid are prominent and popular due to their ease of handling.

We offer these acids and the full range of ingredients to synthesize other organic peracids, including Trifluoroperacetic acid and Perbenzoic acid, in a variety of pack sizes and grades. Discover these products below.

<b><i>meta</i>-Chloroperbenzoic and Peracetic acid</b>			
Product code	Product name	Pack size	CAS no.
255790250		25g	
255791000	3-Chloroperoxybenzoic acid, 70-75%, balance 3-Chlorobenzoic acid and water	100g	937-14-4
255795000		500g	
255790010		1kg	
257750250	Peroxyacetic acid, ca.35wt.% sol. in diluted acetic acid, stabilized	25mL	79-21-0
257751000		100mL	
257755000		500mL	

<b>Reagents suitable for synthesis of organic peracids</b>			
Product code	Product name	Pack size	CAS no.
125612500	Methanesulfonic acid, 99%, extra pure	250mL	75-75-2
125610010		1L	
125610051		5L	
202460250	Hydrogen peroxide, for analysis, 35 wt.% solution in water, stabilized	25mL	7722-84-1
202465000		500mL	
202460010		1L	
202460025		2.5L	
202460100		10L	
202460251	25L		
211780050	Dibenzoyl peroxide, 75%, remainder water	5g	94-36-0
211780010		1kg	
302865000	Hydrogen peroxide, pure, 50 wt% solution in water, stabilized	500mL	7722-84-1
302860025		2.5L	
125622500	Methanesulfonic acid, pure, 70% solution in water	250mL	75-75-2
125620010		1L	
125620050		5L	
149135000	Benzoic acid, 99%, extra pure	500g	65-85-0
149130010		1kg	
149130025		2.5kg	

## Reagents suitable for synthesis of organic peracids

Product code	Product name	Pack size	CAS no.
423470250		25g	
423475000	Benzoic acid, 99.6%, ACS reagent	500g	65-85-0
423470020		2kg	
423470100		10kg	
432970010		1L	
432970050	Methanesulfonic acid, 98%	5L	75-75-2
411881000		100g	
411885000	Hydrogen peroxide, ACS reagent, 30 wt% solution in water, nonstabilized	500g	7722-84-1
411880010		1kg	
411880025		2.5kg	
444380050		5L	
444380050	Hydrogen peroxide, technical, 35 wt% solution in water, stabilized	5L	7722-84-1
139720250		25g	
139721000		100g	
139725000	Trifluoroacetic acid, 99%, extra pure	500g	76-05-1
139720010		1kg	
139720025		2.5kg	
139720100		10kg	
147810250		25g	
147811000		100g	
147812501	Trifluoroacetic anhydride, 99+%	250g	76-05-1
147815000		500g	
147810025		2.5kg	
241022500		250g	
241020010	Urea hydrogen peroxide, 1 g tablets, stabilized, contains 35 wt% H <sub>2</sub> O <sub>2</sub>	1kg	124-43-6
241020051		5kg	



### Related Resource

#### **meta-Chloroperbenzoic Acid technical data sheet**

Use this data sheet to learn more about the important synthetic applications of *meta*-Chloroperbenzoic Acid.

Download a PDF via [www.acros.com](http://www.acros.com) > Tech support > Literature > List

For more information or for a complete list of our products suitable for oxidizing reactions, please visit our web site [www.acros.com](http://www.acros.com)



©2013 Thermo Fisher Scientific Inc. All rights reserved.  
These brands and trademarks are part of Thermo Fisher Scientific Inc. and its subsidiaries.

### Authorised distributor

#### In Australia:

For customer service, call 1300-735-292  
To fax an order, use 1800-067-639  
To email an order, [ordersau@thermofisher.com](mailto:ordersau@thermofisher.com)

#### In New Zealand:

For customer service, call 0800-933-966  
To fax an order, use 0800-329-246  
To email an order, [ordersnz@thermofisher.com](mailto:ordersnz@thermofisher.com)

**ThermoFisher**  
SCIENTIFIC