



OELD

Bluetooth-enabled local display



Maintenance from the palm of your hand

Bluetooth-enabled local display for Searchpoint Optima Plus and Searchline Excel

Now you can reduce time and cost by managing maintenance from your smartphone – with at-a-glance assurance of your gas safety.

The Optima Excel Local Display (OELD) is a smart junction box for the Searchpoint Optima Plus and Searchline Excel infrared detectors for flammable hydrocarbons. The OELD includes an LCD screen for gas information, a “traffic light” indicator for at-a-glance detector status, and Bluetooth® connectivity for simplified, non-intrusive maintenance. Simply pair the OELD with our intrinsically safe, ruggedized smartphone; then use the OELD smartphone app to interact with the gas detector from up to 10 meters (30 feet) away. For maximum flexibility, the gas detector can be mounted either directly or remotely to OELD to suit any situation.

Simplified maintenance with familiar smartphone technology

When you pair a smartphone with OELD, you can perform many tasks for your Searchpoint Optima Plus and Searchline Excel detectors wirelessly and from a convenient position.

Use the OELD mobile app to specify the target gas, configure alarm set points, perform one-man calibrations, access event logs, perform diagnostics, check detector status and more – with no need to go back and forth to the control room, or open the enclosure on your gas detector. That means no hot-work headaches like obtaining permits, declassifying the area or adding more manpower.


For detectors in hard-to-reach locations such as a duct, you can position the corresponding OELD remotely in an easy-to-access location and use the OELD smartphone app to interact with the detector wirelessly.

At-a-glance visibility

OELD has bright indicator lights visible from a distance, where green indicates normal operation, yellow indicates a fault or maintenance and red indicates an alarm. The LCD screen clearly displays real-time readings on detector status, including the gas being monitored, the local gas concentration and units of measurement – so you have easy access to status information.

Gas detection that fits the way you work

The OELD smartphone app delivers the familiar user experience you expect – combined with gas detection technology designed to keep you safe while making your job easier. It simplifies detector maintenance and is a cost-effective way to get even more value from your Searchpoint Optima Plus or Searchline Excel gas detectors.



EASE OF MAINTENANCE

- Simplified maintenance with familiar smartphone technology
- Non-intrusive interaction to reduce time and safety risk
- Easy access to hard-to-reach detectors
- Know before you go: pre-empt maintenance issues

LOCAL VISIBILITY OF SAFETY ISSUES

- Bright “traffic light” indicator for safety awareness
- Easier to locate a unit in fault/warning
- Real-time gas readings

FEATURES

- Robust Aluminium or Stainless steel housing
- Worldwide approvals for hazardous areas including ATEX, IECEx, cULus
- Green/yellow/red/blue multi-colour backlight to show status
- Bluetooth® (BLE) range up to 10 m (30 feet)
- Ingress protection IP66 / Type 4X
- Assessed to have no effect on functional safety of connected gas sensor
- Backward compatible with all versions of Searchpoint Optima Plus and Searchline Excel
- Secure access to OELD units can be easily managed by a primary user via the OELD app

| OELD SPECIFICATION | |
|------------------------------------|---|
| MATERIAL | Marine-grade aluminium alloy or 316 stainless steel with 5-coat painted finish |
| WEIGHT | Aluminium version 2.3 kg (5 lb), stainless steel version 5.0 kg (11 lb) |
| DIMENSIONS | 159 x 197 x 114 mm (6 ¼ x 7 ¾ x 4 ½ inch) |
| CABLE ENTRIES | 5 x M25 (ATEX/IECEX version) or 5 x ¾" NPT (cULus version). One reserved for sensor connection. 3 blanking plugs supplied for unused entries. |
| TERMINATION | 2 x pluggable rising-clamp type for connection to gas detector and field wiring. Accepts cable sizes of 0.5 to 2.5mm ² , 12 to 28 AWG |
| STORAGE TEMPERATURE | -40 to +65 °C (-40 to 149 °F) |
| OPERATIONAL TEMPERATURE | -40 to +65 °C (-40 to 149 °F) -60 to +65 °C (-76 to 149 °F) (CU TR-EX version only) |
| HUMIDITY | 0 to 99% RH (non-condensing) |
| DISPLAY | LCD module showing digital readout of sensor output, bar chart representation, units of measurement, status icons for alarm, maintenance and active Bluetooth connection. |
| CONFIGURABLE DISPLAYED INFORMATION | Displayed information fully user-configurable using the OELD mobile app. Units of measurement (select from %LEL, mg/m ³ , g/m ³ , %Vol, ppm, mA, A, kppm, LEL.m, dB, dBA, ppm.m) Gas name (up to 4 alpha-numeric characters) Measurement range |
| VISUAL INDICATION | Green/yellow/red/blue multi-colour backlight to display for indication of detector and OELD status. Green (normal) indication can be disabled via app. |
| POWER SUPPLY | 18 to 32 Vdc (24 Vdc nominal), <2 W |
| INTERFACES | Bluetooth® (BLE) non-intrusive connection to suitable mobile device running the OELD mobile app. Range up to 10 m (30 feet) (mobile device dependant) Internal RS-485 connection to Searchpoint Optima Plus or Searchline Excel via SHC-1 through the SHC Protection Device |
| ENVIRONMENTAL PROTECTION | IP66 / Type 4X |
| CORE APPROVALS | EN 50270: 2015 (EMC) IEC/EN/UL/CSA 61010 (Electrical Safety) |

| OELD SPECIFICATION | |
|---|---|
| | ATEX/IECEX DEMKO 16 ATEX 1693X IECEX [UL 16.0066X] ⊕ II 2 GD Ex db IIC T6 Ex tb IIIC T85 °C Tamb -40 to +65 °C EN 60079-29-1 Approved Accessory |
| SAFETY APPROVALS | cULus Class I, Div 1, A, B, C & D Class II, Div 1 F & G, Class III, Div 1 Tamb -55 to +65 °C Temp Code T6 Class I, Zone 1, AEx d IIC T6 Class I, Zone 21, AEx tb IIIC T6 ISA 60079-29-1 CU TR-Ex (Russian Customs Union), Tamb -60 to +65 °C* CCCF* Inmetro* NEPSI+* PESO+* |
| MARITIME APPROVALS* | Type approved to DNV, BV+, Lloyds+, ABS EN 60945 (EMC) IEC 60092-504 |
| OTHER APPROVALS | Bluetooth Certified, Radio Equipment Directive (RED), FCC+, country-specific wireless approvals |
| BLUETOOTH COMMUNICATION SECURITY | Certificate-based mutual authentication. Encryption to AES128 |
| *CONTACT HONEYWELL FOR AVAILABILITY +FLAMEPROOF VERSIONS ONLY | |

Honeywell Gas Detection

Honeywell is able to provide gas detection solutions to meet the requirements of all applications and industries.
Contact us in the following ways:

Authorised distributor

Order Placement:

For customer service, call 1300-735-292
To fax an order, use 1800-067-639
To email an order, ordersau@thermofisher.com

Contact Us:

For customer service, call 1300-735-292
For service and calibration, call 1300-736-767
To order online: thermofisher.com

ThermoFisher
SCIENTIFIC

Find out more:

www.honeywellanalytics.com
www.raesystems.com

Europe, Middle East, Africa

Life Safety Distribution GmbH
Javastrasse 2
8604 Hegnau
Switzerland
Tel: +41 (0)44 943 4300
Fax: +41 (0)44 943 4398
gasdetection@honeywell.com

Customer Service:

Tel: 00800 333 222 44
(Freephone number)
Tel: +41 44 943 4380
(Alternative number)
Fax: 00800 333 222 55
Middle East Tel: +971 4 450
5800 (Fixed Gas Detection)
Middle East Tel: +971 4 450
5852 (Portable Gas Detection)

www.honeywell.com

Americas

Honeywell Analytics Distribution Inc.
405 Barclay Blvd.
Lincolnshire, IL 60069
USA
Tel: +1 847 955 8200
Toll free: +1 800 538 0363
Fax: +1 847 955 8210
detectgas@honeywell.com

RAE Systems by Honeywell
Phone: 408.952.8200
Toll Free: 1.888.723.4800
Fax: 408.952.8480

Asia Pacific

Honeywell Industrial Safety
7F SangAm IT Tower,
434, Worldcupbuk-ro, Mapo-gu,
Seoul 03922,
Korea
Tel: +82 (0) 2 6909 0300
Fax: +82 (0) 2 2025 0328
India Tel: +91 124 4752700
China Tel: +86 10 5885 8788 3000
analytics.ap@honeywell.com

Technical Services:

EMEA: HAexpert@honeywell.com
US: ha.us.service@honeywell.com
AP: ha.ap.service@honeywell.com

0ELD_DS01175_01_1016_AMER_EN
Copyright © 2016 Honeywell International Inc.
All rights reserved.

Honeywell