

Pharmacy Refrigerators S Series

The Pinnacle purpose built pharmacy refrigerators have been designed in Australia to meet vaccine storage guidelines. Ideal for pharmacies and hospitals, they provide reliable temperature control and are easy to use.

Features:

- ✓ **QCPP Approved**
S Series refrigerators entered in the ARTG, 353488
- ✓ **+2°C to +8°C Operating Temperature Range**
With exclusive Blue Bottle product temperature simulation ²
- ✓ **Digital Controller** ¹
With battery backup providing 24 hours of temperature readings during power outage
- ✓ **Alarm System**
Alarms when door open and/or out of temperature range
- ✓ **Min / Max Temperature Logger**
- ✓ **Building Management System (BMS) Connection**
- ✓ **Fan Forced Cooling**
- ✓ **Internal Fan Switch**
Will turn off fan when door open
- ✓ **Energy Efficient and Quiet**
Double glazed Low-E glass doors and superior insulation
- ✓ **LED Lighting**
- ✓ **Door Lock**
- ✓ **Cable Port**
- ✓ **Cyclic Defrost**
- ✓ **Warranty**
24 months parts and labour



Optional Features:

- Low Temperature Cut-out
- 4G SMS Auto-dialler
- Additional Wire Coated Shelving
- Guardian T Alarm Testing System
- 7 Day Chart Recorder



Pharmacy Refrigerators S Series



Technical Specifications

Model	PR-S-36-1-GD	PR-S-66-1-GD	PR-S-90-1-GD	PR-S-145-1-GD	PR-S-300-1-GD	PR-S-430-1-GD						
Storage Capacity (litres)	36L	66L	90L	145L	300L	430L						
Voltage	220 VAC - 240 VAC 50Hz											
Amperage	0.8 Amps	0.8 Amps	0.8 Amps	1.05 Amps	1.5 Amps	1.7 Amps						
Size External (W x D x H)	450mm x 490mm x 535mm	450mm x 490mm x 730mm	490mm x 520mm x 820mm	610mm x 610mm x 820mm	610mm x 655mm x 1500mm	610mm x 700mm x 1870mm						
Weight	27kg	29.5kg	35kg	43kg	72kg	84kg						
Refrigerant	R134a											
Warranty Labour (refer to full warranty conditions)	24 months											
Warranty Parts (refer to full warranty conditions)	24 months											
Number of Shelves	2 + Base	2.5 + Base	2.5 + Base	3.5 + Base	6 + Base	8 + Base						
Alarm Points	+2°C to +8°C											
QCPP Approved and TGA Listed	✓	✓	✓	✓	✓	✓						
Digital Controller with LCD Display	Included											
Battery Back Up on Controller												
Min / Max Temperature Logging												
Door Open Alarm												
High Temperature Alarm												
Low Temperature Alarm												
Power Loss Alarm							BMS Only					
Remote Alarm Contacts (BMS)												
Internal Fan Switch												
Cable Port Hole 9.5mm												
Fan Forced Cooling												
Door Lock and Keys	Included											
High Efficiency Insulation												
Glass Door with Double Layer Low-E Glass												
Self Closing Doors												
LED Lighting												
Defrost	Cyclic											
Guardian T Alarm Testing Facility	N/A	N/A	N/A	Optional	Optional	Optional						
7 Day Chart Recorder	Optional											
Low Temperature Cut Out												
Auto Dialler												
Additional Shelving												
Customised Shelving												
Solid Door												
External Construction	Powder Coated Steel											
Door Hinge Right-hand Open	Standard											
Door Hinge Left-hand Open	Optional											
Adjustable Feet	Included											
Power Cord Length	2.5m											

Authorised distributor

In Australia:

For customer service, call 1300-735-292
To fax an order, use 1800-067-639
To email an order, ordersau@thermofisher.com

In New Zealand:

For customer service, call 0800-933-966
To fax an order, use 0800-329-246
To email an order, ordersnz@thermofisher.com