thermo scientific



Nunc products for in vitro fertilization

Security, safety, and reproducibility for your valuable samples



Certifications and testing

We do the testing so you don't have to

Thermo Scientific™ Nunc™ IVF products are produced under ISO 13485 guidelines to help ensure our customers receive a consistent, high-quality product.

Nunc IVF products are FDA-cleared and CE-marked Class II* for IVF use

Other certifications and testing include:

Mouse embryo assay (MEA)

Using the one-cell stage mouse embryo toxicity test, our criterion is that more than 80% of the fertilized eggs should develop to a fully expanded blastocyst after 96 hours. The MEA test is a release test, and the product will only be sold if it meets this criterion.

Human sperm survival assay (HSSA)

To pass the HSSA test, the motility of human sperm should be ≥70% after 24 hours of sample preparation. The HSSA test is a release test, and the product will only be sold if it meets this criterion.

Certificates of conformance

Every single lot of our IVF products is tested to help ensure that all products are safe. Testing results are available online at **thermofisher.com/nunccertificates**.

Biocompatible

All materials have successfully passed the USP biological reactivity Class VI-500 test (7 days implant) and ISO 10993 standards for cytotoxicity.

Sterile

Sterility is obtained through irradiation according to ISO 11137 (sterilization of health care products—requirements for validation and routine control—radiation sterilization).

Nonpyrogenic

Batches are tested using a limulus amebocyte lysate (LAL) test. The test is performed on representative samples using the Associates of Cape Cod™ LAL Detection Kit to quantify gram-negative endotoxins according to our approved test procedure "Use of Limulus Amebocyte Lysate for the Detection and Quantification of Bacterial Endotoxins," based on USP <85>. Products are considered nonpyrogenic at less than 20 endotoxin units/device (0.5 EU/mL).



^{*} In Europe CE-marked Class IIa.

Collection and preparation

The sensitive nature of IVF calls for extreme care during collection and preparation. Whether working with sperm samples or oocytes, viability is paramount and proper sample handling is essential. By emphasizing quality, we provide convenient and reliable products for collection and preparation of male and female gametes.

Thermo Scientific™ Nunc™ IVF Petri Dishes

- · Facilitates gas exchange with vented lid
- Choose the correct size for your application; available in 35 mm, 60 mm, and 90 mm sizes
- · Certificates of conformity available for every lot
- Sterile (sterility assurance level (SAL) 10⁻⁶)
- Nonpyrogenic
- USP Class VI test
- Release tests (MEA and HSSA)





Thermo Scientific™ Nunc™ IVF 11 mL Centrifuge Tubes

- Minimize product waste with package size of five tubes per pack
- · Quickly identify sample volume with clear graduations
- · Compatible with common centrifuge rotors
- · Certificates of conformity available for every lot
- Sterile (SAL 10⁻⁶)
- Nonpyrogenic
- USP Class VI test
- · Release tests (MEA and HSSA)



Embryo fertilization, maturation, and transfer

Thermo Scientific™ Nunc™ ICSI and Center Well dishes are CE-marked Class IIa as medical devices for IVF and were designed specifically for *in vitro* fertilization applications. The flat-bottom design optimizes heat transfer so you can maintain correct temperatures during protocols. Improved dish handling features make it safer and easier to grip, move, and manipulate your precious eggs and embryos.

Nunc IVF ICSI Dish

- Help maintain optimal temperature with true flat bottom
- Low profile provides optimal angles during the intracytoplasmic sperm injection (ICSI) process
- · Increased safety with easy grip design
- Certificates of conformity available for every lot
 - Sterile (SAL 10⁻⁶)
 - Nonpyrogenic
- Release tests (MEA and HSSA)

Nunc IVF Center Well Dish

- Ideal angle of reservoir well walls for locating and easy washing of samples
- Help maintain optimal temperature with true flat bottom
- Increased safety with easy grip design
- Certificates of conformity available for every lot
 - Sterile (SAL 10⁻⁶)
 - Nonpyrogenic
 - Release test (MEA)

Nunc IVF 4-Well Dish

- Help ensure proper orientation and prevent cross-contamination with notched lid and dish
- Help prevent scratches on well bottoms and maintain optimal temperature with 0.8 mm raised edge
- Certificates of conformity available for every lot
 - Sterile (SAL 10⁻⁶)
 - Nonpyrogenic
 - Release tests (MEA and HSSA)







thermo scientific

Product specifications and ordering information

CE-marked			
Nunc IVF Dishes (sterile)			
Description	ICSI dish	Center well dish	
Cat. No.	150265	150260	
Surface	Nontreated	Nontreated	
Air vent	Yes	Yes	
External dimensions, mm	9 x 51	16 x 55	
Units per pack/case	3/120	5/120	
Nunc IVF 4-Well Dishes (sterile)			
Description	4-well dish	4-well dish	
Cat. No.	144444	179830	
Surface	Nunclon™ Delta surface	Nontreated	
Culture area, cm²/well	1.9	1.9	
External dimensions, mm	66 x 66	66 x 66	
Units per pack/case	4/120	4/120	
Nunc IVF Petri Dishes (sterile)			
Traine IVI I our Brones (occine	7		
Description	35 x 10 mm dish	60 x 15 mm dish	90 x 17 mm dish
	·	60 x 15 mm dish 150270	90 x 17 mm dish 150360
Description	35 x 10 mm dish		
Description Cat. No.	35 x 10 mm dish 150255	150270	150360
Description Cat. No. Surface	35 x 10 mm dish 150255 Nontreated	150270 Nontreated	150360 Nontreated
Description Cat. No. Surface Air vent	35 x 10 mm dish 150255 Nontreated Yes	150270 Nontreated Yes	150360 Nontreated Yes
Description Cat. No. Surface Air vent Culture area, cm²/well	35 x 10 mm dish 150255 Nontreated Yes 8.8	150270 Nontreated Yes 21.5	150360 Nontreated Yes 56.7
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case Nunc IVF Tubes* (sterile)	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11 10/500	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case Nunc IVF Tubes* (sterile) Description	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11 10/500 11 mL centrifuge tube	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case Nunc IVF Tubes* (sterile) Description Cat. No.	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11 10/500 11 mL centrifuge tube 137860	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case Nunc IVF Tubes* (sterile) Description Cat. No. Cap type	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11 10/500 11 mL centrifuge tube 137860 Plug	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case Nunc IVF Tubes* (sterile) Description Cat. No. Cap type Material: tube/cap	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11 10/500 11 mL centrifuge tube 137860 Plug Polystyrene/polypropylene	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15
Description Cat. No. Surface Air vent Culture area, cm²/well External dimensions, mm Units per pack/case Nunc IVF Tubes* (sterile) Description Cat. No. Cap type Material: tube/cap Max. RCF tested	35 x 10 mm dish 150255 Nontreated Yes 8.8 35 x 11 10/500 11 mL centrifuge tube 137860 Plug Polystyrene/polypropylene 3,000 x g	Nontreated Yes 21.5 54 x 14	150360 Nontreated Yes 56.7 88 x 15

 $[\]ensuremath{^{*}}$ Not available for sale in the US; therefore, not FDA-cleared.

