

Sodium Phosphate, Dibasic, 7-Hydrate,
Crystal
U.S.P.
Endotoxin Tested



Material No.: 3816-07
Revision No.: 0

Product Specification

Meets U.S.P Requirements, GMP Manufactured Product

Test	Specification
USP - Assay (Na_2HPO_4) (dried basis)	98.0 - 100.5 %
USP - Arsenic (As)	≤ 16 ppm
USP - Chloride (Cl)	≤ 0.06 %
USP - Endotoxin Concentration (2.5 EU/g max.)	Passes Test
USP - Identification	Passes Test
USP - Insoluble Substances	≤ 0.4 %
USP - Loss on Drying	43.0 - 50.0 %
USP - Sulfate (SO_4)	≤ 0.2 %

GMP Manufactured Product

Bulk Pharmaceutical Chemical

CAUTION: For Manufacturing, processing or repackaging

No Class 1,2,3 or other solvents are used or produced in the manufacturing or purification of the product.

Elemental Impurities (USP 232, EP 5.20) - Information on elemental impurities for this product is available on the associated Product Regulatory Data Sheet and elemental impurity profile report.

Packaging Site: Paris Mfg Ctr & DC


Jamie Ethier
Vice President Global Quality

For questions on this Product Specification please contact Technical Services at 855.282.6867 or +1.610.386.1700

Avantor Performance Materials, LLC

100 Mansford Rd, Suite 200, Radnor, PA 19087. U.S.A. Phone 610.386.1700