

Thermo Scientific Model 42i-Y

NO_y Analyzer Chemiluminescent Gas Analyzer

The Thermo Scientific™ Model 42i-Y NO_y Analyzer utilizes chemiluminescence technology to measure the amount of nitrogen oxides in the air from sub-ppb levels up to 1000 ppb.

Features

- Ethernet connectivity for efficient remote access
- Enhanced user interface with one button programming and large display screen
- Flash memory for increased data storage and user downloadable software
- Enhanced electronics design optimizes product commonality
- Improved layout for easier accessibility to components

Introduction

The Thermo Scientific Model 42i-Y Analyzer is a single chamber, single photomultiplier tube design that measures NO_y which includes most oxides of nitrogen with the exception of NH₃ and N₂O.



Dual range and auto range are standard features in this instrument. Because the instrument is operated continuously in the NO_y mode, the response time is less than 10 seconds.

Temperature and pressure correction are standard features. User settable alarm levels for concentration and for a wide variety of internal diagnostics are available from an easy to follow menu structure.

This state-of-the-art gas analyzer offers features such as an Ethernet port as well as flash memory for increased data storage and field upgradability.

Ethernet connectivity provides efficient remote access, allowing the user to download measurement information directly from the instrument without having to be on-site.

You can easily program short-cut keys to allow you to jump directly to frequently accessed functions, menus or screens. The larger interface screen can display measurement information and status, while viewing menu and operational screens.



Thermo Scientific™ Model 42i-Y NO_y Analyzer

Thermo Scientific Model 42i-Y NO_x Analyzer

Specifications	
Preset ranges	0-5, 10, 20, 50, 100, 200, 500, 1,000 ppb 0-10, 20, 50, 100, 200, 500, 1000 and 2,000 mg/m ³
Zero noise	< 25 ppt RMS (120 second averaging time)
Lower detectable limit	< 50 ppt (120 second averaging time)
Zero drift (24 hour)	Negligible
Span drift (24 hour)	+/-1% full scale
Response time	60 seconds (10 second averaging time)
Precision	+/-0.4 ppb (500 ppb range)
Linearity	+/-1% full scale
Sample flow rate	1 LPM
Operating temperature	59°F to 95°F (15°C to 35°C) Performance or 32°F to 113°F (0°C to 45°C) Operating
Power requirements	100 VAC, 115 VAC, 220-240 VAC +/-10% @ 300W
Size and weight	16.75" (W) x 8.62" (H) x 23" (D), 55 lbs. 425 mm (W) x 219 mm (H) x 584 mm (D), 25 kg
Outputs	Selectable Voltage, RS232/RS485, TCP/IP, 10 Status Relays, and Power Fail Indication (standard). 0-20 or 4-20 mA Isolated Current Output (optional)
Inputs	16 Digital inputs (standard), 8 0-10Vdc analog inputs (optional)

Ordering information

Model 42i-Y NO_x Analyzer

Choose from the following configurations/options to customize your own Model 42i-Y Analyzer

1. Voltage options

A = 115 VAC 60 Hz

B = 220 VAC 50 Hz

C = 220 VAC 60 Hz

D = 115 VAC 50 Hz

J = 100 VAC 50/60 Hz

2. Internal zero/span

N = No zero/span assembly (standard)

Z = Internal zero span assembly

3. Converter options

M = Molybdenum (standard)

4. Sample handling

S = Standard plumbing (standard)

5. Ozone handling

D = Drierite scrubber (standard)

P = Permeation dryer

6. Optional I/O

A = None (standard)

C = I/O expansion board (4-20mA outputs—6 channels
0-10v inputs-8 channels)

7. Mounting Hardware

A = Bench mounting and ears/handles, EIA

Other options

Teflon particulate filter

Ozone particulate filter

Rack mounts

Rear extender

Your Order Code: 42i-Y

--	--	--	--	--	--	--

USA

27 Forge Parkway
Franklin, MA 02038
Ph: (866) 282-0430
Fax: (508) 520-2800
orders.aqi@thermofisher.com

India

Industrial Unit No.101+130,
Plot No.C-56/1, TTC Industrial
area, MIDC-Turbhe,
New Mumbai 400 703, India
Ph: +91 82 9199 0337
INinfo@thermofisher.com

China

8/F Bldg C of Global Trade Ctr,
No.36, North 3rd Ring Road,
Dong Cheng District
Beijing, China 100013
Ph: +86 10 84193588
info.eid.china@thermofisher.com

Europe

Ion Path, Road Three,
Winsford, Cheshire CW73GA UK
Ph: +44 1606 548700
Fax: +44 1606 548711
sales.epm.uk@thermofisher.com

Find out more at thermofisher.com/cleanair

ThermoFisher
SCIENTIFIC