Thermo Scientific NMR Reaction Monitoring Accessory

Add the dimension of time to chemistry teaching

The reaction monitoring accessory for Thermo Scientific™ picoSpin™ 45 and picoSpin 80 benchtop NMR spectrometers brings a new dimension to your chemistry classroom. This low-cost accessory facilitates an online flow configuration with the benchtop NMR spectrometer, enabling students to experience chemical reactions as they occur.





Adding a reaction monitoring accessory to the picoSpin 45 or the picoSpin 80 NMR spectrometer gives your students valuable hands-on experience of chemical reaction mechanisms, kinetics, thermodynamics, and other physical organic properties to complement the core of your undergraduate chemistry curriculum.

The instrument's fluid capillary system is perfectly suited to an online flow configuration; no need for fragile NMR tubes and messy preparation when the time comes for the next timed sampling of the reaction mixture.

Watch the chemical reaction unfold before your eyes as NMR data is automatically exported, processed, and analyzed, to produce kinetic curves plotted in real-time. Gain insight to the reaction pathway and mechanisms involved in a way that the classroom cannot provide alone.



Product Specifications

Valve Assembly

- VICI switching valve model: C22Z-2184
 - 4-port 2-position
 - Maximum pressure: 250 psi
 - Universal actuator
 - 24 DC power supply
 - 110/220 VAC, 50/60 Hz, 60 Watts
- Spectrometer communications cable (6')
- Idex Relief Valve model: U-456
 - 100 psi (7 bar) actuation pressure
 - Automatic reset after actuation
- Tubing
 - 1/16" o.d., 0.02" i.d. PTFE
 - Extra tubing included for customized lengths
- Connectors
 - 1/16" tube size
 - Material: PEEK
 - Extra nuts and ferrules included
- Physical
 - Dimensions: $9"H \times 5"W \times 11"D$ (23 cm \times 13 cm \times 28 cm)
 - Weight: 2.9 lbs (1.3 kg)
 - Distance between reaction chemical reaction vessel and spectrometer: 23" (58 cm) to 46" (91 cm)



Software

- Requires software version 0.9.3 on the picoSpin NMR Spectrometer
- Mestrelab Mnova[™] Reaction Monitoring add-on included


Documentation

- Lesson Plan
- Set-up instructions

Optional Pump

- · Positive displacement (piston) style
- Single head design with stepper motor drive
- PEEK fluid path
- 1/16" o.d. tubing inlet and outlet
- Flow Rate: up to 5 mL/min.
- Pressure: 100 psi over flow range
- External Power Supply 115–260 VAC/50–60 Hz





www.thermoscientific.com/picospin

©2015 Thermo Fisher Scientific Inc. All rights reserved. Mnova is a trademark of Mestrelab Research, Inc.
All other trademarks are the property of Thermo Fisher Scientific and its subsidiaries. Specifications, terms and pricing are subject to change.
Not all products are available in all countries. Please consult your local sales representative for details.

Africa +43 1 333 50 34 0 Australia +61 3 9757 4300 Austria +43 810 282 206 Belgium +32 53 73 42 41 Canada +1 800 530 8447 China +86 21 6865 4588

Denmark +45 70 23 62 60 Europe-Other +43 1 333 50 34 0 Finland/Norway/Sweden +46 8 556 468 00 France +33 1 60 92 48 00 Germany +49 6103 408 1014 India +91 22 6742 9494 Italy +39 02 950 591 Japan +81 45 453 9100 Latin America +1 561 688 8700 Middle East +43 1 333 50 34 0 Netherlands +31 76 579 55 55 New Zealand +64 9 980 6700 Russia/CIS +43 1 333 50 34 0 Spain +34 914 845 965 Switzerland +41 61 716 77 00 UK +44 1442 233555 USA +1 800 532 4752

