



Quality Controls

MAS Diabetes Max quality controls

Do more with fewer steps and less waste

The Thermo Scientific™ MAS™ quality controls (QC) portfolio now includes a new MAS™ Diabetes Max option, offering load-and-go barcoded* tubes to help automate your QC workflow and maximize productivity.



More productivity

MAS Diabetes Max tubes load directly into a broad range of instruments to reduce manual steps, lowering the risk of errors and improving turnaround time.

- **Streamlined workflow.** Time-saving load-and-go tubes are ready to use straight from refrigeration
- **Confidence.** Load-and-go tubes eliminate manual pour-off to decrease the risk of handling errors
- **Automated QC.** Barcoded labels streamline programming and identification for traceability every step of the process

More sustainability

Minimize laboratory waste with the new MAS Diabetes Max tube format.

- **Eliminate** dead volume with convenient, pre-measured tubes
- **Remove the need** for micro cups and pipettes

*Barcodes available for selected instruments

More options for MAS Diabetes

Thermo Scientific MAS Diabetes quality control solutions are independent third-party controls suitable for the rigors of clinical use. With a two-year shelf-life and ready-to-use design, you can always count on reliable performance every time for better patient management.

- **Full commutability**
- **Excellent reproducibility**
- **Accurate and stable values**



Lower CV

Improved reliability and repeatability for minimal variations with new lots of manufactured QC.

Human Matrix

The MAS Diabetes control matrix is human whole blood-based and best mimics the behavior of a patient sample.

Part Number	Product Name	Level	Bottles & Size	Storage & Stability	Matrix
DBCL-MP	MAS Diabetes control	1-2	6 x 1mL - bottles	24 month shelf life @ -25 to -15°C from date of manufacture 60 days unopened @ 2 to 8°C 30 days open-vial @ 2 to 8°C	Whole blood
B40000687	MAS Diabetes Max control	1-2	6 x 2mL - tubes	24 month shelf life @ -25 to -15°C from date of manufacture 60 days unopened @ 2 to 8°C 30 days open-vial @ 2 to 8°C	Whole blood



Learn more at thermofisher.com/masdiabetesmax

thermoscientific