Detection of Organochlorine Pesticides by GC-ECD Following U.S. EPA Method 8081

Andrea Caruso and Massimo Santoro Thermo Fisher Scientific, Milan, Italy

Keywords

Chromeleon chromatography data system, electron capture detector, environmental, gas chromatography, organochlorine pesticides, U.S. EPA 8081

Goal

To accurately detect and quantitate organochlorinated pesticides in extracts from solid and liquid matrices using gas chromatography (GC) with an electron capture detector (ECD).

Introduction

Organochlorine insecticides are among the oldest and most toxic synthetic pesticides. First introduced in the 1940s, these chemicals were used extensively until most of them were banned in the 1970s and 1980s due to their health risks. Organochlorines are neurotoxic and some organochlorine compounds are suspected carcinogens. Organochlorines, such as DDT and lindane, also break down slowly once released. This persistence in the environment leads these organochlorines to be incorporated into ecosystems and food chains where they remain for years. For these reasons, the presence of these analytes in water, soils, and other solids must be strictly controlled and various analytical methods have been developed to extract and purify them from various matrixes. The presence of chlorine atoms in their structure makes organochlorines an excellent target for an electron capture detector (ECD)-a sensitive, cheaper, and easier-to-operate alternative to mass spectrometry. This application note describes a convenient method for analyzing and quantifying organochlorinated pesticides via GC and ECD.

Experimental Conditions

Sample Preparation

Matrix extraction and purification are performed following U.S. Enivronmental Protection Agency Method 8081 guidelines.



Instrument Setup

A method was developed for the Thermo Scientific[™] TRACE[™] 1310 Gas Chromatograph used with a Thermo Scientific[™] TriPlus RSH[™] Autosampler, an Instant Connect Split/Splitless (SSL) Injector and an Instant Connect Electron Capture Detector (ECD) for TRACE 1300 Series GC.

| Recommended Conditions | | | | |
|------------------------|---|--|--|--|
| TRACE 1310 GC | | | | |
| Injection Volume: | 1 μL | | | |
| Liner: | Splitless with glass wool (P/N 453A1925) | | | |
| Carrier Gas: | Helium, constant flow, 1 mL/min | | | |
| Column Type: | 30 m, 0.25 mm, 0.25 µm, TG-5MS (P/N 26098-420) | | | |
| Column Oven: | Initial 100 °C, hold 1.0 min. Ramp at 20.0 °C/min up to 180°C. Ramp at 5.0 °C/min to 270 °C. Ramp at 20.0 °C/min to 320 °C. Hold 2.0 min. | | | |
| Instant Connect S | SSL Injector | | | |
| Inlet Temperature: | 250 °C | | | |
| Mode: | Splitless, 2 min; split flow 50 mL/min | | | |
| Instant Connect ECD | | | | |
| Temperature: | 320 °C | | | |
| Makeup Gas: | Nitrogen, 15 mL/min makeup flow | | | |
| | | | | |



Method

The experimental method follows the guidelines for U.S. EPA method 8081, with slight modifications to the GC ramp and use of a column with 0.25 µm film thickness to guarantee better separation. The TriPlus RSH Autosampler is operated in liquid injection mode. All other parameters are those indicated by U.S. EPA Method 8081. Ethyl acetate is used as the solvent for washing the syringe. The standards used for calibration are ordered from Restek. All samples are acquired and processed using the Thermo Scientific[™] Dionex[™] Chromeleon[™] 7.2 chromatography data system (CDS) software.

Results and Discussion

Separation, linearity, repeatability, and limit of detection were assessed for each compound.

The chromatogram of a 5 ppb calibration point is shown in Figure 2.







Figure 1. TRACE 1310 GC and TriPlus RSH Autosampler.



| Т | able | e 1. | Cali | bration | results | for | the | anal | yzed | com | ponen | ts. |
|---|------|------|------|---------|---------|-----|-----|------|------|-----|-------|-----|
|---|------|------|------|---------|---------|-----|-----|------|------|-----|-------|-----|

| Peak Name | Retention Time (min.) | Coefficient of Determination | C1 (Slope) |
|---------------------|--------------------------|------------------------------|------------|
| α-BHC | 9.623 | 0.99978 | 0.0231 |
| γ-BHC | 10.227 | 0.99996 | 0.0122 |
| β-BHC | 10.430 | 0.99983 | 0.0215 |
| δ-BHC | 10.992 | 0.99992 | 0.0193 |
| Heptachlor | 12.383 | 0.99984 | 0.0200 |
| Aldrin | 13.413 | 0.99957 | 0.0227 |
| Heptachlor epoxide | 14.602 | 0.99964 | 0.0208 |
| γ-Chlordane | 15.337 | 0.99987 | 0.0226 |
| Endosulfan I | 15.748 | 0.99923 | 0.0181 |
| α-Chlordane | 15.818 | 0.99968 | 0.0222 |
| DDE | 16.433 | 0.99973 | 0.0225 |
| Dieldrin | 16.578 | 0.99983 | 0.0207 |
| Endrin | 17.295 | 0.99997 | 0.0159 |
| Endosulfan II | 17.577 | 0.99986 | 0.0201 |
| DDD | 17.797 | 0.99919 | 0.0172 |
| Endrin aldehyde | 18.187 | 0.99985 | 0.0184 |
| DDT | 18.967 | 0.99883 | 0.0113 |
| Endosulfan sulphate | 19.040 | 0.99856 | 0.0187 |
| Methoxychlor | 20.550 | 0.99998 | 0.0174 |
| Endrin ketone | 20.958 | 0.99889 | 0.0079 |

As outlined in the U.S. EPA 8081 method, endosulfan I and α -chlordane and DDT and endosulfan sulfate tend to coelute on the 5% phenyl 95% dimethylpolysiloxane stationary phase used for this application. As shown in Figure 3, good resolution was achieved with a score of 1.0 for the α -chlordane-endosulfan I pair and 0.9 for DDT-endosulfan sulphate.

Compounds were quantitated using an external calibration method and a seven-point curve. The seven-point calibration curve ranged from 0.1 to 100 ppb with concentrations of 0.1, 0.5, 1, 2, 5, 10, 100 ppb for each of the analytes. The results are reported in Table 1 and Figure 4.






Figure 3. Resolution of "critical couples".

Aldrin

2 50





External

BackDetector

Figure 4. Calibration curves for six of the analyzed pesticides.

Application Note 10401

The limit of detection was assessed by applying the U.S. EPA guidelines, performing 14 replicate injections, calculating the standard deviation of the response, and then multiplying that value for the "t" value at 99% confidence level, related to the number of replicate injections. The results are reported in Table 2.

Table 2. Limit of detection.

| | Std. Dev | No. of Repeats | t(14-1) | Calculated LOD (ppb) |
|---------------------|----------|----------------------|---------|----------------------------|
| α-BHC | 0.009 | 14 | 2.650 | 0.023 |
| γ-ΒΗϹ | 0.009 | 14 | 2.650 | 0.025 |
| β-BHC | 0.007 | 14 | 2.650 | 0.018 |
| δ-BHC | 0.007 | 14 | 2.650 | 0.019 |
| Heptachlor | 0.011 | 14 | 2.650 | 0.029 |
| Aldrin | 0.005 | 14 | 2.650 | 0.013 |
| Heptachlor epoxide | 0.008 | 14 | 2.650 | 0.021 |
| γ-Chlordane | 0.073 | 14 | 2.650 | 0.194 |
| Endosulfan I | 0.013 | 14 | 2.650 | 0.034 |
| α -Chlordane | 0.019 | 14 | 2.650 | 0.050 |
| DDE | 0.008 | 14 | 2.650 | 0.020 |
| Dieldrin | 0.011 | 14 | 2.650 | 0.030 |
| Endrin | 0.018 | 14 | 2.650 | 0.049 |
| Endosulfan II | 0.023 | 14 | 2.650 | 0.062 |
| DDD | 0.009 | 14 | 2.650 | 0.025 |
| Endrin aldehyde | 0.01 | 14 | 2.650 | 0.026 |
| DDT | 0.008 | 14 | 2.650 | 0.020 |
| Endosulfan sulphate | 0.01 | 14 | 2.650 | 0.028 |
| Methoxychlor | 0.013 | 14 | 2.650 | 0.035 |
| Endrin ketone | 0.039 | 14 | 2.650 | 0.103 |

The repeatability of both retention times and areas has been tested as well on 10 ppb injections (number of injections = 10).The results are reported in Table 3.

Table 3. Retention time and area repeatability (n = 10).

| | Ret. Time RSD% | Peak Area RSD% | |
|---------------------|----------------|----------------|--|
| α-BHC | 0.03 | 2.41 | |
| ү-ВНС | 0.04 | 2.69 | |
| β-ВНС | 0.03 | 2.02 | |
| δ-BHC | 0.03 | 1.59 | |
| Heptachlor | 0.03 | 2.40 | |
| Aldrin | 0.02 | 2.16 | |
| Heptachlor epoxide | 0.02 | 1.97 | |
| γ-Chlordane | 0.02 | 2.47 | |
| Endosulfan I | 0.02 | 2.04 | |
| α -Chlordane | 0.02 | 1.75 | |
| DDE | 0.02 | 2.09 | |
| Dieldrin | 0.02 | 2.18 | |
| Endrin | 0.02 | 2.00 | |
| Endosulfan II | 0.02 | 2.82 | |
| DDD | 0.02 | 2.18 | |
| Endrin aldehyde | 0.02 | 2.66 | |
| DDT | 0.02 | 4.76 | |
| Endosulfan sulphate | 0.02 | 1.71 | |
| Methoxychlor | 0.02 | 2.25 | |
| Endrin ketone | 0.02 | 4.14 | |

Conclusion

This application demonstrated the performance of the TRACE 1300 Series GC, equipped with an Instant Connect SSL Injector and Instant Connect ECD for the analysis of organochlorine pesticides. The system shows excellent results in terms of linearity, sensitivity, and reproducibility. These results indicate that this system is a sensitive, cheaper and simpler alternative to mass spectrometry for assessing the presence of organochlorine residues, as a result of the excellent selectivity of the ECD for chlorinated compounds.

www.thermofisher.com

©2016 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Africa +43 1 333 50 34 0 Australia +61 3 9757 4300 Austria +43 810 282 206 Belgium +32 53 73 42 41 Canada +1 800 530 8447 China 800 810 5118 (free call domestic) 400 650 5118 Denmark +45 70 23 62 60 Europe-Other +43 1 333 50 34 0 Finland +358 9 3291 0200 France +33 1 60 92 48 00 Germany +49 6103 408 1014 India +91 22 6742 9494 Italy +39 02 950 591 Japan +81 45 453 9100 Latin America +1 561 688 8700 Middle East +43 1 333 50 34 0 Netherlands +31 76 579 55 55 New Zealand +64 9 980 6700 Norway +46 8 556 468 00 Russia/ClS +43 1 333 50 34 0 Singapore +65 6289 1190 Spain +34 914 845 965 Sweden +46 8 556 468 00 Switzerland +41 61 716 77 00 UK +44 1442 233555 USA +1 800 532 4752

AN10401-EN 08/16S

