# thermo scientific



### Authors

Joachim Hinrichs, Thermo Fisher Scientific, Bremen, Germany

# **Keywords**

GD-MS, Nickel Alloys, modulated discharge, Pulsed

# Goal

To achieve superior performance of the Thermo Scientific Element GD Plus GD-MS for the analysis of Ni alloys in modulated mode, compared to the bulk analysis of conductive metals with continuous DC GD-MS.

# Introduction

The Thermo Scientific<sup>™</sup> Element<sup>™</sup> GD GD-MS is used and well accepted for trace metal determination in Ni alloys controlled by aerospace regulations. With the upgrade to a modulated supply of the GD source, the precision achievable on the Thermo Scientific<sup>™</sup> Element<sup>™</sup> GD Plus GD-MS needs to be verified. The accuracy is dominated by the calibration materials used and is equivalent to continuous DC operation.




Figure 1. Schematics of pulsed discharge operation.



# Method

The Certified Reference Material (CRM) BAS346A is a nickel superalloy (IN100) with a well characterized set of trace metals important for materials used in the aerospace industry. Therefore this CRM has been used exemplarily to investigate the precision achievable in routine GD-MS quality control tasks.

Repeat analyses were performed including sample preparation by wet grinding the sample on SiC paper grit 80, followed by a washing step with de-ionized water. As a finish, the sample surface was soaked with iso-propanole and blown dry in a nitrogen stream.

#### Table 2. Precision data of repeat analysis of CRM BAS346A.

#### Table 1. Instrumental parameters.

Parameter	Value
Discharge voltage	800 V
Pulse frequency	4 kHz
Pulse duration	40 µs
Average discharge current	~15 mA
Matrix intensity	~1·10 <sup>10</sup> cps (MR)
Presputter time	6 min
Acquisition time	6 min
Anode consumables	Stainless steel

Element	Isotope (Resolution)	Certified value [µg⋅g⁻¹]	RSD of all 16 spots	RSD of 6 spots with flow tube and cap exchange	RSD of 4 spots with cap exchange	RSD of 6 spots without any part exchanged
В	11 (MR)	~200	4.2%	4.0%	1.3%	1.2%
С	12 (MR)	~1500	3.2%	4.3%	2.9%	0.8%
Mg	24 (MR)	$130 \pm 5\%$	1.2%	1.1%	0.7%	1.2%
Ca	44 (MR)	~20	8%	11%	6%	6%
Zn	66 (MR)	$28.8 \pm 5\%$	2.5%	2.3%	1.1%	1.1%
Ga	69 (MR)	$49.6 \pm 4\%$	1.5%	1.8%	0.7%	0.9%
As	75 (MR)	$50.4 \pm 5\%$	1.2%	0.6%	1.0%	1.1%
Se	82 (MR)	5.7 ± 14%	10%	13%	8%	9%
Ag	107 (MR)	42.5 ± 2%	2.4%	2.0%	1.6%	0.7%
Cd	111 (MR)	0.37 ± 11%	9%	9%	9%	11%
In	115 (MR)	~20	1.6%	1.6%	1.1%	1.1%
Sn	119 (MR)	93 ± 9%	0.9%	1.0%	1.0%	0.9%
Sb	121 (MR)	$45 \pm 9\%$	1.2%	0.9%	1.1%	1.2%
Те	130 (MR)	$9.3 \pm 9\%$	7.7%	10.6%	5.5%	3.8%
TI	205 (MR)	$1.9 \pm 16\%$	3.0%	3.4%	0.7%	3.3%
Pb	208 (MR)	$22.2 \pm 5\%$	1.4%	1.7%	0.6%	1.1%
Bi	209 (MR)	$10.3 \pm 7\%$	2.4%	3.0%	1.1%	2.4%

# **Results**

- The results in Table 2 indicate excellent reproducibility for 16 repeat runs including sample preparation.
- Presputter and acquisition times in modulated (pulsed) mode are comparable to continuous modulated operation.
- Best precisions are observed when no source parts are exchanged. This allows for extended analysis (>2 h sputter time, equivalent to approximately 10 sample runs) of similar sample types.
- The typical procedure of changing the anode cap does not significantly impact the precision.
- The exchange of the flow tube shows a visible impact, but still gives precisions similar or better than the reference values itself. As the flow tube receives only small amounts of redeposited sample material, it is typically exchanged on a daily basis.
- A long-term test run on one spot without sample change showed that even after 4 hours the measured concentrations are within a 10% limit. About half of this variation originates from the deep crater eroded, which is never achieved in routine work with ~10–15 minutes sputter time per sample.
- The methodology shown here is subject to ongoing and further optimization, depending on individual lab requirements.

# Conclusion

The Element GD Plus GD-MS offers a solution for highly precise trace metal determination in nickel super alloys. Its much lower sputter rate at a similar level of intensity compared to the non-modulated mode yields an excellent spot-to-spot as well as per-spot precision.

# Find out more at thermofisher.com/GD-MS

©2018 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representatives for details. **AB30490-EN 1118S** 

