



The IonPac ICE-AS6 ion-exclusion column provides fast analysis of aliphatic organic acids and alcohols in complex or high-ionic strength samples. A moderately hydrophobic resin functionalized with sulfonic acid and carboxylic acid groups improves selectivity. The column's unique polymeric structure helps control hydrophobic retention and provides easy column cleanup.

Now sold under the
Thermo Scientific brand

Thermo
SCIENTIFIC




Figure 1 Separation of low-molecular weight organic acids on an IonPac ICE-AS6 ion-exclusion column in less than 20 minutes.

The IonPac ICE-AS6 ion-exclusion column is designed for the determination of aliphatic organic acids and alcohols in complex or high-ionic strength samples, including food and beverage products, biological samples, fermentation processes, industrial process liquors, and waste waters. It provides improved peak efficiency and unique selectivity for applications typically performed using ICE-AS1 or ICE-AS5 columns.

The ICE-AS6 column is a moderately hydrophobic resin functionalized with sulfonic acid and carboxylic acid groups to improve selectivity. The unique polymeric structure of the ICE-AS6 allows HPLC solvents to control hydrophobic retention and provide effective column cleanup.

SUPERIOR CHROMATOGRAPHIC PERFORMANCE

- Weakly ionized acids are separated by pK_a differences.
- Unique selectivity using ion exclusion plus hydrogen bonding and hydrophobic adsorption.
- Strong acid anions such as chloride and sulfate elute in the void.
- Achieves difficult separations, including tartrate from citrate, glycolate from lactate and formate, lactate from malate, and formate from succinate.
- Uses a wide range of acid eluents and detection methods.
- Uses HPLC solvents to control hydrophobic retention of higher molecular weight acids or for effective column cleanup.

Column: IonPac ICE-AS6
 Eluent: 1.0mM Heptafluorobutyric acid
 Flow Rate: 1.0 mL/min
 Detection: Suppressed conductivity
 AMMS-ICE

Sample: 0.25% Sulfuric acid, 50 μ L

Peaks:
 1. Citric
 2. Malic
 3. Glycolic
 4. Lactic
 5. Acetic
 6. Succinic




Figure 2 Ion exclusion allows the determination of organic acids in sulfuric acid and eliminates sulfate interference.

Column: IonPac ICE-AS6
 Eluent: 0.4 mM Heptafluorobutyric acid
 Flow Rate: 1.0 mL/min
 Inj. Volume: 50 μ L
 Detection: Suppressed conductivity
 AMMS-ICE

Peaks:
 1. Inorganics
 2. Inorganics
 3. Maleic
 4. Malonic
 5. Citric
 6. Malic
 7. Quinic
 8. Glycolic
 9. Formic
 10. Lactic
 11. Unknown
 12. Acetic
 13. Unknown
 14. Shikimic
 15. Fumaric
 16. Propionic




Figure 3 Determination of organic acids in coffee.

Column: IonPac ICE-AS6
 Eluent: 0.4 mM Heptafluorobutyric acid
 Flow Rate: 1.0 mL/min
 Inj. Volume: 50 μ L
 Detection: Suppressed conductivity
 AMMS-ICE

Peaks:
 1. Inorganics
 2. Tartaric
 3. Galacturonic
 4. Citric
 5. Malic
 6. Formic
 7. Acetic
 8. Unknown




Figure 4 Determination of trace organic acids in grape juice using suppressed conductivity detection.

UNIQUE SELECTIVITY

The retention mechanisms operating in the ICE-AS6 include:

- Ion exclusion
- Hydrogen bonding
- Hydrophobic interaction

The ICE-AS6 resin is derivatized with sulfonic acid and carboxylic acid functional groups. The ion-exclusion mechanism causes strong acid anions such as sulfate to be eluted in the column void volume, as illustrated in Figure 2. Due to the added hydrogen bonding and adsorption retention mechanisms, the ICE-AS6 has significantly higher retention for hydroxylated weak acids than is typically observed on ion-exclusion columns. Figure 1

illustrates the unique selectivity of the ICE-AS6 for aliphatic organic acids and hydroxy organic acids.

Use the ICE-AS6 for diverse sample matrices including:

- Brines
- Mineral acids
- Waste water
- Power plant water
- Foods and beverages
- Kraft liquors
- Soil extracts

RESISTS FOULING

The polymer packing in the ICE-AS6 resists fouling and allows the analysis of a wide range of complex samples, as shown in Figure 3.

INCREASED SENSITIVITY WITH SUPPRESSED CONDUCTIVITY DETECTION

The ICE-AS6 is designed to be used with a wide range of detectors including conductivity, UV, refractive index, and amperometry. For sensitive detection of aliphatic organic acids and hydroxy organic acids, the ICE-AS6 is designed to be used with the AMMS-ICE, which is a low void volume, high-capacity eluent suppressor. The AMMS-ICE suppressor reduces the background conductivity of the eluent while increasing the conductivity of the analytes to provide a stable baseline and high signal-to-noise ratio (see Figures 1– 4).

USE ICE-AS6 WITH A WIDE RANGE OF ACID ELUENTS AND DETECTORS

The ICE-AS6 can be used with any typical strong acid eluent. A high-acid eluent concentration is used to retain and separate organic acids with low pK_a s such as glucuronic, tartaric, citric, and malonic acids, as illustrated in Figure 5. These high eluent concentrations can be used with amperometric, UV, or refractive index detection. Figure 6 illustrates the selectivity achieved for aliphatic alcohols when chromatography with the ICE-AS6 is coupled with pulsed amperometric detection.

SOLVENT-COMPATIBLE PACKING

The IonPac ICE-AS6 column is compatible with HPLC solvents up to 20%, including methanol, isopropanol, and acetonitrile. Organic solvents can be used to decrease the hydrophobic retention of strongly retained organic acids, as illustrated in Figure 7. For columns fouled with hydrophobic matrix components, organic solvents can be used for effective column cleanup.




Figure 5 Determination of weakly ionized organic acids using UV detection.




Figure 6 Determination of aliphatic alcohols using pulsed amperometric detection.




Figure 7 Organic solvent is used to elute highly retained hydrophobic organic acids.

SPECIFICATIONS

Column

Analytical Column Dimensions:

9 x 250 mm

Maximum Operating Pressure:

5.6 MPa (800 psi)

Eluent Compatibility:

pH 0–7, (Use eluents containing only hydronium ion as the cation. Avoid eluents containing sodium, potassium, etc.)

0–20% HPLC Solvents

Column Construction:

PEEK (Polyetheretherketone) with 10–32 threaded ferrule-style end fittings. All components are nonmetallic.

Substrate

Bead Diameter (μm):

8.0

Bead Type:

Microporous

Crosslinking (%DVB):

8%

Functional Group

Capacity ($\mu\text{eq}/\text{column}$):

27 meq (9 x 250 mm)

Ion-Exchange Group:

Sulfonic and carboxylic acid

Surface Characteristics:

Moderately hydrophobic

ORDERING INFORMATION

In the U.S., call 1-800-346-6390, or contact the Dionex Regional Office nearest you. Outside the U.S., order the IonPac ICE-AS6 column through your local Dionex office or distributor. Refer to the part numbers below.

For suppressed conductivity detection, the IonPac ICE-AS6 column should be used with the AMMS-ICE MicroMembrane™ Suppressor.

IonPac ICE-AS6 Analytical Column

(9 x 250 mm) P/N 46023

AMMS-ICE MicroMembrane Suppressor

(For use with ion exclusion columns.) P/N 37107

9-mm ICE-AS6 Hardware (0.62-in. O.D. Tube)

Bed support (frit and seal washer) P/N 48238

Zitex® bed support (for ICE) P/N 48297

End fitting P/N 48298

Dionex Corporation
1228 Titan Way
P.O. Box 3603
Sunnyvale, CA
94088-3603
(408) 737-0700

Dionex Corporation
Salt Lake City Technical Center
1515 West 2200 South, Suite A
Sunnyvale, CA
84119-1484
(801) 972-9292

Dionex U.S. Regional Offices
Sunnyvale, CA (408) 737-8522
Westmont, IL (630) 789-3660
Houston, TX (281) 847-5652
Atlanta, GA (770) 432-8100
Marlton, NJ (609) 596-0600

Dionex International Subsidiaries
Austria (01) 616 51 25 Belgium (015) 203800 Canada (905) 844-9650 France 01 39 46 08 40 Germany 06126-991-0
Italy (06) 66030052 Japan (06) 6885-1213 The Netherlands (0161) 43 43 03 Switzerland (062) 205 99 66 United Kingdom (01276) 691722
* Designed, developed, and manufactured under an NSAI registered ISO 9001 Quality System.
<http://www.dionex.com>

