

## RF 2000 Fluorescence Detector



*The RF 2000 Fluorescence Detector is designed for use with Dionex Summit™ HPLC systems and DX-500 and DX-600 IC systems. Two independent monochrometers provide the highest reproducibility of excitation and emission wavelengths, thereby facilitating the adaptation of methods to the optimum detection condition for individual components. The RF 2000 is integrated with the Summit HPLC system using the CHROMELEON™ chromatography data system, which further enhances productivity and provides compliance with GLP requirements.*

Now sold under the  
Thermo Scientific brand

**Thermo**  
SCIENTIFIC

### Highest Resolution

The RF 2000 has optimized optical and electronic systems to provide exceptionally high sensitivity. For the Raman spectrum of water, a signal-to-noise ratio better than 300:1 is easily obtained. With the appropriate wavelength settings (both excitation and emission), trace components can be easily detected.

### Greater Wavelength Accuracy and Reproducibility

The RF 2000 offers unsurpassed wavelength accuracy and achieves an excellent reproducibility of  $\pm 0.2$  nm, ensuring that comparable samples produce comparable results.

### Wavelength Selection

The optimum excitation and emission wavelengths for different fluorescent compounds vary significantly. By time-programming both the excitation and emission wavelengths, the RF 2000 permits the response of each component to be optimized for selective trace analysis. In addition to chromatograms, spectra can be recorded within seconds using the wavelength-scanning feature. Comparing these spectra with a library created from known standards allows identification of the analyzed substances and facilitates method development.



## Increasing Productivity by External Control and Automation

Controlling the RF 2000 with CHROMELEON chromatography data system software notably increases productivity in the laboratory. All detector parameters (sensitivity and wavelength) are not only time-programmed but also documented in the automatically generated Audit Trail to provide full GLP compliance.

## Applications

A typical application for fluorescence detection is the determination of polycyclic aromatic hydrocarbons (PAHs) in drinking water, wastewater, and ground and surface waters as

specified by regulatory agencies. Analyzing these complex mixtures requires quick and precise wavelength switching to determine all components near the detection limit within the shortest possible time. Figure 1 shows chromatograms of PAH analysis A) without wavelength switching and B) with wavelength switching.

Other typical applications include the analysis of aflatoxins, carbamates, vitamins, and amino acids in the toxicological, environmental, and food sectors.

## RF 2000 SPECIFICATIONS

### Light Source:

High precision xenon lamp, 150 W

### Optical System:

Concave, blazed holographic grating monochrometers for both excitation and emission beams

### Excitation/Emission Wavelength Range:

200–650 nm (optional: 200–900 nm)

### Spectral Bandwidth:

15 nm for both excitation and emission

### Wavelength Accuracy:

± 2.0 nm

### Wavelength Reproducibility:

± 0.2 nm

### Sensitivity:

S/N ratio > 300 for the Raman line of water (350 nm excitation wavelength, 1.5 sec time constant)

### Cell Volume:

12 µL

### Maximum Cell Pressure:

20 bar (290 psi)

### Wavelength Scanning:

Possible for excitation and emission wavelengths

### Time-Programmed Functions:

Excitation and emission wavelengths (up to 32 steps), response switching, wavelength scan, and autozero

### Dimensions (h x w x d):

20.5 x 26 x 52 cm  
(8.1 x 10.2 x 20.5 in.)

### Weight:

17 kg (37.4 lb)

### Operational Temperature Range:

4–35 °C

### Power Requirements:

100–240 V, 50/60 Hz, 350 VA




Figure 1. PAH analysis A) without wavelength switching and B) with wavelength switching.



Summit and CHROMELEON are trademarks of Dionex Corporation.



**Dionex Corporation**  
1228 Titan Way  
P.O. Box 3603  
Sunnyvale, CA  
94088-3603  
(408) 737-0700

**Dionex Corporation**  
Salt Lake City Technical Center  
1515 West 2200 South, Suite A  
Salt Lake City, UT  
84119-1484  
(801) 972-9292

**Dionex U.S. Regional Offices**  
Sunnyvale, CA (408) 737-8522  
Westmont, IL (630) 789-3660  
Houston, TX (281) 847-5652  
Atlanta, GA (770) 432-8100  
Marlton, NJ (856) 596-0600

**Dionex International Subsidiaries**  
Austria (01) 616 51 25 Belgium (015) 203800 Canada (905) 844-9650 China (852) 2428 3282 Denmark (45) 36 36 90 90 France 01 39 30 01 10  
Germany 06126-991-0 Italy (06) 66 51 50 52 Japan (06) 6885-1213 The Netherlands (0161) 43 43 03 Switzerland (062) 205 99 66  
United Kingdom (01276) 691722

\* Designed, developed, and manufactured under an NSAI registered ISO 9001 Quality System.

