

ALFAAL19745

Magnesium tert-butoxide

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 叔丁醇镁
Magnesium tert-butoxide

Cat No. : L19745
CAS No 32149-57-8
Molecular Formula C₈ H₁₈ Mg O₂

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Powder Solid

Appearance
Yellow

Odor
No information available

Emergency Overview

Flammable solid. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation. Reacts violently with water. Moisture sensitive. Air sensitive.

Classification of the substance or mixture

| | |
|--|------------|
| Flammable solids. | Category 2 |
| Acute Inhalation Toxicity - Dusts and Mists | Category 4 |
| Skin Corrosion/Irritation | Category 2 |
| Serious Eye Damage/Eye Irritation | Category 2 |
| Specific target organ toxicity - (single exposure) | Category 3 |

Label Elements



Signal Word**Warning****Hazard Statements**

H228 - Flammable solid
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H332 - Harmful if inhaled
H335 - May cause respiratory irritation

Precautionary Statements**Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P240 - Ground and bond container and receiving equipment
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a POISON CENTER or doctor if you feel unwell
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material. Reacts violently with water.

Health Hazards

Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Reacts violently with water. Is not likely mobile in the environment. Reacts violently with water.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component | CAS No | Weight % |
|----------------------------------|------------|----------|
| Magnesium 2-methylpropan-2-olate | 32149-57-8 | >95 |

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention.

Inhalation

Remove to fresh air. Get medical attention. If not breathing, give artificial respiration.

Magnesium tert-butoxide

Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

Most important symptoms and effects

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam. CO₂, dry chemical, dry sand, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

Water.

Specific Hazards Arising from the Chemical

Flammable. Thermal decomposition can lead to release of irritating gases and vapors. In the event of fire and/or explosion do not breathe fumes. Reacts violently with water.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal. Do not expose spill to water.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Do not get in eyes, on skin, or on clothing. Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid ingestion and inhalation. Avoid dust formation. Do not allow contact with water.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from water or moist air. Flammables area. Keep away from open flames, hot surfaces and sources of ignition. Store under an inert atmosphere.

Specific Use(s)

Use in laboratories

Magnesium tert-butoxide

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Engineering Measures

Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments |
|-----------------------------|--------------------------------------|-----------------|-------------|-----------------------|
| Nitrile rubber Viton (R) | See manufacturers recommendations | - | EN 374 | (minimum requirement) |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: low boiling organic solvent Type AX Brown conforming to EN371 Type A Brown

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Magnesium tert-butoxide

| | | |
|--|-----------------------------|--|
| Appearance | Yellow | |
| Physical State | Powder Solid | |
| Odor | No information available | |
| Odor Threshold | No data available | |
| pH | No information available | |
| Melting Point/Range | No data available | |
| Softening Point | No data available | |
| Boiling Point/Range | No information available | |
| Flash Point | No information available | Method - No information available |
| Evaporation Rate | Not applicable | Solid |
| Flammability (solid,gas) | No information available | |
| Explosion Limits | No data available | |
| Vapor Pressure | No data available | |
| Vapor Density | Not applicable | Solid |
| Specific Gravity / Density | No data available | |
| Bulk Density | No data available | |
| Water Solubility | Reacts violently with water | |
| Solubility in other solvents | No information available | |
| Partition Coefficient (n-octanol/water) | | |
| Autoignition Temperature | Not applicable | |
| Decomposition Temperature | No data available | |
| Viscosity | Not applicable | Solid |
| Explosive Properties | No information available | |
| Oxidizing Properties | No information available | |
| Molecular Formula | C8 H18 Mg O2 | |
| Molecular Weight | 170.53 | |

SECTION 10. STABILITY AND REACTIVITY

| | |
|---|--|
| Stability | Moisture sensitive. Air sensitive. |
| Hazardous Reactions | None under normal processing. Reacts violently with water. |
| Hazardous Polymerization | Hazardous polymerization does not occur. |
| Conditions to Avoid | Incompatible products. Excess heat. Avoid dust formation. Exposure to moist air or water. Exposure to moisture. |
| Materials to avoid | Strong oxidizing agents. |
| Hazardous Decomposition Products | Carbon monoxide (CO). Carbon dioxide (CO ₂). Thermal decomposition can lead to release of irritating gases and vapors. |

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

| | |
|--|--|
| (a) acute toxicity; | |
| (b) skin corrosion/irritation; | Category 2 |
| (c) serious eye damage/irritation; | Category 2 |
| (d) respiratory or skin sensitization; | |
| Respiratory | Based on available data, the classification criteria are not met |

Magnesium tert-butoxide

| | |
|---|---|
| Skin | Based on available data, the classification criteria are not met |
| (e) germ cell mutagenicity; | Based on available data, the classification criteria are not met |
| (f) carcinogenicity; | Based on available data, the classification criteria are not met There are no known carcinogenic chemicals in this product |
| (g) reproductive toxicity; | Based on available data, the classification criteria are not met |
| (h) STOT-single exposure; | Category 3 |
| Results / Target organs | Respiratory system |
| (i) STOT-repeated exposure; | Based on available data, the classification criteria are not met |
| Target Organs | None known. |
| (j) aspiration hazard; | Not applicable Solid |
| Other Adverse Effects | The toxicological properties have not been fully investigated. |
| Symptoms / effects, both acute and delayed | Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting |

SECTION 12. ECOLOGICAL INFORMATION

| | |
|--|--|
| Ecotoxicity effects | Do not empty into drains. Reacts with water so no ecotoxicity data for the substance is available. |
| Persistence and Degradability | No information available |
| Persistence | Persistence is unlikely, based on information available. |
| Degradability | No information available, Reacts with water. |
| Degradation in sewage treatment plant | No information available. Reacts violently with water. |
| Bioaccumulative Potential | Product does not bioaccumulate due to reaction with water |
| Mobility in soil | Reacts violently with water Is not likely mobile in the environment |
| Endocrine Disruptor Information | This product does not contain any known or suspected endocrine disruptors |
| Persistent Organic Pollutant | This product does not contain any known or suspected substance |
| Ozone Depletion Potential | This product does not contain any known or suspected substance |

SECTION 13. DISPOSAL CONSIDERATIONS

| | |
|--|--|
| Waste from Residues/Unused Products | Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. |
| Contaminated Packaging | Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and |

Magnesium tert-butoxide

empty container away from heat and sources of ignition.

Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN3205
Proper Shipping Name Alkaline earth metal alcoholates, n.o.s
Hazard Class 4.2
Packing Group II

IMDG/IMO

UN-No UN3205
Proper Shipping Name Alkaline earth metal alcoholates, n.o.s
Hazard Class 4.2
Packing Group II

IATA

UN-No UN3205
Proper Shipping Name Alkaline earth metal alcoholates, n.o.s
Hazard Class 4.2
Packing Group II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|----------------------------------|---|---|------|-------|-----------|------|-----|-------|------|------|------|------|
| Magnesium 2-methylpropan-2-olate | - | - | X | - | 250-931-3 | - | - | - | - | | - | - |

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 23-Mar-2012
Revision Date 27-Apr-2024
Revision Summary New emergency telephone response service provider.

Magnesium tert-butoxide

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadviser - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet