Headspace Grade Solvents for Trace Level Analyte Detection

Subhra Bhattacharya, Eric Oliver, and Stephen C. Roemer ¹Thermo Fisher Scientific - Global Chemicals, One Reagent Lane, Fair Lawn, NJ 07410

ABSTRACT

Headspace gas chromatography is the most suited technique for the analysis of highly volatile organics that are partitioned efficiently into the gas phase from the solid or liquid matrices. Detection of residual solvents in pharmaceuticals is performed by headspace GC analysis. The residual solvents in pharmaceuticals are defined as organic volatile chemicals that are used or produced in the manufacturing of drug substances or excipients, or in the preparation of drug products per United States Pharmacopoeia (USP) and International Conference on Harmonization (ICH). The residual solvents are difficult to remove completely from the drug products and therefore the amount of residual solvents should be evaluated by headspace GC analysis. USP and ICH guidelines recommend the acceptable amounts of residual solvents in pharmaceutical for the safety of the patient. Residual solvents are categorized as Class 1 (most toxic), Class 2 and Class 3 according to the toxicity effects. In headspace GC analysis, the pharmaceutical compound of interest is often dissolved in a high boiling solvent to assess the amount of volatile components. Although water is the most common solvent for this type of analysis, other solvents are frequently used when the pharmaceutical compounds are not soluble in water.

We have evaluated five different solvents for headspace GC analysis. The solvents are water, dimethyl sulfoxide (DMSO), N,N-dimethylformamide (DMF), N,N-dimethylacetamide (DMAC) and 1-methyl-2-pyrrolidinone (NMP). Allergy medications such as Allegra, Alavert, Flonas Zyrtec, Claritin and Wal-Dryl were purchased from Walgreens. Residual solvent analysis of these overthe-counter allergy medications was performed using different headspace solvents. Our results showed that all five solvents are suitable for detection of trace level volatile organic components from the pharmaceutical compounds.

MATERIAL AND METHODS

- Solvents: All GC headspace grade solvents were from Fisher Scientific including water (Cat. # W10-1), DMSO (Cat. # D139-1), DMAC (Cat. # D160-1), DMF (Cat. # D133-1), and NMP (Cat. # N140-1)
- Standards: Class 1 (Cat. # PHR1063) and Class 2A (Cat. # PHR1064) residual solvent standard mixes were obtained from Sigma-Aldrich, St. Louis, MO
- \bullet Samples: Allergy and pain medications were purchased from Walgreens (Table 1)

Sample preparation:


- 1. Two to ten tablets were dissolved in 10 mL of water and the mix centrifuged.
 Supernatant (2 mL) was transferred to a 20 mL headspace GC (HSGC) vial.
- 2. Two to ten tablets were dissolved in a mixture of water and DMSO (50:50). The mixture
 was centrifuged and the supernatant transferred to a 20 mL HSGC vial.


Table 1. Allergy and Pain Medications Analyzed

Tablets	Active Ingredients
Advil	Chlorpheniramine maleate 4 mg
Allegra	Fexofenadine HCl 180 mg
Alavert	Loratadine 10 mg
Alka-Seltzer plus (liquid filled capsules)	Acetaminophen 325 mg, Doxylamine succinate (6.25 mg)
Claritin	Loratadine 10 mg
Flonase	Fexofenadine HCl 180 mg
Mucinex	Phenylephrine HCl 5 mg
Wal-Dryl	Diphenhydramine HCl 25 mg
Wal-Phed	Chlorpheniramine maleate 4 mg


Headspace GC-FID Run Conditions


- · Instrument: Thermo Scientific Trace GC Ultra equipped with headspace RSH auto sampler
- Column: ZB-624, 30 m x 0.25 mm x 1.4 micron
- Flow: 1 mL/min
- Detector: flame ionization detector (FID)
- Detector temperature: 250° C
- Injector temperature: 200° C
- Syringe volume: 2.5 mL
- Injection volume: 1.0 mL
- Split ratio: 20
- Agitator temperature: 90° C
- Incubation time: 5 min.
- Hydrogen: 35, Air: 350, Nitrogen: 40 (mL/min)
- Oven temperature:
- Initial 40° C & hold 5 min
- Ramp 10° C per min
- Final 240° C & hold 10 min



































Table 2. Residual Solvent Peaks Information

 Retention time, m/z, identity and amount of residual solvents in the allergy medication tested

Retention Time	m/z	Identity	Quantification
1.94	48	Unknown	**
2.19	58	Acetone	406.93 nmol in Allegra
2.30	84	Methylene chloride	7.98 nmol in Allegra
2.57	60	Acetic acid	**
2.69	88	Ethyl acetate	55.78 nmol in Allegra
4.83	73	DMF	**

RESULTS AND DISCUSSION

- Headspace GC-FID run of Class 1 and Class 2A residual standards (without any dilution) in DMSO is shown in Fig. 1. All five peaks of the Class 1 residual solvent mixture were detected using the method; the 14 peaks from the Class 2A residual solvent mixture were also detected in the same method. The residual solvent peaks are eluted before the DMSO peak (at 10.27 min).
- Fig. 2 shows an overlay of the expanded chromatograms of DMSO solvent with Class 1 residual solvent standard mix, namely 1 - 5 ppm concentration, 100 - 500 ppm concentration, and the Class 2A standard mix at 100 - 1600 ppm concentration. These data clearly show that trace amounts of extraneous peaks are not present in the HSGC solvent.
- Class 2A residual solvent standard mix was diluted further, and the final concentration of components were within the 1 - 16 ppm range. A comparison of this lower concentration standard mix relative to the DMSO blank shows a clean solvent baseline without interference from extraneous peaks (Fig. 3).
- Figs. 4 7 show the blank HSGC-FID run of each solvent and the Class 1 and Class 2A standards in the same solvent. No extraneous peaks were observed in any of the solvents.
- Fig. 8 shows the overlay of HSGC-FID chromatograms of Allegra, Alavert, Alka-Seltzer and Wal-Dryl tablets extracted in water. For Alka-Seltzer, a carryover peak of DMF at 9.30 min was observed. In Allegra, two peaks were observed at 2.79 min and 5.31 min; those peaks were not found in Alavert, Alka-Seltzer and Wal-Dryl.
- No significant peaks were observed in Claritin, Advil and Wal-Phed (data not shown).
- Fig. 9 provides an overlay of HSGC-MS chromatograms of Allegra, Alavert, Alka-Seltzer and Wal-Dryl tablets extracted in water. The early eluting residual solvent peaks in full scale are shown in the upper panel. The lower panel provides the expanded chromatograms. Allegra medication shows peaks at 1.94, 2.19, 2.30, 2.69, and 4.83 min. In Alavert, the peaks at 1.96, 2.30, and 4.85 min were also observed.Similar peaks were found in Wal-Dryl and Alka-Seltzer medications.
- Fig. 10 shows HSGC-MS of Flonase, Allegra, Alavert, Zyrtec, and Mucinex in water/DMSO solution. The broad peak at 5.9 min is DMSO. Allegra, Zyrtec and Mucinex each showed a peak at 1.92 min. This peak was identified as m/z 48; however, positive identity has not yet been attained (Table 2).
- Both water and water/DMSO extracts clearly indicated the presence of peaks at 1.9, 2.2 and 2.6 min (Figs. 9,10). In addition, water-extracted samples also showed peaks at 2.3 and 4.8 min. Mass spectra of these peaks are provided in Fig. 11, and were identified by NIST library search (Table 2).
- Trace samples of acetone, ethyl acetate and methylene chloride were run to confirm the presence of those peaks in the allergy medication. The presence of all three solvents was confirmed by exact match of the retention time and mass spectra profile. Acetone and ethyl acetate are Class 3 solvents and both methylene chloride and DMF are Class 2 solvents per USP and ICH guideline with a limit of 600 ppm and 880 ppm, respectively. The amounts of residual solvents detected were well below the limits. We quantified acetone, ethyl acetate and methylene chloride from Allegra medication (Table 2); DMF and other solvents were not quantified.

Conclusions

- The new GC headspace grade solvents from Fisher Scientific are all highly purified and suitable for analyzing residual solvents in pharmaceuticals.
- No extraneous peaks were found when blank solvents were analyzed by GC-FID-HS.
- All five solvents provided an interference free base line and are suitable for trace analyte detection.
- HSGC analysis of allergy medications demonstrated clearly that detection of trace level impurity peaks could be accomplished using these headspace grade solvents.

www.thermoscientific.com

©2016 Thermo Fisher Scientific Inc. All rights reserved. ISO is a trademark of the International Standards Organization. All other trademarks are the property of Thermo Fisher Scientific and its subsidiaries. This information is presented as an example of the capabilities of Thermo Fisher Scientific products. It is not intended to encourage use of these products in any manners that might infringe the intellectual property rights of others. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Africa +43 1 333 50 34 0 Australia +61 3 9757 4300 Austria +43 810 282 206 Belgium +32 53 73 42 41 Brazil +55 11 2730 3006

Canada +1 800 530 8447 **China** 800 810 5118 (free call domestic) 400 650 5118

Denmark +45 70 23 62 60 Europe-Other +43 1 333 50 34 0 Finland +358 10 3292 200 France +33 1 60 92 48 00 Germany +49 6103 408 1014 India +91 22 6742 9494 Italy +39 02 950 591 Japan +81 6 6885 1213 Korea +82 2 3420 8600 Latin America +1 561 688 8700 Middle East +43 1 333 50 34 0 Netherlands +31 76 579 55 55 New Zealand +64 9 980 6700 Norway +46 8 556 468 00 Russia/CIS +43 1 333 50 34 0 Singapore +65 6289 1190 Sweden +46 8 556 468 00 Switzerland +41 61 716 77 00 Taiwan +886 2 8751 6655 UK/Ireland +44 1442 233555 USA +1 800 532 4752

Thermo Fisher Scientific,

Sunnyvale, CA USA is ISO 9001 Certified.

Thermo

A Thermo Fisher Scientific Brand