thermoscientific



Thermo Scientific ClipTip pipetting systems

Sealed in security | Feel the difference



Breakthrough ClipTip technology

Achieve newfound confidence with the **Thermo Scientific™ ClipTip™ pipetting system** that locks tips firmly in place so they will not loosen or fall off, regardless of application pressure. You can actually feel the tips lock firmly in place with a light touch, making daily pipetting a totally new experience. No more banging tips on your pipette to ensure that they are properly attached and sealed.



Worry-free pipetting is finally here with the only tip that clips.

Eliminate the frustration of banging, checking and rocking tips on your pipette

With a light touch, each tip is 'clipped' securely on the pipette.

Minimize the risk of loose or leaking tips

When ClipTip pipette tips are on, they are sealed and will not loosen. The ClipTip pipetting system remains sealed until you decide to eject tips, even in the most comprehensive applications, including multiple tip touches and mixing cycles.

Enable consistent and reproducible pipetting from user to user

Higher-quality results and more efficient research.

- 4 | E1-ClipTip Electronic Pipettes
- 6 | F1-ClipTip Manual Pipettes
- 12 | F1-ClipTip System Order Information
- 14 | E1-ClipTip System Order Information

You'll feel the difference the first time you use the Thermo Scientific ClipTip pipetting system.

It is a challenge to ensure a quality seal in daily pipetting.

The ideal solution is for the pipette and tip to form a system that increases confidence in reproducibility, reduces forces required to attach and detach the system, and secures the best possible accuracy and precision.



FRICTION SEALING SYSTEMS

Pipettes with a friction-seal system rely on a user's force to attach tips to the pipette, which varies from user to user.

- Increased tip attachment and ejection forces
- Loose tips that can drop off or leak air
- Decreased confidence in reproducibility of results
- Premature tip cone wear

CLIPTIP SYSTEM

By clipping the tips to the pipette with a light touch the ClipTip system optimizes comfort, accuracy and precision

- Extremely low tip attachment and ejection forces
- Reproducibility you can count on
- Complete seal on every channel
- No loose tips





Electronic pipettes

Feel the difference with E1-ClipTip Pipettes

An optimal solution for complex protocols

When combined with interlocking ClipTip technology, the electronic pipetting action and flexible user interface of the E1-ClipTip System enable efficient use of precious time and resources.

Electronic operation helps you enjoy pipetting again

Designed for optimum comfort and ease of use, the electronic tip ejection and index finger pipetting action let your thumb relax during pipetting.

Ideal operation for multiple users and environments

Personalized user interface and password protection ensure unified operation among multiple users.

E1-ClipTip Equalizer – a perfect choice for sample transfers between various labware formats

E1-ClipTip Equalizer pipette with adjustable tip spacing allows you to set the distance between tips simply by sliding the scale to expand and contract to your desired setting. This means fewer repetitions for multiple applications.

Connected Pipetting via Bluetooth or USB cable

Connect your E1-ClipTip pipette to the My Pipette Creator app on your PC to easily create programs, to download pre-written protocols, and to share protocols between pipettes and colleagues.

Enjoy pipetting again

One pipette, one movement, one press of the trigger

Convenient Li-ion battery

Quickly recharge for long-lasting performance

Maximized comfort

Electronic index finger pipetting action minimizes thumb strain and an adjustable finger rest allows for optimal pipetting position for both left and right-handed users.

Rotating display, unique multichannel ski boot design, and short single-channel barrel offer visibility and a neutral pipetting position in any working environment.

Program storage

Store up to 30 protocols in your pipette - and the rest in Thermo Fisher Cloud. Programming protocols on your PC with My Pipette Creator application reduces strain on your eyes and thumbs, also allowing you to transfer protocols to multiple pipettes, instead of programming individually.

Pipette tracking

Service and calibration trackers remind you when the pipette needs to be re-calibrated or sent for service



Effortless ejection

Electronic tip ejection is effortless, and intuitive user interface prevents any accidental tip ejection whenever there is liquid inside the tips

A pipette for multiple applications

Choose from single channels, 8–16 channel multichannels, or 6–12 channel adjustable tip spacing multichannel pipettes within the volume range of 0.5– 1250 µL based on your application and consumables type

Customizable calibrations

Higher quality results with customizable calibrations. Improve accuracy by creating different calibrations for liquids with varying viscosity or when using special tips.

E1-Cliptip pipette

Requires 87% lower tip attachment forces and up to 93% lower tip ejection forces compared to other adjustable tip spacing pipettes²

¹ E1-ClipTip electronic pipettes are warranteed to be free from defects in material and workmanship for a period of two years from date of purchase. Two-year warranty applies to pipettes that have been registered, one-year warranty to non-registered. To register the pipette and for more information, visit www.thermoscientific.com/pipettewarranty

² Thermo Scientific Smart Note. Tip attachment and ejection force vary significantly among different adjustable tip spacing pipette brands. 2016.

Intuitive operation & optimal functions to feel comfortable from day one




Pipettes that work the way you do

The icon-based user interface offers clear, fast and easy operation with the same basic functions that you are familiar with on your current pipette.

My Pipette Function allows you to customize your main menu view to include your most-used functions. You can also create shortcuts for your preferred programs and pipetting functions.


Now with BLUETOOTH connectivity and 5 user profiles

Two programming options:



Presets for everyday ready-to-go mode

Simple and quick pipette settings for your most common applications, such as forward and reverse pipetting and multidispensing. Adjust the volume and speed, and you're ready to go.



Matrix for complex applications

The step-based programming is an excellent option when a variety of pipetting functions is required in a unique order. Rather than trying to make a pre-set function work, you can select any of the functional steps — such as Fill, Dispense, Mix, Multi, or Purge —together while setting specific volumes and speeds for each.



Choose to lock important protocol settings

Safeguard the integrity of your assays by utilizing password protection for saved settings such as calibration and stored programs, as well as a customized main menu view to deliver consistent, efficient operation regardless of the user.

Introducing web-based My Pipette[™] Creator pipetting app

Boost your productivity and efficiency and connect your E1-ClipTip pipette via Bluetooth™ or USB cable to the My Pipette™ Creator app on your PC. My Pipette™ Creator enables you to easily create programs and download pre-written protocols that can be shared with colleagues and multiple pipettes at once.





Download protocols

Download pre-programmed protocols for your E1-ClipTip pipettes and favorite Thermo Fisher Scientific reagent kits from the Protocol Library. Save time, enhance consistency, minimize programming errors, and help ensure optimal results.



Program protocols

Reduce the strain on your eyes and thumbs by programming protocols on your PC. Minimize programming errors and enable consistent results by transferring protocols to multiple pipettes, instead of programming each pipette individually.



Share protocols

Share protocols with your colleagues in another lab, location or country.



Manage pipettes

Connect multiple E1-ClipTip pipettes to the My Pipette Creator application for efficient, centralized programming that provides consistent results and improved collaboration.

Learn more at thermofisher.com/mypipette

Sample transfers have never been this simple

Do sample transfers require several different pipette models and take up too much time?

Perform sample transfers between virtually any tube, rack, microplate, or horizontal gel box.

Adjustable tip spacing allows you to set the distance between tips simply by sliding the scale to expand and contract to your desired setting.

The unique equalizer window links the tip spacing scale to the particular application. This means fewer repetitions for multiple applications.

Transfer multiple samples between different lab formats at once



Increased research efficiency and quality

Over **80%** time savings and fewer repetitions compared to single channel pipettes*



^{*}Compared to a manual single channel pipette filling a 96-well microplate from microcentrifuge tubes. See Thermo Scientific Smart Note: Is there an easier and more efficient way to transfer liquids between various labware formats, than using traditional handheld pipettes? 2014.

Speed up sample transfer time and reduce repitition

E1-ClipTi	ip Equaliz	zer Pipettes			
Channels	Maximum spacing (mm)	Transfer to/from	\leftrightarrow	Transfer from/to	Minimum spacing (mm)
6-channel	19.8	• Test tube racks • 24-well microplates	\iff	96-well microplates Deepwell blocks	9.0
				AMAL STATE OF THE	
8-channel	14.2	Microcentrifuge tube racks 48-well microplates	\leftrightarrow	96-well microplates Deepwell blocks	9.0
		THE PART OF THE PA			
Equalizer	Pipettes	3			
Equalizer	Pipettes Maximum spacing (mm)	Transfer to/from	\leftrightarrow	Transfer from/to	Minimum spacing (mm)
	Maximum		↔	Transfer from/to • 384-well microplates • 384 PCR plates • Agarose Gels	
Channels	Maximum spacing (mm)	Transfer to/from • 96-well microplates • 48-well microplates • Deepwell blocks	↔	• 384-well microplates • 384 PCR plates	spacing (mm)
Channels	Maximum spacing (mm)	Transfer to/from • 96-well microplates • 48-well microplates • Deepwell blocks • Microcentrifuge tube racks		• 384-well microplates • 384 PCR plates • Agarose Gels	spacing (mm)

Manual pipettes

Maintain precise sample volumes on every channel

Whether you're using a single or multichannel pipette, the F1-ClipTip pipetting system enables a complete seal on every channel for precise sample volumes, saving valuable time to accelerate your discoveries.

Attach tips easily to help reduce strain injuries²

No longer bang tips onto your pipette. With a light touch each tip is 'clipped' securely on the F1-ClipTip pipette and remains sealed until you decide to eject tips.

A complete tip seal for confidence in your results

The F1-ClipTip system enables consistent and reproducible pipetting from user to user.

"We love these ClipTip pipettes!

Hearing the click is an excellent indicator that I have secured the tips to the multichannel. Some of the other brands do not have anything close to that security – many times using the multichannel was impossible because I would have to push each tip on securely, removing any time-savings the pipettor claimed to offer. It's so light weight too!

To date our real-time results have been more consistent than with other multichannel pipettes and so reliably precise we use our set exclusively for real-time now."

- Grace W., Lead Research Specialist



See it in action at: thermofisher.com/cliptip

¹ Thermo Scientific Application Note: ClipTip Technology Part 2 - Secure Seals for Every Channel, 2012

² Thermo Scientific Application Note: ClipTip Technology Part 3 - Reduce the Risk of Repetitive Strain Injury (RSI), 2013

Exceptional performance and comfort, redefined

Adjustable comfort The 120° adjustable finger

rest – for both right- and left-handed operator comfort – allows your hand to relax during pipetting cycles.

Industry-leading lifetime warranty*

With convenient online registration.

ClipTip Technology

A secure seal on every channel with low attachment and ejection forces for results you can count on again and again.

Silent, effortless volume adjustment

Enjoy the new silent and light volume adjustment with over 50% lower forces compared to earlier models. Improved grip on the volume adjustment knob offers effortless and precise adjustment.



Secure volume lock

Securely set and lock volumes to prevent undesirable volume drift during operation.

F1-Clip	oTip Manual P	ipette	es and C	ClipTip Pipette Tips	2 μL/10 μL/12.5 μL/20 μL		
Item No.	Description	Color Key	Volume Range	Increment/Packaging	50 μL		
2/10 μL Pipe	ettes		'	Increment	100 μL/ 200 μL		
4641310N	F1-ClipTip 0.1-2 µL		0.1-2 μL	0.002 μL	· ·		
4641320N	F1-ClipTip 1-10 µL		1-10 µL	0.02 μL	300 μL		
4661210N	F1-ClipTip 8-ch 1-10 µL		1-10 μL	0.02 μL			
4661220N	F1-ClipTip 12-ch 1-10 µL		1-10 μL	0.02 μL	_		
12.5 Ext μL	Tips*			Packaging			
94410060	ClipTip 12.5 Ext		0.1-12.5 μL	Racked, 96 tips/rack, 10 racks/pack			
94410063	ClipTip 12.5 Ext		0.1-12.5 μL	Racked, Sterile, 96 tips/rack, 10 racks/pack			
94420063	ClipTip 12.5 Ext		0.1-12.5 μL	Racked, Filtered, Sterile, 96 tips/rack, 10 racks/pack	<u>. </u>		
20 µL Pipett	es						
4641180N	F1-ClipTip 2-20 µL		2-20 μL	0.02 μL			
20 μL TIPS †	•			Packaging			
94410210	ClipTip 20		1-20 μL	Racked, 96 tips/rack, 10 racks/pack			
94410213	ClipTip 20		1-20 µL	Racked, Sterile, 96 tips/rack, 10 racks/pack			
94410217	ClipTip 20		1-20 μL	Reload Tower, 96 tips/insert, 10 inserts/pack			
94410218	ClipTip 20		1-20 μL	Reload Tower, Sterile, 96 tips/insert, 10 inserts/pack			
94420213	ClipTip 20		1-20 μL	Racked, Filtered, Sterile, 96 tips/rack, 10 racks/pack	<u> </u>		
94420218	ClipTip 20		1-20 μL	Reload Insert, Filtered, Sterile, 96 tips/insert, 10 insert	rts/pack		
50 μL PIPET	TES			Increment			
4641190N	F1-ClipTip 5-50 µL		5-50 μL	0.1 μL			
4661120N	F1-ClipTip 8-ch 5-50 µL		5-50 μL	0.1 μL			
4661160N	F1-ClipTip 12-ch 5-50 μL		5-50 μL	0.1 μL			
50 μL TIPS				Packaging			
94410250	ClipTip 50		5-50 μL	Racked, 96 tips/rack, 10 racks/pack			
94410253	ClipTip 50		5-50 μL	Racked, Sterile, 96 tips/rack, 10 racks/pack			
94410257	ClipTip 50		5-50 μL	Reload Tower, 96 tips/insert, 10 inserts/pack			
94410258	ClipTip 50		5-50 μL	Reload Tower, Sterile, 96 tips/insert, 10 inserts/pack			
94420253	ClipTip 50		5-50 μL	Racked, Filtered, Sterile, 96 tips/rack, 10 racks/pack			
94420258	ClipTip 50		5-50 μL	Reload Insert, Filtered, Sterile, 96 tips/insert, 10 insert	rts/pack		
100 μL / 200	μL PIPETTES			Increment			
4641200N	F1-ClipTip 10-100 μL		10-100 μL	0.2 μL			
4641210N	F1-ClipTip 20-200 µL		20-200 μL	0.2 μL			
4661130N	F1-ClipTip 8-ch 10-100 μL		10-100 μL	0.2 μL			
4661170N	F1-ClipTip 12-ch 10-100 μL		10-100 μL	0.2 μL			
200 μL TIPS				Packaging			
94410310	ClipTip 200		10-200 μL	Racked, 96 tips/rack, 10 racks/pack			
94410313	ClipTip 200		10-200 μL	Racked, Sterile, 96 tips/rack, 10 racks/pack			
94410317	ClipTip 200	0	10-200 μL	Reload Tower, 96 tips/insert, 10 inserts/pack			
94410318	ClipTip 200	0	10-200 μL	Reload Tower, Sterile, 96 tips/insert, 10 inserts/pack			
94420313	ClipTip 200		10-200 μL	Racked, Filtered, Sterile, 96 tips/rack, 10 racks/pack			
94420318	ClipTip 200		10-200 μL	Reload Insert, Filtered, Sterile, 96 tips/insert, 10 inse	rts/pack		
300 μL PIPE	TTES		·	Increment			
4641220N	F1-ClipTip 30-300 µL		30-300 μL	1 μL			
4661140N	F1-ClipTip 8-ch 30-300 µL	•	30-300 μL	1 μL			
4661180N	F1-ClipTip 12-ch 30-300 µL		30-300 μL	1 μL			
300 μL TIPS				Packaging			
94410510	ClipTip 300		30-300 μL	Racked, 96 tips/rack, 10 racks/pack			
94410513	ClipTip 300		30-300 μL	Racked, Sterile, 96 tips/rack, 10racks/pack			
94410517	ClipTip 300		30-300 μL	Reload Tower, 96 tips/insert, 10 inserts/pack			
				, , , , , , , , , , , , , , , , , , , ,			

^{*} CT 12.5 Ext tips and compatible F1-ClipTip pipettes utilize 'snap and seal' technology. All ClipTip pipette tips are low retention except for the CT12.5, CT12.5 Ext and 384-format tips. † CT20 tips are also used with old F1-ClipTip 1-10µl pipette models with catalogue numbers 4641170N, 4661110N, 4661150N and 4651190N.

94410518	ClipTip 300		30-300 μL	Reload Tower, Sterile, 96 tips/insert, 10 inserts/pack	2 μL/10 μL/12.5 μL/20 μL	
94420513	ClipTip 300	•	30-300 µL	Racked, Filtered, Sterile, 96 tips/rack, 10 racks/pack	- 50 μL	
94420518	ClipTip 300		30-300 μL	Reload Insert, Flitered, Sterile, 96 tips/inset, 10 inserts/pack	100 μL/ 200 μL	
94410610	ClipTip 300 Ext		30-300 μL	Racked, 96 tips/rack, 8 racks/pack	300 μL	
94410613	ClipTip 300 Ext		30-300 μL	Racked, sterile, 96 tips/rack, 8 racks/pack	1000 μL	
94410617	ClipTip 300 Ext		30-300 μL	Reload tower, 96 tips/insert, 10 inserts/pack	1250 μL	
94410618	ClipTip 300 Ext		30-300 μL	Reload tower, sterile, 96 tips/insert, 10 inserts/pack		
94420613	ClipTip 300 Ext		30-300 μL	Racked, filtered, sterile, 96 tips/rack, 8 racks/pack		
				Increment/Packaging		
Item No.	Description	Color Key	Volume Range	Increment/Packaging		
Item No. 1000 μL PIP		Color Key	Volume Range	Increment/Packaging Increment		
		Color Key	Volume Range			
1000 μL PIPI	F1-ClipTip 100-1000 μl**	Color Key		Increment		
1000 μL PIP 4641230N	F1-ClipTip 100-1000 μl**	Color Key		Increment 1 µL		
1000 μL PIPI 4641230N 1000 μL TIPS	ETTES F1-ClipTip 100-1000 μl** S	Color Key	100-1000 μL	Increment 1 μL Packaging		
1000 μL PIPI 4641230N 1000 μL TIPS 94410710	F1-ClipTip 100-1000 μl** S ClipTip 1000	Color Key	100-1000 μL 100-1000 μL	Increment 1 µL Packaging Racked, 96 tips/rack, 8 racks/pack		
1000 μL PIPI 4641230N 1000 μL TIPS 94410710 94410713	F1-ClipTip 100-1000 μl** S ClipTip 1000 ClipTip 1000	Color Key	100-1000 μL 100-1000 μL 100-1000 μL	Increment 1 μL Packaging Racked, 96 tips/rack, 8 racks/pack Racked, Sterile, 96 tips/rack, 8 racks/pack		

Item No.	Description	Volume Range
4651280N	F1-ClipTip 10 μL	10 μL
4651200N	F1-ClipTip 20 µL	20 μL
4651210N	F1-ClipTip 25 µL	25 μL
4651220N	F1-ClipTip 50 µL	50 μL
4651230N	F1-ClipTip 100 μL	100 μL
4651240N	F1-ClipTip 200 µL	200 μL
4651250N	F1-ClipTip 250 µL	250 μL
4651260N	F1-ClipTip 500 µl**	500 μL
4651270N	F1-ClipTip 1000 µl**	1000 μL

Order online and find additional specifications at **thermofisher.com/cliptip**

** Short Shaft

Item No.	Description	Contents of Kit		
4701140N	F1-ClipTip GLP Kit 1	• F1-ClipTip 10-100 µL single channel • F1-ClipTip 100-1000 µL single channel • F-Series Stand	 ClipTip 200 rack ClipTip 1000 rack 25 mL reservoir 25 mL divided reservoir 100 mL divided reservoir 	F1-ClipTip GLP Kit 2
4701150N	F1-ClipTip GLP Kit 2	 F1-ClipTip 20-200 μL single channel F1-ClipTip 100-1000 μL single channel F1-ClipTip 30-300 μL 8-channel F-Series Stand 	 ClipTip 200 rack ClipTip 300 rack ClipTip 1000 rack 25 mL reservoir 25 mL divided reservoir 100 mL divided reservoir 	

Item No.	Description	Color Key	Increment/Packaging			
9420400	F-Series Stand, white, 6 positions					
94410219	Empty Rack, Small		10 racks, no tips/inserts			
94410519	Empty Rack, Medium		10 racks, no tips/inserts			
94410619	300 Ext Empty Rack		8 racks, no tips/inserts			
94410819	Empty Rack, Large	• •	8 racks, no tips/inserts			

Item No.	Description	Color Key	Volume Range	Tip Spacing Range (mm)	Increment/Packaging	30 μL/ 50 μL
0.5-12.5 μL l		Key	Range	Range (mm)	Increment	100 μL/ 125 μL/ 200 μL
4670000BT	E1-ClipTip, 0.5-12.5 μL		0.5-12.5 μL		0.01 µL	300 μL
4671000BT	E1-ClipTip, 8-ch 0.5-12.5 μL		0.5-12.5 µL		0.01 µL	950 μL/ 1000 μL
4671010BT	E1-ClipTip, 12-ch 0.5-12.5 μL		0.5-12.5 µL		0.01 µL	· ·
12.5 μL TIPS				1	Packaging	1250 μL
94410040	ClipTip 12.5		0.5-12.5 μL		Racked, 96 tips/rack, 10 racks/pack	
94410043	ClipTip 12.5		0.5-12.5 µL		Racked, sterile, 96 tips/rack, 10 rack	s/pack
94420043	ClipTip 12.5		0.5-12.5 µL		Racked, filtered, sterile, 96 tips/rack,	10 racks/pack
94410060	ClipTip 12.5 Ext		0.5-12.5 μL		Racked, 96 tips/rack, 10 racks/pack	_
94410063	ClipTip 12.5 Ext		0.5-12.5 μL		Racked, sterile, 96 tips/rack, 10 rack	s/pack
94420063	ClipTip 12.5 Ext		0.5-12.5 μL		Racked, filtered, sterile, 96 tips/rack,	10 racks/pack
384, 12.5 μL	PIPETTES*		-		Increment	
4671020BT	E1-ClipTip, 16-ch 0.5-12.5 µL		0.5-12.5 μL		0.01 μL	
4672010BT	E1-ClipTip Equalizer 384, 8-ch 0.5-12.5 µL	Eq	0.5-12.5 µL	4.5-14.2	0.01 µL	
4672020BT	E1-ClipTip Equalizer 384, 12-ch 0.5-12.5 µL	Eq	0.5-12.5 μL	4.5-9.0	0.01 µL	
384, 12.5 μL	TIPS*			•	Packaging	
94410050	ClipTip 384, 12.5		0.5-12.5 μL		Racked, 384 tips/rack, 10 racks/pack	ζ
94410053	ClipTip 384, 12.5		0.5-12.5 μL		Racked, sterile, 384 tips/rack, 10 rac	ks/pack
94420053	ClipTip 384, 12.5		0.5-12.5 μL		Racked, filtered, sterile, 384 tips/rack	k, 10 racks/pack
94410070	ClipTip 384, 12.5 Ext		0.5-12.5 μL		Racked, 384 tips/rack, 10 racks/pack	ζ
94410073	ClipTip 384, 12.5 Ext		0.5-12.5 μL		Racked, sterile, 384 tips/rack, 10 rac	ks/pack
94420073	ClipTip 384, 12.5 Ext		0.5-12.5 μL		Racked, filtered, sterile, 384 tips/rack	k, 10 racks/pack
384, 30 μL P	IPETTES*				Increment	
4671030BT	E1-ClipTip, 16-ch 1-30 μL		1-30 µL		0.01 μL	
4672030BT	E1-ClipTip Equalizer 384, 8-ch 1-30 µL	Eq	1-30 µL	4.5-14.2	0.01 μL	
4672040BT	E1-ClipTip Equalizer 384, 12-ch 1-30 μL	Eq	1-30 µL	4.5-9.0	0.01 μL	
384, 30 μL T	PS*				Packaging	
94410100	ClipTip 384, 30		1-30 µL		Racked, 384 tips/rack, 10 racks/pack	<
94410103	ClipTip 384, 30		1-30 µL		Racked, Sterile, 384 tips/rack, 10 rac	cks/pack
94420103	ClipTip 384, 30		1-30 µL		Racked, Filtered, Sterile, 384 tips/rac	k, 10 racks/pack
125 µL PIPE	TTES				Increment	
4670020BT	E1-ClipTip, 2-125 μL		2-125 μL		0.1 μL	
4671040BT	E1-ClipTip, 8-ch 2-125 μL		2-125 μL		0.1 μL	
4671050BT	E1-ClipTip, 12-ch 2-125 μL		2-125 μL		0.1 µL	
4672050BT	E1-ClipTip Equalizer, 8-ch 2-125 μL	Eq	2-125 μL	9.0-14.2	0.1 µL	
200 μL TIPS		,			Packaging	
94410310	ClipTip 200		2-200 μL		Racked, 96 tips/rack, 10 racks/pack	
94410313	ClipTip 200		2-200 μL		Racked, Sterile, 96 tips/rack, 10 rack	ks/pack
94410317	ClipTip 200		2-200 μL		Reload Tower, 96 tips/insert, 10 inser	ts/pack
94410318	ClipTip 200		2-200 μL		Reload Tower, Sterile, 96 tips/insert,	10 inserts/pack
94420313	ClipTip 200		2-200 μL		Racked, Filtered, Sterile, 96 tips/rack	, 10 racks/pack
94420318	ClipTip 200		2-200 µL		Reload Insert, Filtered, Sterile, 96 tips	s/insert, 10 inserts/pack
384, 125 μL	1				Increment	
4671060BT	E1-ClipTip, 16-ch 2-125 μL		2-125 μL		0.1 μL	
4672060BT	E1-ClipTip Equalizer 384, 8-ch 2-125 μL	Eq	2-125 μL	4.5-14.2	0.1 µL	
4672070BT	E1-ClipTip Equalizer 384, 12-ch 2-125 µL	Eq	2-125 μL	4.5-9.0	0.1 μL	
384, 125 μL	TIPS*				Packaging	
94410150	ClipTip 384, 125		2-125 µL		Racked, 384 tips/rack, 10 racks/pacl	<u> </u>

94410153	ClipTip 384, 125		2-125 μL		Racked, Sterile, 384 tips/rack, 10 ra	acks/pack
94420153	ClipTip 384, 125		2-125 μL		Racked, Filtered, Sterile, 384 tips/ra	nck, 10 racks/pack
Item No.	Description	Color Key	Volume Range	Tip Spacing Range (mm)	Increment/Packaging	
300 μL PIPE	ITES				Increment	2 μL/10 μL/12.5 μL/20
4670030BT	E1-ClipTip, 10-300 μL		10-300 μL		0.1 μL	30 μL/ 50 μL
4671070BT	E1-ClipTip, 8-ch 10-300 μL	•	10-300 μL		0.1 μL	100 μL/ 125 μL/ 200 μL
4671080BT	E1-ClipTip, 12-ch 10-300 μL	•	10-300 μL		0.1 μL	300 μL
4672080BT	E1-ClipTip Equalizer, 8-ch 10-300 μL	Eq	10-300 μL	9.0-14.2	0.1 μL	 850 μL/ 1000 μL
300 μL TIPS					Packaging	1250 μL
94410510	ClipTip 300		30-300 μL		Racked, 96 tips/rack, 10 racks/pacl	(
94410513	ClipTip 300	•	30-300 μL		Racked, sterile, 96 tips/rack, 10 rac	ks/pack
94410517	ClipTip 300		30-300 μL		Reload tower, 96 tips/insert, 10 inse	erts/pack
94410518	ClipTip 300		30-300 μL		Reload tower, sterile, 96 tips/insert,	10 inserts/pack
94420513	ClipTip 300	•	30-300 μL		Racked, filtered, sterile, 96 tips/rack	k, 10 racks/pack
94420518	ClipTip 300		30-300 μL		Racked, filtered, sterile, 96 tips/rack	k, 10 racks/pack
94410610	ClipTip 300 Ext	•	30-300 μL		Racked, 96 tips/rack, 8 racks/pack	
94410613	ClipTip 300 Ext		30-300 μL		Racked, sterile, 96 tips/rack, 8 rack	s/pack
94410617	ClipTip 300 Ext		30-300 μL		Reload tower, 96 tips/insert, 10 inse	erts/pack
94410618	ClipTip 300 Ext		30-300 μL		Reload tower, sterile, 96 tips/insert, 10 inserts/pack	
94420613	ClipTip 300 Ext		30-300 μL		Racked, filtered, sterile, 96 tips/rack	k, 8 racks/pack
850 µL PIPE	TTES	Increment				
4671090BT	E1-ClipTip, 12-ch 30-850 μL		30-850 μL		1.0 µL	
1000 μL TIPS	S				Packaging	
94410710	ClipTip 1000		30-1000 μL		Racked, 96 tips/rack, 8 racks/pack	
94410713	ClipTip 1000		30-1000 μL		Racked, Sterile, 96 tips/rack, 8 rack	s/pack
94410717	ClipTip 1000		30-1000 μL		Reload Tower, 96 tips/insert, 8 inser	ts/pack
94410718	ClipTip 1000		30-1000 μL		Reload Tower, Sterile, 96 tips/insert,	8 inserts/pack
94420713	ClipTip 1000		30-1000 μL		Racked, Filtered, Sterile, 96 tips/rac	k, 8 racks/pack
94420718	ClipTip 1000		30-1000 μL		Reload Insert, Filtered, Sterile, 96 tip	os/insert, 8 inserts/pack
15-1250 μL l	PIPETTES				Increment	
4670040BT	E1-ClipTip, 15-1250 μL		15-1250 μL		1.0 µL	
4671100BT	E1-ClipTip, 8-ch 15-1250 μL		15-1250 μL		1.0 µL	
4672090BT	E1-ClipTip Equalizer, 6-ch 15-1250 μL	Eq	15-1250 μL	9.0-19.8	1.0 µL	
4672100BT	E1-ClipTip Equalizer, 8-ch 15-1250 μL	Eq	15-1250 μL	9.0-14.2	1.0 µL	
1250 µL TIPS	S				Packaging	
	ClipTip 1250		15-1250 µL		Racked, 96 tips/rack, 8 racks/pack	
94410810			15-1250 μL		Racked, Sterile, 96 tips/rack, 8 rack	s/pack
94410810 94410813	ClipTip 1250		10 1200 pz			
	ClipTip 1250 ClipTip 1250		15-1250 µL		Reload Insert, 96 tips/insert, 8 inser	ts/pack
94410813			+		Reload Insert, 96 tips/insert, 8 inser Reload Insert, Sterile, 96 tips/insert,	<u> </u>
94410813 94410817	ClipTip 1250		15-1250 µL			8 inserts/pack

Item No.	Descritpion	Color Key	Increment/Packaging
9420500	E1-ClipTip Charging Stand, 1 position	Compatible with E1-ClipTip pipettes	
9420510	E1-ClipTip Multi Charging Stand, 3 position	Compatible with E1-ClipTip pipettes	
94410219	Empty Rack, Small		10 racks, no tips/inserts
94410519	Empty Rack, Medium		10 racks, no tips/inserts
94410619	300 Ext Empty Rack		8 racks, no tips/inserts
94410819	Empty Rack, Large		8 racks, no tips/inserts

Order online and find additional specifications thermofisher.com/cliptip





Pipetting for a lifetime

A history of liquid handling innovations providing consistent, reproducible results









TECHNIQUES

TOOLS

ERGONOMICS

SERVICE

Learn how the right combination of technique, selecting the right tools, ergonomics and service support Good Laboratory Pipetting at thermofisher.com/pipettingforlifetime

Protecting your investment

For more than 25 years, we have prided ourselves by offered quality-minded service that meets customers diverse needs.

Whether you're working in a unique environment such as cGLP, cGMP, critical research, academia, or have a special requirement, you can feel confident that your pipettes will have the accuracy and performance you need.

We provide you with:

- Online visibility of service status, calibration history, and asset management
- Tailored solutions to fit your unique needs
- Option to send pipettes to our calibration laboratory or have us come to your site



- Support Plans
- Parts and Consumables
- Training and More



Let our expertise complement yours

Explore all the new ways to protect your instruments and equipment at thermofisher.com/equipment-service

Pipette warranty registration

Register your pipette online to activate your free warranty at www.thermofisher.com/pipettewarranty

Find out more at thermofisher.com/cliptip

© 2021 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. The Bluetooth® is a trademark of Bluetooth SIG, Inc. Specifications, terms and pricing are subject to change. Validity of lifetime warranty varies by country. Not all products are available in all countries. Please consult your local sales representative for details.

