

Thermo Fisher Scientific hereby certifies that the product identified below is produced, inspected and found to be in compliance with product and quality specification requirements as documented in our ISO 13485:2003 Quality Management System (QMI-SAI Global File No. 1606319 and 1606321) in the USA.



Lisa Adams
Mgr. Quality Engineering

The following information represents Product Certification for: Item#: **1-1863-10**

Certificate issued: **10/24/2012**

Description: **Clos,Capt Assy,38mm,Fire Org/Irridescent** Lot#: **1082819**

Manufactured: **10/16/2012**

Part Number	Description	Common Name	DMF#	Cytotoxicity	USP Class VI	FDA Compliance - 21 CFR
1-1863-24	Clos,38/430,PPCO,Fire Orange,Nalge	COMPONENT PART				
8-0028-35P	Resin,PPCO,Fire Orange,Inj	COMPONENT PART				
8-0029-04	RESIN,PP,COPOLYMER,INJ	POLYPROPYLENE COPOLYMER	1698	N/A	N/A	177.1520(a)(3)(i) and(c)3.1 a, 3.2a
8-0097-88	Color,PPCO,Fire Orange,Inj	COMPONENT PART				
1-1863-94	Btn,38mm,PPCO,Fire Orange,L/T	COMPONENT PART				
8-0028-35P	Resin,PPCO,Fire Orange,Inj	COMPONENT PART				
8-0029-04	RESIN,PP,COPOLYMER,INJ	POLYPROPYLENE COPOLYMER	1698	N/A	N/A	177.1520(a)(3)(i) and(c)3.1 a, 3.2a
8-0097-88	Color,PPCO,Fire Orange,Inj	COMPONENT PART				
1-1863-71	Strap,38mm,LLDPE,Irridescent,L/T	COMPONENT PART				
8-0049-75P	Resin,LLDPE,Irridescent BK,Inj	COMPONENT PART				
8-0049-06	RESIN,LLDPE,INJ	LLDPE, INJECTION	N/A	N/A	N/A	177.1520 (c) 3.1 a
8-0097-89	Color,Irridescent BK,Multi, Inj	COMPONENT PART				

If N/A appears in any of the columns above it means the information is not available. Any item listed as "COMPONENT PART" will show blank in the DMF#, Cytotoxicity, USP Class VI, and FDA Compliance Information columns.

If the word "PASSED" appears in the USP Class VI column next to the resin listing, this material has passed USP Class VI requirements, latest Volume, as part of our initial test approval protocol.

If the word "PASSED" appears in the Cytotoxicity column next to the resin listing, this material was tested and shown to be non-cytotoxic as part of our initial test approval protocol, using either mouse fibroblast L929 cells or the more sensitive human diploid lung cell lines WI-38 or MRC-5.