

Superspeed Rotors

Thermo Scientific Fiberlite F8-6x1000y Rotor

(this rotor is no longer available)*



ROTOR SPECIFICATIONS

Type	Fixed Angle
Material	Carbon Fiber Composite
Capacity	6 x 1000 mL
Maximum Speed	8,500 rpm
Maximum Sample Density	1.2 g/mL
Tube Dimensions Ø x L	98 x 195 mm
Angle	20°
K Factor	5096.0
Net Weight	17.6 kg/38.8 lbs
Warranty	15 years

	RCF	RADIUS
Maximum	15,900 xg	196.0 mm
Minimum	4,369 xg	54.0 mm

ROTOR AND ACCESSORIES ORDERING INFORMATION

		THERMO SCIENTIFIC SORVALL Evolution RC Series
Fiberlite F8-6x1000y	Cat. No.	76641
	Max. Speed	8,500 rpm
	Max. RCF	15,900 xg
Fiberlite F8-6x1000y Rotor Package includes:		
	Rotor Lid Assembly	099-061108
	O-ring Refresher Kit	021-061108

LABWARE ORDERING INFORMATION

Tube Vol. (mL)	Vol. Fill (mL)	Description	Cat. No.	Qty. /Pkg.	Tubes /Rotor	Max. Speed (rpm)	Max. RCF (xg)	Dims ØxL (mm)	REQUIRED TUBE CLOSURES, ADAPTERS, TOOLS & ACCESSORIES			
									Type	Cat. No.	Qty. /Pkg.	Description
1000.0	1000.0	Nalgene™ PPCO Oak Ridge Bottle	3141-1002	2	6	8,500	15,900	98 x 195	Closure	Included	2	Noryl Cap with PP Plug
1000.0	1000.0	Nalgene PC Oak Ridge Bottle	3140-1002	2	6	8,500	15,900	98 x 195	Closure	Included	2	Noryl Cap with PP Plug
500.0	450.0	Nalgene PPCO Oak Ridge Bottle	3141-0500	24	6	8,500	15,900	70 x 160	Closure Adapter	Included 010-0145	24 1	PP Sealing 1 place/adapter
500.0	450.0	Nalgene PC Oak Ridge Bottle	3140-0500	24	6	8,500	15,900	70 x 160	Closure Adapter	Included 010-0145	24 1	PP Sealing 1 place/adapter
250.0	—	Corning™ Disposable Conical Tube ¹	—	—	6	8,500	15,900	—	Adapter	010-1196	2	1 place/adapter
250.0	250.0	Nalgene PPCO Oak Ridge Bottle	3141-0250	36	6	8,500	15,900	61 x 133	Closure Adapter	Included 010-0150	36 2	PP Sealing 1 place/adapter
250.0	250.0	Nalgene PC Oak Ridge Bottle	3140-0250	36	6	8,500	15,900	61 x 135	Closure Adapter	Included 010-0150	36 2	PP Sealing 1 place/adapter

Refer to manufacturer's recommendations for product performance information, including cycle limits and chemical compatibility limitations.

*Contact your sales representative for alternate solutions.

¹ Performance depends upon tube brand. Contact your sales representative for recommended tube manufacturers and further information.

LABWARE ORDERING INFORMATION CONTINUED

Tube Vol. (mL)	Vol. Fill (mL)	Description	Cat. No.	Qty. /Pkg.	Tubes /Rotor	Max. Speed (rpm)	Max. RCF (xg)	Dims ØxL (mm)	REQUIRED TUBE CLOSURES, ADAPTERS, TOOLS & ACCESSORIES			
									Type	Cat. No.	Qty. /Pkg.	Description
175.0	175.0	Nalgene PPCO Conical Wide-Mouth Tube	3143-0175	36	6	8,500	15,900	61 x 144	Closure Adapter	Included	36	PP Sealing
										010-1132	2	1 place/adapter
175.0	175.0	Nalgene PC Conical Wide-Mouth Tube	3144-0175	36	6	8,500	15,900	61 x 144	Closure Adapter	Included	36	PP Sealing
										010-1132	2	1 place/adapter
80.0	73.0	PC Oak Ridge Tube	010-0515	6	6	8,500	15,900	38 x 109	Closure Adapter	Included	6	PP Sealing
										010-1093	2	3 places/adapter
80.0	61.0	PPCO Oak Ridge Tube	010-1280	6	18	8,500	15,900	38 x 109	Closure Adapter	Included	6	PP Sealing
										010-1093	2	3 places/adapter
85.0	81.0	Nalgene PC Oak Ridge Tube	3118-0085	100	18	8,500	15,900	38 x 109	Closure Adapter	Included	100	PP Screw Top
										010-1093	2	3 places/adapter
50.0	50.0	Nunc™ Disposable Conical Tube ¹	339653	25	18	8,500	15,900	30 x 115	Closure Adapter	Included	25	PP Sealing
										010-0180	2	5 places/adapter
50.0	–	Corning Disposable Conical Tube ¹	–	–	30	–	–	–	Adapter	010-0180	2	5 places/adapter
50.0	–	BD Falcon™ Disposable Conical Tube ¹	–	–	30	–	–	–	Adapter	010-0180	2	5 places/adapter
50.0	46.0	Nalgene PC Oak Ridge Tube	3138-0050	50	30	8,500	15,900	29 x 115	Closure Adapter	Included	50	PP Sealing
										010-1091	2	6 places/adapter
50.0	46.0	Nalgene PPCO Oak Ridge Tube	3139-0050	50	36	8,500	15,900	29 x 115	Closure Adapter	Included	50	PP Sealing
										010-1091	2	6 places/adapter
50.0	46.0	Nalgene PSF Oak Ridge Tube	3137-0050	50	36	8,500	15,900	29 x 115	Closure Adapter	Included	50	PP Sealing
										010-1091	2	6 places/adapter
50.0	46.0	Nalgene FEP Oak Ridge Tube	3114-0050	10	36	8,500	15,900	29 x 108	Closure Adapter	Included	10	ETFE Screw Cap
										010-1091	2	6 places/adapter
30.0	30.0	Nalgene PC Oak Ridge Tube	3138-0030	50	42	8,500	15,900	26 x 102	Closure Adapter	Included	50	PP Sealing
										010-1095	2	7 places/adapter
30.0	30.0	Nalgene PPCO Oak Ridge Tube	3139-0030	50	42	8,500	15,900	26 x 102	Closure Adapter	Included	50	PP Sealing
										010-1095	2	7 places/adapter
30.0	30.0	Nalgene PSF Oak Ridge Tube	3137-0030	50	42	8,500	15,900	26 x 102	Closure Adapter	Included	50	PP Sealing
										010-1095	2	7 places/adapter
30.0	30.0	Nalgene FEP Oak Ridge Tube	3114-0030	10	42	8,500	15,900	26 x 102	Closure Adapter	Included	10	ETFE Screw Cap
										010-1095	2	7 places/adapter
16.0	16.0	Nalgene PC Oak Ridge Tube	3139-0016	50	84	8,500	15,900	18 x 107	Closure Adapter	Included	50	PP Sealing
										010-1087	2	14 places/adapter
16.0	16.0	Nalgene PPCO Oak Ridge Tube	3138-0016	50	84	8,500	15,900	18 x 107	Closure Adapter	Included	50	PP Sealing
										010-1087	2	14 places/adapter
15.0	–	Corning Disposable Conical Tube ¹	–	–	72	–	–	–	Adapter	010-1079	2	12 places/adapter
15.0	–	BD Falcon Disposable Conical Tube ¹	–	–	72	–	–	–	Adapter	010-1079	2	12 places/adapter
10.0	8.0	Nalgene PPCO Oak Ridge Tube	3139-0010	50	108	8,500	15,900	16 x 100	Closure Adapter	Included	50	PP Sealing
										010-1307	2	18 places/adapter
10.0	8.0	Nalgene PC Oak Ridge Tube	3138-0010	50	108	8,500	15,900	16 x 100	Closure Adapter	Included	50	PP Sealing
										010-1307	2	18 places/adapter
10.0	–	Vacutainer™ Tube ¹	–	–	108	–	–	16 x 100	Adapter	010-1085	2	18 places/adapter
3.0	–	Vacutainer Tube ¹	–	–	180	–	–	16 x 100	Adapter	010-1131	2	30 places/adapter

Refer to manufacturer's recommendations for product performance information, including cycle limits and chemical compatibility limitations.

Note: Thermo Scientific Sorvall RC-6 Plus centrifuges manufactured prior to March 2009 may require software upgrade 314295G01 (NA) or HKKS308102E (Europe and Asia Pacific).

¹ Performance depends upon tube brand. Contact your sales representative for recommended tube manufacturers and further information.

Find out more at thermofisher.com/rotors

© 2017 Thermo Fisher Scientific Inc. All rights reserved. Corning is a registered trademark of Corning Inc. BD Falcon and Vacutainer are registered trademarks of BD Bioscience. All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

ThermoFisher
SCIENTIFIC