

Flammable Storage Lab Refrigerators, Freezers and Combination Units

Designed to be used for the storage of volatiles, compounds and solvents where a spark-free internal cabinet environment is required.

Not available in North America, consult your sales representative for availability.

- Sparkfree interior to reduce the risk of internal explosion
- All models are manual defrost
- Tough white exterior
- CFC- and HCFC-free refrigeration system and insulation

Warranty: 13 months parts and labor



Model No: 10FCEETSV
286.0 liter flammable
storage combination refrigerator
and freezer

Thermo Scientific Flammable Material Refrigerators (Temperature Range 1° to 12°C)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Shipping Weight
20FRCETSV*	20.9 cu. ft. (591.82 liters)	4 fixed shelves	230V/50hz	73.13" x 34" x 35.81" (185.7 x 86.4 x 90.95 cm)	57.8" x 27.8" x 23.8" (146.7 x 70.49 x 60.3 cm)	198 lbs. (89.8 kg)
20FREETSV	20.9 cu. ft. (591.82 liters)	4 fixed shelves, 6 door shelves	230V/50hz	73.13" x 34" x 35.81" (185.7 x 86.4 x 90.95 cm)	57.8" x 27.8" x 23.8" (146.7 x 70.49 x 60.3 cm)	198 lbs. (89.8 kg)

* Corrosion-resistant model, features stainless steel interior door and stainless steel shelves

Thermo Scientific Flammable Material Freezers (Temperature Range -12° to -20°C)

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Shipping Weight
20FFEETSV	20.9 cu. ft. (591.82 liters)	4 fixed shelves, 6 door shelves	230V/50hz	73.13" x 34" x 35.81" (185.7 x 86.4 x 90.95 cm)	57.8" x 27.8" x 23.8" (146.7 x 70.49 x 60.3 cm)	198 lbs. (89.8 kg)

Thermo Scientific Flammable Material Combination Refrigerator/Freezers (Temperature Range: 1° to 12°C [ref], -12° to -20°C [frz])

Model No.	Capacity	Interior Storage	Voltage	Exterior Dimensions: (H x W x D)	Interior Dimensions: (H x W x D)	Shipping Weight
10FCEETSV	10.1 cu. ft. (286.0 liters)	3 adjustable interior, 1 fixed interior, 1 drawer, 4 door shelves	230V/50hz	59.75" x 23.63" x 28.6" (151.77 x 60 x 76.2 cm)	Ref: 38.25" x 19.75" x 18.25" (97.2 x 50.2 x 46.4 cm); Frz: 11.25" x 18" x 18.25" (28.6 x 45.7 x 46.4 cm)	150 lbs. (68 kg)

Find out more at thermofisher.com/cold

ThermoFisher
SCIENTIFIC