

<b>Specifications</b>	<b>Catalog Number</b>		
	<b>DLCPTHUMI001</b>		
<b>Application and Operating Conditions</b>			
Application	Temperature and humidity sensor to be used with a DeviceLink Connect remote monitoring system		
Application Environment	Non-corrosive, non-flammable, non-explosive, good air ventilation		
<b>Sensor Specifications</b>			
<b>Type</b>	<b>Temperature</b>	<b>Relative Humidity</b>	
Measurement Range	-17°C to +49°C (1°F to 120°F)	2% to 95% RH (non-condensing)	
Accuracy	±1°C (±1.8°F)	±3% RH	
Display Resolution	0.1	0.1	
System Resolution	0.01	0.01	
<b>Sensor Construction</b>			
Connection Interface	USB (Type A) connection to DeviceLink Connect mote		
Housing	316 stainless steel		
Dimensions	5.5" x 0.625" (138mm x 16mm) (L x D)		
Weight	2.88oz (67g)		
Cable Length	6.8' (2.1m)		



**Temp/RH Sensor Package Contents**



**Temp/RH Sensor Connected to DeviceLink Connect Mote**

© 2022 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries. Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.