

Bench meters

Achieve consistent pH analysis

Eutech 1710 pH/mV bench meters

Measure pH using the Eutech 1710 pH/mV Bench Meter.

Benefits

- Simplify pH testing with these economical pH meters
- Easily view 5" display with backlight
- Save bench space with small meter footprint
- Support GLP compliance with date and time stamped logs
- Help ensure accuracy with viewable calibration logs with date and time stamp
- Track critical data with 500-point log with date and time stamp
- Keep long-term records with data output to a printer or computer

The Thermo Scientific™ Eutech™ 1710 pH/mV Bench Meter is designed for laboratory users with diverse ranges of technical knowledge who require an easy-to-use and easy-to-calibrate meter for routine pH testing. The meter's large, backlit display offers easy-to-view readings and the meter's small footprint reduces its required bench space. This pH meter is ideally suited for simplified, economical lab testing.

Analyze pH or RmV simultaneously with mV and temperature using the Eutech 1710 pH/mV Bench Meter. Measure pH in a range of -2.00 to 18.00 pH, measure RmV in a range of -2000.0 to +2000.0 mV and measure temperature in a range of -5.0 to 105.0 °C. Perform one-to-five-point pH calibrations, one-point RmV calibrations, and one-point temperature adjustment calibrations.

Large, backlit display offers easy-to-view readings and small footprint saves lab space, this pH meter is designed for simplified, economical lab testing.

Use the onscreen stabilizing and ready indicators to help identify when pH meter and readings are complete. The pH electrode condition icon helps ensure reliable electrode performance throughout your testing.

View active pH, RmV and temperature calibration logs with date and time stamp to ensure accurate, reproducible measurements. Record key measurements using the 500-point data log with date and time stamp. Output data logs and calibration logs to a printer or computer for long-term data storage.

Product specifications

Parameter	Description
pH	
Range	-2.00 to 18.00 pH
Resolution	0.1, 0.01 pH
Relative accuracy	±0.01 pH ± 1 LSD
Calibration points	1 to 5 points
Calibration method	Automatic buffer recognition with manual buffer entry option
Calibration pH buffer sets	USA (pH 1.68, 4.01, 7.00, 10.01, 12.45) NIST (pH 1.68, 4.01, 6.86, 9.18, 12.45)
Slope display	Yes
mV / ORP	
Range	±2000 mV
Resolution	0.1 mV
Relative accuracy	±0.2 mV or ±0.05 % of the reading, whichever is greater
Calibration points	1 point
Offset adjustment	Up to ±250 mV
Temperature	
Range	-5.0 to 105.0 °C
Resolution	0.1 °C
Relative accuracy	±0.3 °C
Calibration points	1 point
Offset adjustment	Up to ±5 °C
Features	
Display	5" backlit LCD
Time and date	Yes
Time format	12 hour AM/PM
Date format	Selectable, DD-MM-YYYY or MM-DD-YYYY
Read types	Continuous, Auto-Read, Timed
Timed interval	5 seconds to 60 minutes

Parameter	Description
Features - continued	
Data log	500 sets with time and date
Calibration log	Active pH, RmV, temperature with time and date
Calibration alarm	Yes, 1 to 168 hours or off
Sleep mode	Yes, optional
Self-test	Automatic with startup
Memory	Non-volatile
Input	BNC, ATC
Data output	Computer or printer
Data output format	CSV or print
Warranty	3 years
Certifications	CE, cTUVus, FCC Class B, CES-001, KC, RCM
Enclosure	IP-54
Power	100-240 VAC, 50-60Hz, 9 DC adapter, 1.3A
Dimensions (L x W x H)	198.3 mm x 155.2 mm x 61.7 mm
Weight	700 grams
Environmental conditions	
Environmental conditions	Indoors
Altitude	Up to 2,000 metres
Operating temperature	5°C to 45°C
Operating relative humidity	5 to 85%, non-condensing
Storage temperature	-20°C to 60°C
Storage relative humidity	5 to 85%, non-condensing
Mains fluctuation	±10% of range (100-240VAC)
Installation category	II
Pollution degree	2
Protection class	III

Ordering Information

Description	Cat. No.
Thermo Scientific Eutech 1700 pH/mV Bench Meter with electrode stand, PC cable and universal power adapter	EBPH171000
Thermo Scientific Eutech 1700 pH/mV Bench Meter standard kit, includes meter with gel-filled plastic-body pH/ATC electrode, solutions, stand, PC cable and power adapter	EBPH171001
Thermo Scientific Eutech 1700 pH/mV Bench Meter easy-to-clean kit, includes meter with refillable plastic-body double junction pH electrode, ATC probe, solutions, stand, PC cable and power adapter	EBPH171002
Thermo Scientific Eutech 1700 pH/mV Bench Meter low-maintenance kit, includes meter with gel-filled plastic-body double junction pH electrode, ATC probe, solutions, stand, PC cable and power adapter	EBPH171003
Thermo Scientific Eutech 1700 pH/mV Bench Meter chemically resistant sensor kit, includes meter with refillable glass-body double junction pH electrode, ATC probe, solutions, stand, PC cable and power adapter	EBPH171004
Thermo Scientific Eutech 1700 series electrode stand with meter-attachable bracket	EB1700ARM
Thermo Scientific Eutech 1700 series universal power adapter with twist-and-lock connector, 100-240V 50/60Hz	EB1700PWR
Thermo Scientific Eutech 1700 series USB computer cable	EB1700USB
Thermo Scientific Eutech 1700 series meter dust cover	EB1700CVR
Thermo Scientific Eutech Compact Thermal Printer for Eutech meters; 100-240V, 50/60Hz	01X594301
Thermo Scientific Eutech Replacement Paper for compact thermal printer, 2 rolls	01X594401

 Learn more at thermofisher.com/eutech

thermoscientific

For Laboratory Use. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific use or application. © 2022 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. **EXTXXX 0922**