



# TDE Series ultra-low temperature freezers



# TDE Series ultra-low temperature freezers

Thermo Scientific™ TDE Series –80°C ultra-low temperature (ULT) freezers, powered by the H-Drive system, are designed for efficiency. As a result, the series delivers a foundational ULT experience with the reliability and performance needed to protect your work—and the sustainability to meet global compliance.

## Designed to keep your samples safe

- Worry-free storage; with low peak variation, samples are protected throughout the entire cabinet<sup>1</sup>
- Fast door opening recovery; as little as 1 minute for chest freezers
- Secure freezer settings with sample security
- General-purpose models for nondiagnostic general laboratory use, and Class II Medical Device models for storage and preservation of blood and blood products at freezing temperatures<sup>2</sup>
- Backed by our Global Service and Support team

## Limit environmental impact and lower HVAC costs

- –86°C 600 box models are ENERGY STAR™-certified and feature an ACT™ Environmental Impact Factor Label
- Energy use as low as 6.6 kWh/day, depending on size and temperature
- Less heat emission lowers HVAC costs
- SNAP and EU F-gas regulation compliant, natural hydrocarbon refrigerants
- Environmentally friendly, polyurethane foam with non-HFC blowing agent is compliant with SNAP and EU F-gas regulations
- Manufactured in an award-winning, zero-waste-to-landfill facility



## User-friendly and quiet

- H-Drive Information Center (HIC) touchscreen user interface
- Quiet enough to reside directly in the laboratory; at just 50 dBA, the sound is comparable to a home refrigerator<sup>3</sup>
- Decrease storage footprint up to 25%
- 5-year parts and labor standard warranty\*

\* Restrictions and exclusions apply. Warranty is void if the unit is not maintained as set forth in the operation and service manuals.

1. Typical freezer data based on internal testing with freezer setpoint at –80°C and ambient temperature at 20°C. Performance data vary across freezer size and electrical specification.

2. Verification of medical devices in the United States can be found on: <https://www.accessdata.fda.gov/scripts/cdrh/cfdocs/cfr/rl.cfm>.

3. All data based on internal testing unless otherwise noted. Data on file.


# A rich heritage of innovation

From our first ULT freezer in 1940 to today, the combined experience of REVCO™, Forma Scientific™, Jewett™, Harris™, and other families of products continues to drive our ability to deliver industry-leading innovations that help accelerate science and health care.

## Easy-to-access controls with setpoint security

- Easy to use: plug in and go, no setup required
- HIC combines easy-to-read temperature with simple capacitive touch buttons
- Advanced security features: alarm settings, setpoint security passcode, and padlock-compatible doors

**Heart**—the heart is the health status for the freezer



**Easy-to-read alerts**

- Alarm bell**—indicates visual and audible alarms
- Door**—illuminates during a door ajar alarm
- Wrench**—generic service warning
- Thermometer**—indicates when the cabinet temperature exceeds either warm alarm or cold alarm setpoints

**Easy-to-navigate controls**

- Plus**—increases the value of the selected setting
- Check mark**—saves a change to the selected value
- Minus**—decreases the value of the selected setting
- Settings**—represents the various settings

**Setpoint security**—protect your settings with a 3-digit numeric code



## Ready for connectivity

TDE Series ULT freezer models are compatible with the Thermo Scientific™ DeviceLink™ Connect monitoring system. This enables you to have a connected experience with your unit, so you always know the safety of your samples and the performance of your refrigerator or freezer—anytime, anywhere. The units are also compatible with Thermo Scientific™ Smart-Vue™ Pro wireless monitoring systems.

## Get your ULT freezers connected

The DeviceLink Connect system connects to your **instrument**. The InstrumentConnect app connects to **you**.



## Help improve connectivity with automated data collection, storage, and mobile access

- The DeviceLink Connect monitoring solution allows 24/7 access to data and alarms from monitored lab equipment
- Data are securely stored in the cloud and sent to users via email and mobile phone notifications
- Streamlined dashboard-style reports reduce time spent interpreting data


DeviceLink Connect kit ordering information:

Description	Cat. No.
DeviceLink Connect Remote Monitoring System (Kits*) for ULT freezers	DLCKTULTS101

\* Kit includes a DeviceLink Connect system, 1-year basic monitoring subscription, power cable, commissioner USB, monitoring hardware, and an applicable serial or USB cable.

For more information on the DeviceLink Connect monitoring system, please visit [thermofisher.com/dlc](http://thermofisher.com/dlc).

For more information on the Smart-Vue Pro system, please visit [thermofisher.com/smartvuepro](http://thermofisher.com/smartvuepro).





## Verified sustainability

TDE Series ULT freezers have completed the ACT Environmental Impact Factor Label labeling process, which is designed to address the need of both scientists and procurement specialists for clear, third party–verified information about the environmental impact of laboratory products. The criteria for the ACT label were developed with input from industry experts and external stakeholders, and the label process entails third-party verification of the sustainable impacts of a product, its operations, and its end of life. For additional information on the ACT label, go to [thermofisher.com/actlabel](http://thermofisher.com/actlabel).

## User-friendly cabinet design

- Ergonomic design: single-hand operation with lockable door handle for easy and secure access to samples
- Flat top workspace for quick access to hands-free operation
- Casters for easy mobility; all are lockable to safely secure unit into place
- Easy-to-access USB for simplified service



## A sound environment

You know that the constant noise created by compressors can compromise communications and create a less-than-ideal working environment. TDE Series ULT freezers are up to 10x quieter than our previous generation of ULT freezers.\*



### Decibel scale of common sounds

Noise source	Decibel level
Freeway traffic, vacuum cleaner	70
Conversation in restaurant, office, background music	60
TDE Series ULT freezers	50
Library	40
Quiet rural area	30
Rustling leaves	22
Breathing	10

\* Thermo Scientific™ TDE60086FA model compared to Thermo Scientific™ Revco™ UXF60086FA model.

# TDE Series -80°C ULT upright freezers

Thermo Scientific™ TDE Series -80°C ULT upright freezers, powered by the H-Drive system, are designed for efficiency. As a result, the series enables a foundational ULT experience with the reliability and performance needed to protect your work—and the sustainability to meet global compliance.



## Performance data

Model series	Energy consumption* (kWh/day)	Peak variation from -80°C setpoint (°C)**	60 second door opening recovery time (minutes)	Warm-up time (-80°C to -50°C) (minutes)†	Noise level (dBA)
TDE30086	11.2	+7.2 / -6.1	13	255	51.5
TDE40086	12.9	+6.0 / -4.0	16	277	50.8
TDE50086	12.8	+4.5 / -3.2	21	302	50.0
TDE60086	13.6	+4.6 / -3.3	22	343	50.5

\* Energy consumption: Typical data based on internal testing with freezer setpoint at -80°C and 20°C ambient temperature.

\*\* Peak variation from setpoint: Typical data based on internal testing with freezer setpoint at -80°C and 20°C ambient temperature.

† Warm-up time: Typical freezer data based on internal testing with empty freezer setpoint at -80°C and ambient temperature at 20°C.

## Upright freezers (-50°C to -86°C)

General-purpose model	Capacity		Electrical	Amps/breaker (plug type)	Max shelf weight lbs. (kg)	Interior dimensions H x W x D in. (cm)	Exterior dimensions H x W* x D in. (cm)	Shipping weight lbs. (kg)
	Cu. ft. (L)	Cryoboxes (2 in.)						
TDE30086FA	14.9 (422)	300	115V/60Hz	12.6/20 (NEMA 5-20)	125 (57)	51.2 x 17.8 x 28.3 (130.1 x 45.2 x 71.9)	78.0 x 23.0 x 38.5 (198.1 x 58.4 x 97.7)	712 (323)
TDE30086FD			208-230V/60Hz	5.6/15 (NEMA 6-15)				
TDE40086FA	19.4 (549)	400	115V/60Hz	13.0/20 (NEMA 5-20)	165 (75)	51.2 x 23.1 x 28.3 (130.1 x 58.8 x 71.9)	78.0 x 28.3 x 38.5 (198.1 x 71.9 x 97.7)	687 (312)
TDE40086FD			208-230V/60Hz	5.9/15 (NEMA 6-15)				
TDE50086FA	24.1 (682)	500	115V/60Hz	12.5/20 (NEMA 5-20)	205 (93)	51.2 x 28.8 x 28.3 (130.1 x 73.0 x 71.9)	78.0 x 34.0 x 38.5** (198.1 x 86.4 x 97.7)	734 (333)
TDE50086FD			208-230V/60Hz	5.0/15 (NEMA 6-15)				
TDE60086FA	28.8 (816)	600	115V/60Hz	12.7/20 (NEMA 5-20)	245 (111)	51.2 x 34.4 x 28.3 (130.1 x 87.3 x 71.9)	78.0 x 39.6 x 38.5** (198.1 x 100.6 x 97.7)	820 (372)
TDE60086FD			208-230V/60Hz	6.2/15 (NEMA 6-15)				

\* Allowance for handle and hinge, add 4.2 in. (10.7 cm) to cabinet width.

\*\* Doorway width clearance is 34.5 in. (87.6 cm) for TDE50086 and TDE60086 models.

## Upright medical device freezers (-50°C to -86°C)

Medical device model	Capacity		Electrical	Amps/breaker (plug type)	Max shelf weight lbs. (kg)	Interior dimensions H x W x D in. (cm)	Exterior dimensions H x W* x D in. (cm)	Shipping weight lbs. (kg)
	Cu. ft. (L)	Cryoboxes (2 in.)						
TDE30086LA	14.9 (422)	300	115 V/60Hz	12.6/20 (NEMA 5-20)	125 (57)	51.2 x 17.8 x 28.3 (130.1 x 45.2 x 71.9)	78.0 x 23.0 x 38.5 (198.1 x 58.4 x 97.7)	712 (323)
TDE30086LD			208-230V/60Hz	5.6/15 (NEMA 6-15)				
TDE40086LA	19.4 (549)	400	115V/60Hz	13.0/20 (NEMA 5-20)	165 (75)	51.2 x 23.1 x 28.3 (130.1 x 58.8 x 71.9)	78.0 x 28.3 x 38.5 (198.1 x 71.9 x 97.7)	687 (312)
TDE40086LD			208-230V/60Hz	5.9/15 (NEMA 6-15)				
TDE50086LA	24.1 (682)	500	115V/60Hz	12.5/20 (NEMA 5-20)	205 (93)	51.2 x 28.8 x 28.3 (130.1 x 73.0 x 71.9)	78.0 x 34.0 x 38.5** (198.1 x 86.4 x 97.7)	734 (333)
TDE50086LD			208-230V/60Hz	5.0/15 (NEMA 6-15)				
TDE60086LA	28.8 (816)	600	115V/60Hz	12.7/20 (NEMA 5-20)	245 (111)	51.2 x 34.4 x 28.3 (130.1 x 87.3 x 71.9)	78.0 x 39.6 x 38.5** (198.1 x 100.6 x 97.7)	820 (372)
TDE60086LD			208-230V/60Hz	6.2/15 (NEMA 6-15)				

\* Allowance for handle and hinge, add 4.2 in. (10.7 cm) to cabinet width.

\*\* Doorway width clearance is 34.5 in. (87.6 cm) for TDE50086 and TDE60086 models.

# TDE Series –80°C ULT chest freezers

Thermo Scientific™ TDE Series –80°C ULT chest freezers, powered by the H-Drive system, enable the same excellent experience as our ULT upright freezers, with an additional benefit of enhanced performance. The combination of our ULT chest freezers' rapid door open recovery and tight peak variation make them perfect for frequent entry or long-term storage applications.



## Performance data

Model series	Energy consumption* (kWh/day)	Peak variation from –80°C setpoint (°C)**	60-second door opening recovery time (minutes)	Warm-up time (–80°C to –50°C) (minutes)†	Noise level (dBA)
TDEC06386	6.6	+5.1/-3.6	1	141	50.9
TDEC25286	9.4	5.2/-3.4	3	134	55.5
TDEC39686	11	5.2/-2.8	1	162	52.9

## Specifications for chest freezers (–50°C to –86°C)

General-purpose model	Capacity		Electrical	Amps/breaker (plug type)	Interior dimensions H x W x D in. (cm)	Exterior dimensions H x W x D in. (cm)	Shipping weight lbs. (kg)
	Cu. ft. (L)	Cryoboxes (2 in.)					
TDEC06386FA	3 (85)	63	115V/60Hz	10.5/20 (NEMA 5–20)	16.4 x 18.4 x 18.4 (41.7 x 46.7 x 46.7)	43.7 x 28.8 x 32.7 (111.0 x 73.2 x 83.1)	380 (172)
TDEC25286FA	13 (360)	252	115V/60Hz	16/20 (NEMA 5–20)	27.8 x 42.4 x 18.5 (70.6 x 107.7 x 47.0)	40.5 x 72.3 x 33.1 (102.9 x 183.6 x 84.1)	710 (322)
TDEC25286FD			203–230V/60Hz	12/15 (NEMA 6–15)			
TDEC39686FA	20 (566)	396	115V/60Hz	16/20 (NEMA 5–20)	27.8 x 66.4 x 18.5 (70.6 x 168.7 x 47.0)	40.5 x 96.3 x 33.1 (102.9 x 244.6 x 84.1)	860 (390)
TDEC39686FD			203–230V/60Hz	12/15 (NEMA 6–15)			

## Specifications for medical device chest freezers (–50°C to –86°C)

Medical device model	Capacity		Electrical	Amps/breaker (plug type)	Interior dimensions H x W x D in. (cm)	Exterior dimensions H x W x D in. (cm)	Shipping weight lbs. (kg)
	Cu. ft. (L)	Cryoboxes (2 in.)					
TDEC06386LA	3 (85)	63	115V/60Hz	10.5/20 (NEMA 5–20)	16.4 x 18.4 x 18.4 (41.7 x 46.7 x 46.7)	43.7 x 28.8 x 32.7 (111.0 x 73.2 x 83.1)	380 (172)
TDEC25286LA	13 (360)	252	115V/60Hz	16/20 (NEMA 5–20)	27.8 x 42.4 x 18.5 (70.6 x 107.7 x 47.0)	40.5 x 72.3 x 33.1 (102.9 x 183.6 x 84.1)	710 (322)
TDEC25286LD			203–230V/60Hz	12/15 (NEMA 6–15)			
TDEC39686LA	20 (566)	396	115V/60Hz	16/20 (NEMA 5–20)	27.8 x 66.4 x 18.5 (70.6 x 168.7 x 47.0)	40.5 x 96.3 x 33.1 (102.9 x 244.6 x 84.1)	860 (390)
TDEC39686LD			203–230V/60Hz	12/15 (NEMA 6–15)			

\* Energy consumption: Typical data based on internal testing with freezer setpoint at –80°C and 20°C ambient temperature.

\*\* Peak variation from setpoint: Typical data based on internal testing with freezer setpoint at –80°C and 20°C ambient temperature.

† Warm-up time: Typical freezer data based on internal testing with empty freezer setpoint at –80°C and ambient temperature at 20°C.

# TDE Series -40°C ULT upright freezers

Thermo Scientific™ TDE Series -40°C ULT freezers, powered by the H-Drive system, bring the excellent experience you'd expect from our -80°C freezers but tuned specifically for the performance required between -10°C and -40°C.



## Performance data

General-purpose model	Energy consumption* (kWh/day)	Peak variation from -40°C setpoint (°C)**	60-second door opening recovery time (min)†	Warm-up time (-40°C to -20°C) (min)‡	Sound (dBA)
TDE40040FA	5.2	+2.6/-2.2	20	300	49
TDE40040FD	4.4	+3.4/-1.5	18	314	52
TDE50040FA	5.3	+3.0/-2.4	24	350	51
TDE50040FD	5.1	+2.2/-2.2	25	318	48
TDE60040FA	6.0	+1.4/-2.4	23	384	49
TDE60040FD	5.9	+1.5/-1.9	25	362	49

\* Energy consumption: Typical data based on internal testing with freezer setpoints at -40°C and 20°C ambient temperature.

\*\* Peak variation from setpoint: Typical data based on internal testing with freezer setpoint at -40°C and 20°C ambient temperature.

† Door opening recovery: Typical data—internal recovery testing is -38.5°C. During the door opening, all inner and outer doors are opened for 60 seconds.

‡ Warm-up time: Typical data based on internal testing with empty freezer setpoint at -40°C and ambient temperature at 20°C.

For specific model performance data, please refer to the individual technical specification sheet for the desired model.

## Specifications for upright freezers (-10°C to -40°C)

General-purpose model	Capacity		Electrical	Amps/breaker (plug type)	Max shelf weight lbs. (kg)	Interior dimensions H x W x D in. (cm)	Exterior dimensions H x W* x D in. (cm)	Shipping weight lbs. (kg)
	Cu. ft. (L)	Cryoboxes (2 in.)						
TDE40040FA	19.4 (549)	400	115V/60Hz	7.2/20 (NEMA 5-20)	165 (75)	51.2 x 17.8 x 28.3 (130.1 x 45.2 x 71.9)	78.0 x 28.3 x 38.5 (198.1 x 71.9 x 97.7)	642 (292)
TDE40040FD			208-230V/60Hz	3.4/15 (NEMA 6-15)				
TDE50040FA	24.1 (682)	500	115V/60Hz	7.5/20 (NEMA 5-20)	205 (93)	51.2 x 28.8 x 28.3 (130.1 x 73.0 x 71.9)	78.0 x 34.0 x 38.5 (198.1 x 86.4 x 97.7)	668 (304)
TDE50040FD			208-230V/60Hz	4.0/15 (NEMA 6-15)				
TDE60040FA	28.8 (816)	600	115V/60Hz	7.5/20 (NEMA 5-20)	245 (111)	51.2 x 34.4 x 28.3 (130.1 x 87.3 x 71.9)	78.0 x 39.6 x 38.5** (198.1 x 100.6 x 97.7)	765 (348)
TDE60040FD			208-230V/60Hz	4.0/15 (NEMA 6-15)				

\* Allowance for handle and hinge, add 4.2 in. (10.7 cm) to cabinet width.

\*\* Doorway width clearance is 34.5 in. (87.6 cm) for TDE50040 and TDE60040.



# TDE Series ULT upright freezers— options and accessories

Options (field installations must be performed by a qualified professional)

Description	Installation	Model series			
		TDE30086	TDE40086	TDE50086	TDE60086
<b>LN<sub>2</sub> Backup System</b> Maintains temperature down to –80°C with liquid nitrogen. Models for TDE30086 are stand-alone.	Factory	N/A	LN4567	LN4567	LN4567
	Field	FLN300A* FLN300D**	FLN456LEA* FLN456LED**	FLN456LEA* FLN456LED**	FLN456LEA* FLN456LED**
<b>CO<sub>2</sub> Backup System</b> Maintains temperature down to –67°C with CO <sub>2</sub> . Models for TDE30086 are stand-alone.	Factory	N/A	CO4567	CO4567	CO4567
	Field	FCO300A* FCO300D**	FCO456LEA* FCO456LED**	FCO456LEA* FCO456LED**	FCO456LEA* FCO456LED**
<b>TSX Pro Series User Interface Option</b> (only available for upright models)	Factory	UI34567H	UI34567H	UI34567H	UI34567H
<b>Chart Recorder (Inkless)</b> Seven-day inkless recorder Range: –115°C to +50°C (+5°C resolution) Dia.: 6 in. (15.2 cm)	Factory	N/A	N/A	CR4567	CR4567
	Field	N/A	N/A	FCR500LE	FCR600LE
<b>Chart Recorder (Ink)</b> Seven-day ink recorder Range: –100°C to +38°C (+2°C resolution) Dia.: 6 in. (15.2 cm) Models for TDE30086 and TDE40086 are stand-alone.	Factory	N/A	N/A	CRP4567	CRP4567
	Field	6383-6A* 6383-6D**	6383-6A* 6383-6D**	FCRP500LE	FCRP600LE
<b>Revco Five Inner Door Configuration</b>	Factory	5D300	5D400	5D500	5D600
<b>Stainless Steel Freezer Interior</b>	Factory	SS34567	SS34567	SS34567	SS34567
<b>Twist Lock Plug</b> NEMA L6–15P for 208–230V/60Hz	Factory	US230V15ATL	US230V15ATL	US230V15ATL	US230V15ATL
	Field	TL230V15A	TL230V15A	TL230V15A	TL230V15A
<b>Twist Lock Plug</b> NEMA L6–20P for 208–230V/60Hz	Factory	US230V20ATL	US230V20ATL	US230V20ATL	US230V20ATL
	Field	TL230V20A	TL230V20A	TL230V20A	TL230V20A

\* A = 115V/60Hz (NEMA 5-20 plug).

\*\* D = 208–230V/60Hz (NEMA 6-15 plug).



## Accessories

Description	Model series			
	TDE30086	TDE40086	TDE50086	TDE60086
<b>Air Filter (Replacement)</b>	AF34567LE	AF34567LE	AF34567LE	AF34567LE
<b>Alarm Delay Module</b> Eliminates nuisance alarms due to intermittent or transitory conditions. (The alarm conditions must exist for a user-defined period before the signal is broadcast.)	6903	6903	6903	6903
<b>Battery Backup (Replacement)</b>	400159	400159	400159	400159
<b>Chart Paper, for Inkless Recorder, 50/Pack</b>	N/A	N/A	6185	6185
<b>Chart Paper, for Ink Recorder, 50/Pack</b>	17020	17020	17020	17020
<b>Cryo Gloves, Medium</b>	4425	4425	4425	4425
<b>Cryo Gloves, Large</b>	4426	4426	4426	4426
<b>Seismic Restraint Kits</b>	TF-ULT300	TF-ULT400	TF-ULT500	TF-ULT600
<b>Shelf Kits: Include One Shelf and Clips</b>	SK300	SK400	SK500	SK600



Cord description	Model
NEMA 5–20 125V/20A	US125V20A
NEMA 6–20 230V/15A	US230V15A
Argentina 230V/16A	AR230V16A
Australia 230V/16A	AU230V16A
Brazil 230V/16A	BR230V16A
China 230V/16A	CH230V16A
Denmark 230V/16A	DK230V16A
Continental EU 230V/16A	EU230V16A
India 230V/16A	IN230V16A
Israel 230V/16A	IS230V16A
Italy 230V/16A	IT230V16A
Japan 125V/20A	JP125V20A
Japan 250V/15A	JP250V15A
Switzerland 230V/16A	SW230V16A
UK 230V/13A	UK230V13A

# Racks for boxes and microplates

## Racks for 5 cm boxes

Description	Dimensions H x W x D cm	Storage capacities	Model series				Cat. No.
			TDE30086	TDE40086	TDE50086	TDE60086	
Sliding drawer rack	30.2 x 14.0 x 68.3	Boxes/rack	25	25	25	25	 920090
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Boxes/freezer	300	400	500	600	
Adjustable side access rack	29.5 x 13.7 x 67.9	Boxes/rack	25	25	25	25	 1950520
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Boxes/freezer	300	400	500	600	




## Racks for 7.62 cm boxes

Description	Dimensions H x W x D cm	Storage capacities	Model series				Cat. No.
			TDE30086	TDE40086	TDE50086	TDE60086	
Sliding drawer rack	30.2 x 14.0 x 68.3	Boxes/rack	15	15	15	15	 920091
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Boxes/freezer	180	240	300	360	
Adjustable side access rack for 3 in. boxes	29.5 x 13.7 x 67.9	Boxes/rack	15	15	15	15	 1950521
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Boxes/freezer	180	240	300	360	

## Racking shelf kits

Description	Storage capacities	Model series			
		TDE30086	TDE40086	TDE50086	TDE60086
	Cat. No.	RSK300SD4	RSK400SD4	RSK500SD4	RSK600SD4
Sliding drawer racks with boxes for one shelf (12.7 x 12.7 x 5.0 cm boxes with 100-count cell dividers)	Racks included	3	4	5	6
	Boxes included	75	100	125	150

## Racks for standard or deep-well microplates

Description	Dimensions H x W x D cm	Storage capacities	Model series				Cat. No.
			TDE30086	TDE40086	TDE50086	TDE60086	
Side access rack with locking rod	30.2 x 14.0 x 65.3	Plates/rack	147	147	147	147	 1950592
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Plates/freezer	1,764	2,352	2,940	3,528	
Side access microplate rack	30.2 x 14.0 x 65.3	Plates/rack	98	98	98	98	 1950523
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Plates/freezer	1,260	1,680	2,100	2,520	
Sliding drawer microplate rack	30.2 x 14.0 x 66.3	Plates/rack	35	35	35	35	 1950642
		Racks/shelf	3	4	5	6	
		Racks/freezer	12	16	20	24	
		Plates/freezer	420	560	700	840	

## Boxes and dividers

Description	No. of dividers	Quantity	Color	Cat. No.
Thermo Scientific™ Nalgene™ polycarbonate 5.08 cm box for 1.2 to 2.0 mL vials	81	24/case	White	5026-0909
5.08 cm fiberboard box	0	12/pack	White	5954
5.08 cm fiberboard box	81	1	White	820002
5.08 cm fiberboard box	100	1	White	820109
7.62 cm fiberboard box	0	12/pack	White	5956
7.62 cm fiberboard box	81	1	White	820003
5.08 cm fiberboard box	0	12/pack	Multiple	1950878
5.08 cm fiberboard box	0	12/pack	Pink	1950879
5.08 cm fiberboard box	0	12/pack	Red	1950880
5.08 cm fiberboard box	0	12/pack	Yellow	1950881
5.08 cm fiberboard box	0	12/pack	Green	1950882
5.08 cm fiberboard box	0	12/pack	Blue	1950883
5.08 cm fiberboard box	0	12/pack	Black	1950884

## Fiberboard dividers

Description	Quantity/pack	Cat. No.
Grid dividers, hold 100 x 12 mm tubes/vials	12	5958
Grid dividers, hold 81 x 13 mm tubes/vials	12	6212
Grid dividers, hold 64 x 14 mm tubes/vials	12	5960
Grid dividers, hold 49 x 16 mm tubes/vials	12	5959

# TDE Series ULT chest freezers— options and accessories







## Accessories

Description	Installation	Model series		
		TDEC06386	TDEC25286	TDEC39686
LN <sub>2</sub> Backup System, maintains temperature down to -80°C with liquid nitrogen	Factory	332353G01	332353G05	332353G05
	Field	FLN743A*	FLN744A*/FLN744D**	FLN744A*/FLN744D**
CO <sub>2</sub> Backup System, maintains temperature down to -70°C with CO <sub>2</sub>	Factory	332353G02	332353G06	332353G06
	Field	FCO743A*	FCO744A*/FCO744D**	FCO744A*/FCO744D**
Chart Recorder (Inkless), 7-day inkless recorder Range: -115°C to +50°C (+5°C resolution) Diameter: 6 in. (15.2 cm)	Factory	332791G01	332166G01	332166G01
	Field	FCR741	FCR742	FCR742
Chart Recorder (Ink), 7-day ink recorder Range: -115°C to +50°C (+5°C resolution) Diameter: 6 in. (15.2 cm)	Factory	332791G02	332166G02	332166G02
	Field	FCR741INK	FCR742INK	FCR742INK

\* A = 115V/60Hz (NEMA 5-20 plug).

\*\* D = 208–230V/60Hz (NEMA 6-15 plug).

Description	Cat. No.
Replacement Air Filter Chest Freezers (quantity of 5)	332297H02
Replacement Backup Battery	400159
Chart Paper, for Inkless Recorder, 50/pack	90520H07
Chart Paper, for Ink Recorder, 50/pack	17020
Cryo Gloves, medium	4425
Cryo Gloves, large	4426

	Description/dimensions H x W x D in. (cm)	Freezer capacity cu. ft. (liters)	Boxes/racks (plates)	Racks/freezer (plates)	Boxes/freezer (plates)	Cat. No.
	2 in. Box Rack - Side Access Rack (Tower), 15.2 x 5.5 x 5.5 (38.6 x 14.0 x 14.0)	3 (85)	7	9	63	398184
	3 in. Box Rack - Side Access Rack (Tower), 16.0 x 5.5 x 5.6 (40.6 x 14.0 x 14.2)	3 (85)	5	9	45	398185
	2 in. Box Rack - Side Access Rack (Tower), 26.5 x 5.5 x 5.5 (67.3 x 14.0 x 14.0)	13 (360)	12	21	252	398186
		20 (566)	12	33	396	
	3 in. Box Rack - Side Access Rack (Tower), 26.3 x 5.5 x 5.6 (66.8 x 14.0 x 14.2)	13 (360)	8	21	168	398187
		20 (566)	8	33	264	
	Microplate Rack, 26.5 x 5.5 x 5.5 (67.3 x 14.0 x 14.0)	13 (360)	27	21	567	398188
		20 (566)	27	33	891	
	Wire Basket with Rollers* 12.3 x 16.5 x 11.8 (31.2 x 41.9 x 29.9)	13 (360)	NA	5	NA	114048
		20 (566)	NA	9	NA	

\* Basket rail set is required: Cat. No. 189001 for 360 L chest and Cat. No. 189000 for 566 L chest.

# Services

## Certificate of calibration

Control, alarm, and temperature recording systems are systematically calibrated at the factory for accurate performance. An optional certificate of calibration to a NIST (National Institute of Standards and Technology, formerly National Bureau of Standards)-traceable instrument includes a model number and serial number certificate (single-point calibration). Multiple-point calibration is also available. Calibration certificates must be requested when ordering. For details, contact your sales representative.

## Validation testing program

Validation testing services ordered in advance of shipment may accelerate in-house installation qualification (IQ) and operation qualification (OQ) programs. Validation services include documentation and performance reports, compressor and subsystem component specifications, microprocessor flow diagrams, software specifications, and more. For more details, contact your sales representative.

Services description	Cat. No.
Temperature mapping of 24 hours at setpoint to include: <ul style="list-style-type: none"> <li>• Mapping data graphed at each location</li> <li>• Thermocouple placement diagram</li> <li>• Test equipment list</li> <li>• Average uniformity and stability at specified cycle</li> <li>• Minimum, average, and maximum temperatures at each thermocouple location</li> <li>• Uniformity and stability at each location</li> </ul>	74554TA
Temperature mapping of 24 hours (traceable instruments and raw data) at setpoint to include: <ul style="list-style-type: none"> <li>• Mapping data graphed at each location</li> <li>• Thermocouple placement diagram</li> <li>• Test equipment list utilizing Kaye Validator™ thermal validation equipment</li> <li>• Calibration certificates of test equipment</li> <li>• Thermocouple calibration reports</li> <li>• Average uniformity and stability at specified cycle</li> <li>• Minimum, average, and maximum temperatures at each thermocouple location</li> <li>• Uniformity and stability at each location</li> </ul>	7456TA
Certificate of verification	6916-2
Factory quality control test log report	6916-4
Factory quality control test temperature graphs	6916-5
Calibration certificate (chest)	260029
Certificate of conformance (chest)	260043
Unit-specific calibration certificate (chest)	260049

Note: Selected models require calibration certificate for NSF 456 vaccine standard labeling.



## Also available: Thermo Scientific™ TSX™ Universal Series ULT freezers

Designed to meet the highest protection and sustainability standards for storage at ultra-low temperatures

Find out more at [thermofisher.com/ult](https://thermofisher.com/ult)

thermo scientific

**For Laboratory Use. It is the customer's responsibility to ensure that the performance of the product is suitable for customers' specific uses or applications.** © 2022, 2024 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. ENERGY STAR and the ENERGY STAR mark are trademarks owned by the U.S. Environmental Protection Agency. ACT is a trademark of My Green Lab. Kaye Validator is a trademark of Amphenol Corporate. COL35993 0524