

Catalog #: LHC4011 **Lot #:*** 1472509

***Note:** A letter at the end of the lot number signifies an additional packaging of this same lot.

Product Use

This kit is comprised of components for the measurement of human IFN- α in plasma or tissue culture supernatant. The assay may be run alone or in combination with other singleplex bead kits from Life Technologies[™]. Buffer reagents needed to complete the reaction are sold separately under Catalog #LHB0001. These reagents are intended for use in the **Luminex[®] 100[™]/200[™]** and the **FLEXMAP 3D[®]** System. **This kit is configured for research use only and is not to be used in diagnostic procedures.**

Reagents Provided

Hu IFN- α

1. **Part #:** LM071 **Description:** Antibody Bead Concentrate (10X) **Lot:** 1472511 **Size:** 0.25 mL-100 tests

Bead Region: 17

Form: 0.25 mL 10X bead concentrate solution in storage buffer. Contains 0.05% sodium azide as a preservative.

Storage: **Light-sensitive material.** Store at 2 to 8°C in the dark, until the expiration date indicated on the kit.

Hu IFN- α

2. **Part #:** BN071 **Description:** Biotinylated Ab Conc. (10X) **Lot:** 1472510 **Size:** 1 mL-100 tests

Form: 1 mL of a 10X stock of Biotinylated Antibody Concentrate in Biotin Diluent. Contains 0.1% sodium azide as preservative. Concentration of antibody is matched to this lot of beads. Do not mix lots of coated beads and detection antibody.

Storage: Store at 2 to 8°C until the expiration date indicated on the kit.

3. **Part #:** SM311 **Description:** Hu 16-Plex Standard **Lot:** 1388776 **Size:** 2 Vials

Form: Lyophilized. The proteins in this standard have been calibrated against the mass of highly purified recombinant protein, with the respective Life Technologies[™] ELISA kit, and NIBSC calibration standard (if available). Contains 0.1% sodium azide as a preservative.

Storage: Store at 2 to 8°C. Use within 1 hour after reconstitution. Discard immediately after use.

Concentration of Reconstituted Standard**:








IL-1 β (8,800 pg/mL)	IL-10 (22,050 pg/mL)	IFN- α (13,300 pg/mL)	IL-6 (4,950 pg/mL)
IL-12 (11,200 pg/mL)	IL-13 (19,200 pg/mL)	IL-15 (25,400 pg/mL)	IL-17 (21,950 pg/mL)
GM-CSF (17,700 pg/mL)	IL-5 (5,100 pg/mL)	IFN- γ (11,350 pg/mL)	TNF- α (6,700 pg/mL)
IL-2 (10,900 pg/mL)	IL-7 (6,300 pg/mL)	IL-4 (42,600 pg/mL)	IL-8 (10,500 pg/mL)

****Important note:** The concentrations of reconstituted standard are lot-specific. Please verify all concentration values entered in data analysis software.

Reconstitution: Reconstitute with 1 mL Assay Diluent when measuring IFN- α in serum or plasma samples. For other sample types, such as tissue culture supernatants, reconstitute the standard in 1 mL of a solution consisting of 50% Assay Diluent + 50% of sample matrix. Allow standard to rehydrate for approximately 10 minutes before further dilution.

Recommended Starting Concentration for Standard Curve: Upon reconstitution, the starting concentration of standard is the value cited above. Make serial 1:3 dilutions in Assay Diluent (serum/plasma samples) or other appropriate matrix. Use 100 μ L per assay. If establishing a Multiplex Assay, this same standard can be used to measure the other related cytokines cited above in a Multiplex Assay format. Refer to the user manual included in the Buffer Reagent Kit for further information.

Explanation of symbols

Symbol	Description	Symbol	Description	Symbol	Description
	Manufacturer		Catalog number		Batch code
	Use by		Temperature limitation		
	Consult instructions for use		Caution, consult accompanying documents		

For Research Use Only. Not for use in diagnostic procedures.

www.lifetechnologies.com

Life Technologies Corporation • 7335 Executive Way, Frederick, MD 21704 • Tel: 800.955.6288 • E-mail: techsupport@lifetech.com

LHC4011

(Page 1 of 2) MAN0009615 Rev 1.00 Effective Date: 09 OCT 2013

Limited Use Label License: Research Use Only



The purchase of this product conveys to the purchaser the limited, non-transferable right to use the purchased amount of the product only to perform internal research for the sole benefit of the purchaser. No right to resell this product or any of its components is conveyed expressly, by implication, or by estoppel. This product is for internal research purposes only and is not for use in commercial applications of any kind, including, without limitation, quality control and commercial services such as reporting the results of purchaser's activities for a fee or other form of consideration. For information on obtaining additional rights, please contact outlicensing@lifetech.com or Out Licensing, Life Technologies, 5791 Van Allen Way, Carlsbad, California 92008.

Human IFN- α Singleplex Bead Kit

Technical Data Sheet

Performance Characteristics

Analytical Sensitivity: The minimum detectable dose of Human IFN- α is < 5 pg/mL. This was determined by adding two standard deviations to the mean FI obtained when the zero standard was assayed 16 times.



Typical Standard Curve

Specificity*: Buffered solutions of a panel of substances at 5 or 10 ng/mL were assayed with the Life Technologies™ Human IFN- α Singleplex Bead Kit. The following substances were tested and all were found to have no cross-reactivity: human IL-1 β , IL-2, IL-4, IL-5, IL-6, IL-8, IL-10, IL-12, IL-13, IL-15, EGF, Eotaxin, FGFb, G-CSF, GM-CSF, IFN- γ , MCP-1, MIP-1 α , MIP-1 β , RANTES, TNF- α , and VEGF. This Kit will recognize the following human interferon species: IFN- α A, IFN- α 2, IFN- α A/D, IFN- α C, IFN- α D, IFN- α G, IFN- α J, and IFN- α K. The following human interferon species are not recognized by this kit: IFN- α B2, IFN- α F, IFN- α H, IFN- α I, IFN- β , IFN- γ , and IFN- ω .

Precision*:

	Intra-assay (n=24)	Inter-assay (n=46)
Mean (pg/mL)	2045	2089
SD	139	166
%CV	6.8	7.9

Linearity*: Tissue culture medium containing 10% fetal calf serum was spiked with human IFN- α and serially diluted in a solution of 50% Assay Diluent and 50% tissue culture medium. Linear regression analysis revealed a correlation coefficient of 0.99.

Recovery:

Sample type	Results
Serum (Human)	✓
EDTA plasma (Human)	✓
Citrate plasma (Human)	✓
Heparin plasma (Human)	✓
Tissue culture medium with 10% fetal calf serum*	✓

Notes: 70-130% recovery (✓), 50-69% recovery (–), 131-150% recovery (+) and <50% or >150% recovery (NR - Not recommended) *Analysis performed during product development and with first lots produced.

Correlation to ELISA*:

A correlation coefficient of 0.94 was calculated when values for tissue culture medium, obtained with the Human IFN- α Singleplex Bead Kit, were compared to the Life Technologies™ IFN- α ELISA (cat.# KHC4012). Human IFN- α Singleplex Bead Kit (pg/mL) x 1.5 = Hu IFN- α ELISA (pg/mL). Correlation of results obtained with the Human IFN- α Singleplex Bead Kit to one's own system should be determined to arrive at an appropriate multiplication factor.

For Research Use Only. Not for use in diagnostic procedures.

www.lifetechnologies.com

Life Technologies Corporation • 7335 Executive Way, Frederick, MD 21704 • Tel: 800.955.6288 • E-mail: techsupport@lifetech.com

LHC4011

(Page 2 of 2) MAN0009615 Rev 1.00 Effective Date: 09 OCT 2013

Limited Use Label License: Research Use Only

The purchase of this product conveys to the purchaser the limited, non-transferable right to use the purchased amount of the product only to perform internal research for the sole benefit of the purchaser. No right to resell this product or any of its components is conveyed expressly, by implication, or by estoppel. This product is for internal research purposes only and is not for use in commercial applications of any kind, including, without limitation, quality control and commercial services such as reporting the results of purchaser's activities for a fee or other form of consideration. For information on obtaining additional rights, please contact outlicensing@lifetech.com or Out Licensing, Life Technologies, 5791 Van Allen Way, Carlsbad, California 92008.