# **thermo**scientific thermo scientific Thermo Scientific TSG Series Small Capacity

Innovative refrigeration solutions for healthcare and research needs

Refrigerators



## Designed with you in mind

The Thermo Scientific TSG Series powered by solid state refrigeration technology, has been designed to meet the rigorous and demanding needs of healthcare, research and industrial applications where solid performance is required, in support of breastmilk and medication storage, analyzer kits and reagents, and even cell culture media.

The TSG Series brings cutting edge innovation into refrigeration by incorporating solid state technology in place of traditional refrigeration methods—this means that you are not only are able to maintain the most demanding storage conditions but you also can enjoy increased storage capacity meaning you can get more done in less space. All while using less energy and putting almost no heat into the work environment.

#### Available in two sizes:

- TSG205 designed for countertop needs
- TSG505 designed for under-counter needs



Clear intuitive displays for precise temperature control

#### **Model specific features:**

- Remote alarm contacts on the undercounter refrigerator, supporting requirements of research for monitoring
- Datalogging and download capability on countertop models via USB port to support clinical record management requirements
- TSG505 is certified to the NSF/ANSI 456
  Vaccine Storage standard
- Universal voltage on the TSG505, allowing for deployment anywhere 110/230v 50/60Hz power is available



Warranty for both products is 5 years on the solid state refrigeration system and 2 years parts and labor

#### **Key features of both models:**

- Solid state refrigeration technology
- Whisper quiet operation leading to a more comfortable work environment supporting clinical and healthcare needs
- Increased capacities due to fewer refrigeration components means you can store more in less space
- Energy Star rated performance meaning lower operating costs
- Green refrigerants supporting global initiatives to reduce green house gas emissions
- Full alarm set, including hi/lo temperature, door ajar and power fail to support requirements for medical storage

## **Product Specifications**

Therm	Thermo Scientific TSG series small capacity undercounter refrigerator											
Cat. No.	Settable Range	Capacity cu. ft. (liters)	Electrical	Plug Type*	Doors	Shelves	Defrost	Sound Level	Certifications	Interior Dimensions: (D x W x H)	Exterior Dimensions: (D x W x H)	Shipping Weight Ibs. (kg)
TSG505SA	+2°C to +9°C	5.5 (156)	100 - 240v, 50/60hz	NEMA 5-15	1, Solid	3	Auto	43 dBA	SGS, CE, REACH, RoHS, NSF/ANSI 456	19.5 x 20.5 x 23 in. (495x 520x 584 mm)	23.6 x 26 x 32 in. (600 x 660 x 813 mm)	128 (58)
TSG505GA	+2°C to +9°C	5.5 (156)	100 - 240v, 50/60hz	NEMA 5-15	1, Glass	3	Auto	43 dBA	SGS, CE, REACH, RoHS, NSF/ANSI 456	19.5 x 20.5 x 23 in. (495x 520x 584 mm)	23.6 x 26 x 32 in. (600 x 660 x 813 mm)	145 (66)

<sup>\*</sup>All models can accomodate any plug. Contact your sales rep for help determining the appropriate plug/cord type for your facility.



<sup>\*</sup>Regional plug types available

Thermo Scientific TSG series small capacity countertop refrigerator												
Cat. No.	Settable Range	Capacity cu. ft. (liters)	Electrical	Plug Type*	Doors	Shelves	Defrost	Sound Level	Certifications	Interior Dimensions: (D x W x H)	Exterior Dimensions: (D x W x H)	Shipping Weight Ibs. (kg)
TSG205SA	+2°C to +8°C	1.8 (156)	120v, 60hz	NEMA 5-15	1, Solid	3	Auto	36 dBA	TUV	14.3 x 12.2 x 18.4 in. (363 x 310 x 467 mm)	20.5 x 22.1 x 23 in. (521 x 561 x 58.mm)	83 (38)



### **thermo**scientific

#### **Customer installed accessories**

For use with refrigerator size	1.8 cu. ft. (50.9L)	5.5 cu. ft. (156L)		
Description	Cat. No.	Cat. No.		
Rolling Wire Basket		WB05		
Additional Wire Shelf		WS05		
Set of casters with mounting hardware		CS05		
8.5" Roller Base w/Casters	RB02			
Pyxis Lock Bracket-Top Mount	PA02			
Omnicell Flexlock adapter		OF02		
Power Cord 115V	10005	6H01		
Power Cord, D NEMA 6-15P 230V	10009	1H01		
Power Cord, V EU Schuko 230V	10008	9H01		
Power Cord, C China 220V/50Hz	10009	2H01		
Power Cord, W UK Type G-10A 23	100090H01			



Thermo Scientific™ Smart-Vue™ Pro Remote Monitoring System



Thermo Scientific™ Capitol Vial Snappies™ Breast Milk Container System



Thermo Scientific™ Samco™ Clicktainer™ Vials and Specimen Containers

