

# Polypropylene Fume Hood - Wet Scrubber

**NEW!**

TopAir's Polypropylene Fume Hood - Wet Scrubber features a quality scrubbing media which collects mist and chemicals and channels them down to the water tank. Its upper eliminator prevents mist from reaching the exhaust fan.

The fume hood is used to filter out acids and prevent them from being released into the environment. The scrubber is built-in as an integrated part of the hood.

The Polypropylene fume hoods are made of high-quality non-corrosive polypropylene with excellent chemical resistance.

The fume hoods protect laboratory staff from noxious fumes released by acids, dangerous gas and organic solvents- materials and acids which regular steel hoods may not withstand.

The hoods are designed for work with heavy chemicals, have been independently tested, and **EN-14175 / CE / ASHRAE 110-1995 certified.**

## Wet scrubber functionality comprises:

- Spray Nozzles
- Upper Eliminator
- Scrubbing Media
- Water Pump
- Water Tank
- Visual + Audio Alarm for low water level
- Wide surface for extended reach
- Low noise system
- Low pressure drop
- Compact size
- Easy access for maintenance and repairs
- Control panel including on/off unit power and light switch, with an optional VAV system
- **EN-14175, ASHRAE 110-1995, CE certified**



# Models

Spec/Model	FH-120-WS	FH-150-WS	FH-180-WS	FH-200-WS	FH-250-WS
External Dimensions	1200 x 980 x 2370 mm	1500 x 980 x 2370 mm	1800 x 980 x 2370 mm	2000 x 980 x 2370 mm	2500 x 980 x 2370 mm
W x D x H	47.3x 38.6 x 93.3"	59.0 x 38.6 x 93.3"	70.9 x 38.6 x 93.3"	78.7 x 38.6 x 93.3"	98.4 x 38.6 x 93.3"
<b>WE CAN CUSTOMIZE TO ANY SIZE - EVEN A SINGLE UNIT! CONTACT US FOR DETAILS</b>					
Workspace	1000 x 630 x 1000 mm	1300 x 630 x 1000 mm	1600 x 630 x 1000 mm	1800 x 630 x 1000 mm	2300 x 630 x 1000 mm
(W x D x H)	39.4 x 24.8 x 39.4"	51.2 x 24.8 x 39.4"	63 x 24.8 x 39.4"	70.8 x 24.8 x 39.4"	90.5 x 24.8 x 39.4"
Front Sash Max Opening	720 mm / 28.3"	720 mm / 28.3"	720 mm / 28.3"	720 mm / 28.3"	720 mm / 28.3"
Production / test Standard	EN-14175 / ASHRAE 110-1995				
Air Velocity	0.5±0.1 m/s, 100±20 FPM				
Hood Material	White Polypropylene				
Work Table Material	HPL/ Ceramic / Epoxy / PP / Stainless steel				
Optional Control System	VAV System with 9" color touch screen				
Optional	Water tap/ gas tap / vacuum tap/ pp sink				
Power Supply	110 / 220V, 50/60 Hz, Single/triple phase				
Illumination	800 LUX LED lights				

# Accessories

Description	Model
Kit for Fume Hood includes: 1 water tap, 1 gas tap, 1 cup sink and 4 power outlets	FH-KIT
Gas tap	FH-GTAP
Water tap	FH-WTAP
Polypropylene cup sink	FH-PP-SINK
Polypropylene sink 30 x 40	FH-SINK-3040
Power outlet	FH-SOCKET
Air flow monitor with audible alarm VAV+VFD installed, including 9" LCD touch screen controller	FH-VAV
Centrifugal fan 0.75 kw 2800 RPM/IE3	FH-FAN-750
Centrifugal fan 1.1 KW 2800 RPM/IE3 DIA 300 mm	FH-FAN-1100-300

## Authorised distributor

### In Australia:

For customer service, call 1300-735-292

To fax an order, use 1800-067-639

To email an order, [ordersau@thermofisher.com](mailto:ordersau@thermofisher.com)

### In New Zealand:

For customer service, call 0800-933-966

To fax an order, use 0800-329-246

To email an order, [ordersnz@thermofisher.com](mailto:ordersnz@thermofisher.com)

**ThermoFisher**  
SCIENTIFIC