

## Combination Refrigerator and Freezer S Series

The Pinnacle purpose built Fridge/Freezer has been designed in Australia to meet vaccine storage guidelines. Ideal for pharmacies, hospitals, and laboratories they provide reliable temperature control and are easy to use.

### Features:

- ✓ **+2°C to +8°C Refrigerator Operating Temperature Range and -20°C Freezer**
- ✓ **Digital Controllers**
- ✓ **Alarm System**  
Alarms when door open and/or out of temperature range
- ✓ **Min / Max Temperature Logger**
- ✓ **Building Management System (BMS) Connection**
- ✓ **Fan Forced Cooling\***
- ✓ **Manual Defrost Freezer**
- ✓ **Internal Fan Switch**  
Will turn off fan when door open\*
- ✓ **Energy Efficient and Quiet**
- ✓ **LED Lighting\***
- ✓ **Door Lock**
- ✓ **Cable Port Hole\***
- ✓ **Warranty**  
24 months parts and labour



Product code: PRF-S-200/100-1

### Optional Features:

- Low Temperature Cut-out
- 4G SMS Auto-dialler
- Additional Wire Coated Shelving
- Guardian T Alarm Testing System
- 7 Day Chart Recorder

\*Refrigerator Only



# Combined Refrigerator and Freezer S Series

## Technical Specifications

Model	PRF-S-200/100-1
Storage Capacity (litres)	200L Refrigerator 100L Freezer
Voltage	220 VAC - 240 VAC 50Hz
Amperage	6.5 Amps
Size External (W x D x H)	600mm x 610mm x 1750mm
Weight	100 kg
Refrigerant	R600a
Warranty Labour (refer to full warranty conditions)	24 months
Warranty Parts (refer to full warranty conditions)	24 months
Number of Shelves	Refrigerator: 3 Freezer: 1
Alarm Points	Refrigerator: +2°C to +8°C Freezer: -10°C to -25°C
Digital Controller with LCD Display	
Min / Max Temperature Logging	
Door Open Alarm (Refrigerator Only)	Included
High Temperature Alarm	
Low Temperature Alarm	
Power Loss Alarm	BMS Only
Remote Alarm Contacts (BMS)	Included
Independent Controllers	Included
Cable Port Hole 9.5mm	Included
Fan Forced Cooling	Fan Forced Cooling is for Refrigerator Only
Door Lock and Keys	Included
Self Closing Doors	Included
LED Lighting	LED Lighting is for Refrigerator Only
Defrost	Refrigerator Cyclic Freezer Manual
Guardian T Alarm Testing Facility	Optional
7 Day Chart Recorder	
Low Temperature Cut Out	
Auto Dialler	Optional
Additional Shelving	
Customised Shelving	
Door	Refrigerator Glass Door Freezer Solid Door
External Construction	Powder Coated Steel
Door Hinge Right-hand Open	Standard
Door Hinge Left-hand Open	Not Available
Adjustable Feet	Included (Back Rollers)
Power Cord Length	2.5m

### Authorised distributor

#### In Australia:

For customer service, call 1300-735-292  
To fax an order, use 1800-067-639  
To email an order, ordersau@thermofisher.com

#### In New Zealand:

For customer service, call 0800-933-966  
To fax an order, use 0800-329-246  
To email an order, ordersnz@thermofisher.com