

Fibronectin Ab-11 (Clone FBN11)

Mouse Monoclonal Antibody

Cat. #MS-1351-P0, -P1, or -P (0.1ml, 0.5ml, or 1.0ml at 200µg/ml) (Purified Ab with BSA and Azide)

Cat. #MS-1351-P1ABX or -PABX (0.1ml or 0.2ml at 1.0mg/ml) (Purified Ab without BSA and Azide)

Description: Fibronectin is a dimeric glycoprotein which is present in cells, extracellular matrix, and blood.¹ It possesses at least four binding sites for collagen, glycosaminoglycans, transglutaminase, and a cell surface receptor. Fibronectin is involved in cell adhesion, tissue organization, and wound healing.

Mol. Wt. of Antigen: 440kDa (non-reduced) and 220 (reduced)

Epitope: Not known

Species Reactivity: Human, Mouse and Rat. Others-not known.

Clone Designation: FBN11

Ig Isotype: IgG₁

Immunogen: Recombinant fibronectin protein.

Applications and Suggested Dilutions:

- Immunofluorescence

The optimal dilution for a specific application should be determined by the investigator.

Cellular Localization: Connective tissue matrix and basement membrane

Storage and Stability: Ab with sodium azide is stable for 24 months when stored at 2-8°C. Antibody WITHOUT sodium azide is stable for 36 months when stored at below 0°C.

Supplied As: 200µg/ml of antibody purified from ascites fluid by Protein G chromatography. Prepared in 10mM PBS, pH 7.4, with 0.2% BSA and 0.09% sodium azide. Also available without BSA and azide at 1mg/ml.

Suggested Reference:

1. D'Ardenne AJ, et al. J Clin Pathol 1986; 39:138-44.
2. Kirkpatrick P, et al. J Clin Pathol 1984; 37:639-44.
3. Christensen L. et al. APMIS 1990; 98:615-23.
4. Christiansen BS, et al. Scand J Clin Lab Invest 1988; 48:685-90.

Limitations and Warranty:

Our products are intended FOR RESEARCH USE ONLY and are not approved for clinical diagnosis, drug use or therapeutic procedures. No products are to be construed as a recommendation for use in violation of any patents. We make no representations, warranties or assurances as to the accuracy or completeness of information provided on our data sheets and website. Our warranty is limited to the actual price paid for the product. NeoMarkers is not liable for any property damage, personal injury, time or effort or economic loss caused by our products.

Material Safety Data:

This product is not licensed or approved for administration to humans or to animals other than the experimental animals. Standard Laboratory Practices should be followed when handling this material. The chemical, physical, and toxicological properties of this material have not been thoroughly investigated. Appropriate measures should be taken to avoid skin and eye contact, inhalation, and ingestion. The material contains 0.09% sodium azide as a preservative. Although the quantity of azide is very small, appropriate care should be taken when handling this material as indicated above. The National Institute of Occupational Safety and Health has issued a bulletin citing the potential explosion hazard due to the reaction of sodium azide with copper, lead, brass, or solder in the plumbing systems. Sodium azide forms hydrazoic acid in acidic conditions and should be discarded in a large volume of running water to avoid deposits forming in metal drainage pipes.

For Research Use Only

