Acros Organics BV (Thermo Fisher Scientific)
Janssen Pharmaceuticalaan 3a
Geel,
2440, Belgium

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	41095
Lot Number	A0480626
Description	D(+)-Glucose,ACS reagent,anhydrous
CAS Number	50-99-7
Quality Test/Release Date	09/Feb/2026
Suggested retest date	09/Feb/2031
Country of Origin	CZECH REP.
Declaration of Origin	plant
BSE/TSE	from maize

Result Name	Units	Specifications	Test Value
Appearance (Color)		White	White
Appearance (Form)		Crystalline powder	Crystalline powder
Infrared spectrum		Conforms	Conforms
Loss on drying	%	=<0.2 (105°C, 6 h)	=<0.2 (105°C, 6 h)
Heavy metals (as Pb)	ppm	=<5	=<5
Residue after ignition	%	=<0.02	=<0.02
Specific optical rotation		+52.5° to +53.0° (25°C, 589 nm) (c=10, H2O, NH4OH)	+52.7° (25°C, 589 nm) (c=10, H2O, NH4OH)
Chloride (Cl)	ppm	=<100	=<100
Iron (Fe)	ppm	=<5	=<5
Insoluble matter	%	=<0.005	=<0.005
Titrable acid	meq/g	=<0.002	=<0.002
Starch		Passes test	Passes test
SO4 and SO3 (as SO4)	%	=<0.005	=<0.005

Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.