

Precision manufacturing in plastics

Original equipment manufcaturer (OEM) PCR and qPCR plastics guide

Accuracy and reproducibility

For more than 25 years, we've been at the forefront of innovation in the manufacturing of high-grade plastic consumables, with a focus on providing plastic solutions for molecular biology applications, including PCR and qPCR. The quality and reliability of our products enable you, our customer, to help ensure the accuracy, reproducibility, and validity of your biological data.

We have the essentials to help ensure that your development and manufacturing projects are a success

- State-of-the-art injection molding manufacturing facilities
- Custom development teams help rapidly take ideas from concept through design, prototyping, toolmaking, molding, quality control, and logistics
- Expertise in manufacturing with a wide range of polymers
- Product assembly and packing know-how to deliver what you need, with the option to either receive white-box products or to define your own requirements for custom manufacturing, barcoding, packaging, and/or labeling
- Quality systems to respond to your evolving requirements with rigorous documentation for the supply chain, manufacturing, and quality control processes
- Dedicated account representatives to provide you with world-class customer service

Manufacturing designed to eliminate contaminants at the source, providing you with peace of mind

- All plastic consumables are produced in injection-molding facilities that meet 10,000 or 100,000 clean room (ISO 4 or 5 clean room) standards
- Virgin polypropylene
- Primary packaging is contained within a class 10,000 or 100,000 clean room
- Production runs 24/7 according to ISO 9001 guidelines, with complete traceability and process controls



Innovative product design

of the tube and increasing the

signal-to-noise ratio.



Evaporation protection

Raised rim design around each well enables secure sealing, and safeguards against evaporation.



Definitive quality control, adapted to your needs

We are ISO 9001–registered, and our quality systems are the cornerstone of our business. Among our rigorous standards of product testing and process controls, we adhere to comprehensive standard operating procedures (SOPs). This includes referencing to assay testing; plastic integrity testing; 24/7 roving QC patrols to help ensure procedural adherence; equipment qualification; process verification; and validation. A controlled raw material supply chain and established vendor partnerships help ensure consistency and security of supply.

- Time-and-date batch segregation of every production run prior to QA release
- On-site coordinate-measuring machines help ensure that tools and moldings adhere to specified product tolerances
- Formalized change control process to help ensure consistency, compliance, and conformance of materials
- Raw material and vendor qualifications that provide security of supply
- Corrective and preventative action systems
- Application-specific testing helps ensure product performance in functional assays, e.g., qPCR and PCR testing, centrifugation, and sealing and storage conditions
- Our employees use these systems in day-to-day activities and take great pride in consistently meeting our customers' requirements and exceeding your expectations for service
- We encourage customers to tour and audit our OEM facilities



Make us a part of your team: contact our licensing and commerical supply specialists at **thermofisher.com/oemplastics**



Custom products

Your product can be tailored to meet both the application and your customer's needs, from the product itself to the label on the box.

Product

- Off-the-shelf options are available for most life science consumables: PCR tubes, strip tubes, 24- to 384-well PCR plates, and a wide range of plate seals
- Any of the off-the-shelf products can be customized to individual requirements, including colored lettering, unique adhesive seal formats, and additional colored stripes on tube strip end tabs, which can be used to indicate different diagnostic tests
- If none of the existing products match your instrument or application, our R&D team will work with you to understand all the product requirements and design a consumable that uniquely fits your platform

Product format

- Standard pack sizes are available for off-the-shelf products; individually wrapped, handy small pack sizes, or bulk options are available for high-throughput users
- All of the products can be supplied in any pack size, from a kit-ready custom component bag containing 5 seals bearing a lot number label to a pack of 5,000 strip tubes ready for reagent loading in your facility

Packaging

- Our standard products are supplied in white boxes with plain, nonbranded labels
- All OEM products can be supplied with any or all of the following customized components:
 - Labels printed in our manufacturing site or supplied to us ready for the final packaging stage
 - Unique lot numbers
 - Product information inserts
 - Certificates of conformity
 - Outer packaging from specific finish to box design



Make us a part of your team: contact our licensing and commerical supply specialists at **thermofisher.com/oemplastics**

Custom design and prototypes

Existing clients spanning the diagnostics, therapeutics, and research markets value our expertise in new product design and prototyping. Our design team delivers creativity with the ability to produce reliable and accurate plastic solutions for scientific applications. The team has an excellent record in bringing innovative, profitable, and highly engineered products to market within customer-defined time frames. Communication is the key. Our designers, engineers, and molecular biologists are ready to listen to your team so we can develop products that meet—and perhaps exceed—your expectations.

Tools we use to design your products

- Premold conceptual designs using SOLIDWORKS[™] 3D CAD software
- Computer-generated stereo lithography apparatus (SLA) to create solid, plastic, 3D objects from CAD drawings
- Rapid prototyping in polypropylene to provide fully functional samples before mold production
- Design for manufacture
- Mold flow analysis
- In-house prototype tooling and testing
- Risk management/FMEA

We develop integrative partnerships with our customers, providing high-quality products and tailored support services from concept through manufacturing scale-up. Whether you are a large corporation or a start-up company, we offer you quality plastics components, quickly and reliably, at any volume. Understanding your requirements is the foundation of our business.



Custom manufacturing

Injection molding is the technique used for the reproducible production of identical, highprecision components. Our engineers are continually improving the technology we use to develop and manufacture products. Molds are made using the latest machine-cutting technology, before being hand-finished by our highly skilled craftsmen. Every new manufacturing project requires the development and creation of a new tool—and we've made hundreds.

We offer:

- Development of custom-made molds and automation, using a design team and tool team that work at the same site
- Trusted quality as pioneers in the manufacturing of thin-walled plastic consumables for PCR-based technologies
- A dedicated project management team to oversee development and maintain customer–client relationships



Custom barcoding services

Tracking of samples is important to many customers, so we offer the ability to have your plates produced with barcode sequences unique to your product, in any common barcode format.

Design the perfect barcoding* solution to fit your unique needs

Choose plates for the ultimate barcoding flexibility

Plate type

Any fully skirted or semi-skirted plate from the entire PCR range

Barcode format

Code 128, Code 39, or Interleaved 2 of 5, with flexible human-readable code position

Label size

Available in standard label sizes or customizable according to requirements

Barcode density Range of dimensions available

Sequence You determine start-to-end sequence and alphanumeric pattern

Positioning Any code on any side, all the same code, or varied

* 1,000 plate minimum orders. Smaller quantities may be possible, but are subject to an order fee. Please inquire.

Barcode format options

		Barcode type											
		Code 128	Code 39	Interleaved 2 of 5									
er	7 mils	A000002	ADDIGOCO2										
Multiplier	10 mils	A0000002	AQOOQ2										
Σ	13 mils	A0000002	ADD2										



PCR tubes and strips

SP-0019, SP-0018 🔻



From top to bottom: SP-1182, SP-0020 🔻



SP-0085 🔻



Individual tubes

- Compatible with standard 0.2 or 0.5 mL thermal cycler blocks
- Caps form a secure seal, yet are easy to open and close
- Height: 20.7 mm, 0.2 mL tube
- Height: 29.75 mm, 0.5 mL tube

Ordering information

0.2 mL in	dividual tubes		0.5 mL individual tubes	
SP-0018	w/Flat Caps	Clear	SP-0021 w/Flat Caps	Clear
SP-0019	w/Domed Caps	Clear	Pack size: 1,000 tubes	
Pack size	: 1,000 tubes			

0.2 mL strip tubes

- Compatible with 0.2 mL thermal cycler blocks
- Caps form a secure seal, yet are easy to apply and remove
- 8 tubes per strip
- Height: 20.7 mm
- Pitch: 9 mm

Ordering information

0.2 mL strip tubes												
SP-1182	w/Flat Caps	Clear										
SP-0020	w/Domed Caps	Clear										
Pack size	: 250 tube strips/c	ap strips										

Low-profile strip tubes

- Ideal strip for reaction volumes below 20 µL
- Compatible with 0.2 mL thermal cycler blocks
 - Low profile to help reduce dead space and increase PCR efficiency
- Labeled A-H end tabs
- Height: 15.5 mm
- Pitch: 9 mm

Ordering information

Low-profile strip tubes

SP-0085Strips of 8 Low-Profile TubesClearPack size:120 tube strips

SP-0036, SP-0035 🔻



24- and 48-Well Semi-Skirted

- Conveniently pre-cut into 24- or 48-well segments
- Semi skirt adds rigidity and allows for labeling or barcoding
- Height: 18.65 mm
- Pitch: 9 mm

.

Ordering information

24-Well Semi-Skirted (Pre-Cut)

SP-0036 Clear Pack size: 50 plates 48-Well Semi-Skirted (Pre-Cut)

SP-0035 Clear Pack size: 50 plates



Available as kit component only.







96-Well PCR Strip Tube Plate

- Strip of eight tubes linked to each other forming the familiar 12 x 8 or 96-well ANSI format
- Tear points between strips enable single or multiple strip requirements for customized experiments
- Maximum fill volume of 0.2 mL

Ordering information

96-Well PCR Strip Tube Plate, 96-Well PCR Strip Tube Plate, Low Profile SP-3800 Clear

Frame, Skirted SP-3805 White Pack size: 25 frames

96-Well Semi-Skirted, Segmented

White

- Proprietary segmented plate design allows plates to be cut • into 24- and 48-well sections
- Semi skirt adds rigidity and allows for labeling or barcoding
- Cut corner: H1

SP-3800/W

Pack size: 25 plates

- Height: 18.65 mm
- Pitch: 9 mm •

Ordering information

96-Well Semi-Skirted, Segmented

SP-0127 Clear

Pack Size: 25 plates

96-Well Non-Skirted, Flexi-Plate

- Segmented into 12 breakable strips
- Standard profile
- Height: 19.3 mm •
- Pitch: 9 mm •

Ordering information

96-Well Non-Skirted, Flexi-Plate

SP-4896 Clear

Pack size: 25 plates

•

Thermo Scientific[™] Armadillo[™] PCR plates / strip plates

- Easily and safely breakable into 8-tube strips
- Certified DNA-, DNase-, and RNase-free
- Optically clear skirt aids in visualization of liquids •

Ordering information

	0							
Armadil	o 96-well PCR Strip Plates							
SP-2396	Full skirt, clear frame, clear wells							
SP-3396	Full skirt, clear frame, white wells							
SP-2496	Low profile, semi-skirt, clear frame, clear wells							
SP-3496	Low profile, semi-skirt, clear frame, white wells							
SP-2596	Semi-skirt, clear frame, clear wells							

SP-3596 Semi-skirt, clear frame, white wells Pack size: 25 plates

SP-2384	Clear frame, clear wells								
SP-3384	Clear frame, white wells								
Pack size: 50 plates									
Armadillo 96-well PCR Strip Plates									
SP-2696	Low-Profile PCR Strip Plate, 96 well, clear								
SP-3696	Low-Profile PCR Strip Plate, 96 well, clear, white well								
SP-2796	PCR Strip Plate, 96 well, clear								
SP-3796	PCR Strip Plate, 96 well, clear, white well								
Pack size: 25 plates									

Armadillo 384-well PCR Plates

Choosing a plate

Please refer to the following compatibility table to find the PCR plate suitable for your instrument. Plate model recommendations are based on the optimal PCR performance and ease of handling. Most recommended plates are either fully skirted or semi-skirted;

these plates offer increased rigidity, which helps reduce plate warping during thermal cycling, facilitates multichannel pipetting, and helps improve overall ease of use.

				Bio-Rad Agilent (MJ Research) (Stratagene) Eppendor					dorf	f Biometra												
			F	PCF	3		qPC	CR	F	PCR		qP	CR	PC	R	qPCR		F	PCF	2		qPCR
Legend • Recommended plate • Alternative option • Validated plate Plate type		ion	96-well block			/iQ2								er ^m EP Gradient/Pro								
			T100, MJ Mini ¹ , PTC-100 ¹ with 96-well block	iCycler [™] , MyCycler [™]	C1000, S1000, PTC-200	iCycler [™] , iQ [™] 4, iQ [™] 5, MyiQ [™] , MyiQ2	CFX96™, Opticon™	CFX384 [™] MiniOatiooo [™]	SureCycler [™] 8800	Robocycler	Gradient Cycler	Mx4000 [™]	Mx3000P [™] , Mx3005P [™]	Mastercycler [™] Gradient, Mastercycler [™] EP Gradient/Pro	M384	Mastercycler [™] ep Realplex	Uno, TRobot	Uno II	T1 Thermocycler	TGradient	TProfessional	TOptical
96-well		Cat. No.																				
Fully skirted	Low-profile	SP-0037, SP-3805*	•		•		•				•			•		•			•	•	•	•
	Fast block	W4346906, W4346907 SP-1900														•						
Semi- skirted	Flat deck Raised skirt	SP-0824 W8010560 SP-0446	•		•							•				•			•	•		
	Segmented	SP-0127	•	٠	•	•					•	•	•	•		•	•		•	•		
Non-skirted	Standard Standard-flexi Low-profile	SP-0074 SP-4896 SP-0029, SP-3800	•	•	•	•	•		•	•	•	•	•	•		•	• •	•	•	•	•	•
24- or 48	-well																					
Semi-skirted		SP-0036, SP-0035														•						
384-well																						
Standard	Standard	W4309849 SP-1384			•			•			•			•	•				•		•	

* SP-3800 or SP-3800/W also required.

Tip

Low-profile versions help minimize the air space above the PCR reaction, further reducing evaporation effects. We recommend that you choose the low-profile options where available.

Additional instruments

Techne					_				PCI	۲					Sequer	icing	9		A	oplie	d Bios	system	IS
	PC	CR	qPCR		Corbett	Gene Technologies	1	лw	G	Takara	Thermo Scientific Hybaid		Thermo Scientific Hybaid		nersham	ΓW	Gene Technologies.	F	PCR			qPCR	
	Flexigene, TC-412, TC-4000	Genius, Touchgene, TC-512, TC-5000, TC-Plus	Prime, PrimeQ	M 0 0	Palm-Cycler	GS1, GS4, GSX	Primus 96	Primus 384	The Q LifeCycler [™]	TP 3000	PCR Express, Px2, PxE, MultiBlock System & MBS ¹¹	Omnigene, Omn-E		MegaBACE [™] 500	MegaBACE ^w 4000	BaseStation [™]	WAVE**	ProFlex", SimpliAmp", Veriti", Veriti" Dx, 2720, 9700	Veriti, Veriti Dx 96-well Fast Block	ProFlex, Veriti, Veriti Dx, 9700 384-well Block	QuantStudio" 3/5/6/7/12K, QuantStudio" Dx, ViiA" 7, ViiA" 7 Dx, 7900HT, 7000, 7300, 7500 96-well Block	QuantStudio 3/5/6/7/12K, ViiA 7, ViiA 7 Dx, 7900HT, 7500, 7500 Dx, StepOnePlus ^w 96-well Fast Block	QuantStudio 3/5/6/7/12K, QuantStudio Dx, ViiA 7, ViiA 7 Dx, 7900HT 384-well Block
		•	•		•	•	•				•	•		•		•	•		•			•	
	•	•																•			•		•
	•	•				•	•		•	•	•	•						•			•		•
	•	•				•	•		•	•	•	•						•					
	•	•	•	(•	•		•	•	•	•											
	•	•				•			•	•	•	•						•					
	-						•		•	•	•												
	•	•				•		•			•			•	•					•			•

PCR plates

SP-1900 🔻



96-Well Fully Skirted, Low Profile

- ANSI footprint and stackable for use in • automated systems
- Low profile to help reduce dead space and increase • PCR efficiency
- Available in a rigid version providing 4x more rigidity for • superior robotic handling
- Cut corner: H1
- Height: 14 mm
- Pitch: 9 mm

Ordering information

96-Well Fully Skirted, Low Profile

SP-0037 Clear Pack size: 25 plates

96-Well Semi-Skirted, Fast Block

- Raised plate deck to aid in spill prevention •
- Compatible with Fast blocks including Applied Biosystems™ instruments-no adapters necessary
- Cut corner: A1 •
- Height: 14.4 mm •
- Pitch: 9 mm

Ordering information

96-Well Semi-Skirted, Fast Block

SP-1900 Clear Pack size: 25 plates



96-Well Semi-Skirted, Flat Deck

- Flat plate deck facilitates sealing and handling •
- Compatible with Applied Biosystems instruments-. no adapters necessary
- Cut corner: A12
- Height: 19.3 mm .
- Pitch: 9 mm •

Ordering information

96-Well Semi-Skirted, Flat Deck

SP-0824	Clear
SP-0824-L	Clear w/black letters
Pack size: 25	plates









96-Well Semi-Skirted, Raised Deck

- Available in a rigid version providing 4x more rigidity for • superior robotic handling
- Compatible with Applied Biosystems instruments-no adapters necessary
- Cut corner: A12
- Height: 19.3 mm
- Pitch: 9 mm •

Ordering information

96-Well Semi-Skirted, Raised Deck

SP-0446	Clear
Pack size: 25 pla	ites

96-Well Non-Skirted, Low Profile

- Low profile to help reduce dead space and increase • PCR efficiency
- Available with black alphanumeric lettering .
- Improved access for liquid handling •
- Maximum well volume: 0.2 mL
- Cut corner: H12
- Height: 13.98 mm
- Pitch: 9 mm

Ordering information

96-Well Non-Skirted, Low Profile

SP-0029 Clear

Pack size: 25 plates

96-Well Non-Skirted, Standard

- Non-skirted format compatible with most thermal cyclers •
- Available with black alphanumeric lettering
- Cut corner: H1
- Height: 19.3 mm .
- Pitch: 9 mm •

Ordering information

96-Well Non-Skirted, Standard

SP-0074	Clear
SP-0074-L	Clear w/black letters
Deals sizes OF	

Pack size: 25 plates

384-Well Plates, Fully Skirted, Standard

- Compatible with all leading 384-block thermal cyclers •
- Maximum well volume: 40 µL
- Cut corner: A24 •
- Height: 8 mm
- Pitch: 4.5 mm

Ordering information

384-Well Fully Skirted, Standard

SP-1384 Clear Pack size: 50 plates

14



Sealing options

We offer a wide range of robust sealing options to suit any application. All of our sealing products are designed for ease of use while providing the ultimate in sample protection.

The qPCR sealing options are optically clear to help deliver maximum and consistent signal transmission, which is critical for accurate qPCR results.

Legend

 Successful 	ly tested

× Not recommended

			PC	R cap strips*		ļ	Adhesive sea	ls	
		Flat cap strips	Domed cap strips	Optical qPCR cap strips	Flat cap mats	Ultra Clear cap mats	PCR foil seal	PCR film seal	Optical qPCR seal
	Cat. No. –	SP-0361 (8 caps per strip)	SP-0075 (8 caps per strip)	SP-0100 (8 caps per strip)	SP-3815 (12 x 8 strips)	SP-3820 (12 x 8 strips)	SP-0028	SP-0027	SP-0605
	Pack size –	250 strips	250 strips	120 strips	25 mats	25 mats	100 sheets	100 sheets	50 sheets
su	PCR (including waterbath)	•	•	•	•	•	•	•	•
atic	qPCR	×	×	•	×	•	×	×	•
Applications	Sealing temp range	-20°C ± 120°C	-40°C ± 120°C	-20°C ± 120°C	-80°C ± 110°C				
Ap	Long-term storage	•	•	•	•	•	•	•	×
Γ	Pierceable	×	×	×	×	×	8.1 N	×	×
ties	Peelable	•	•	•	•	•	•	•	•
peri	Resealable	•	•	•	•	•	•	•	
Mechanical properties	Thickness**						75 µm	255 µm	100 µm
Γ	DMSO (100%)	•	•	•	•	•	•	×	•
e	Ethanol (100%)	•	•	•	•	•	×	×	•
anc	Isopropanol (100%)	•	•	•	•	•	×	×	•
Resistance	Autoclavable	•	•	•	•	•	00000		
Å	UV irradiation	•	•	•	•	•	00000		
	Gamma irradiation	•	•	•	•	•			
tible	Applicator tools	SP-0078	SP-0078	SP-0078			SP-1391	SP-1391	SP-1391
Compatible products	Tubes/plates	8-strip PCR tubes 96-well PCR plates	All plates	All plates	All plates				
						1000 m L.			

* Choose cap shape according to the instrument manufacturer's recommendation.

^{**} Does not include release liner.

Plastics for Applied Biosystems instruments

Applied Biosystems[™] PCR plastics are optimized to provide unmatched temperature accuracy and uniformity for fast and efficient PCR and qPCR applications. Only these plastics are validated and "Engineer-Approved" for use with Applied Biosystems instruments, for optimal fit and performance.

Features of Applied Biosystems plastics:

- All plastics are produced in injection-molding, state-of-the-art facilities that meet 10,000 clean room standards
- ISO 9001- and ISO 13485-certified facilities
- Six Sigma and lean manufacturing processes to help enable the highest quality and lower costs

Tube strips

W4316567 🔻



Custom or no-label packaging

- Production runs 24/7 with complete traceability and process controls
- Customized QC, quantities, and configurations

8-tube strips, 0.2 mL

- Designed for precise PCR and qPCR applications and optimal fit on Applied Biosystems instruments
- Polished surface and conical bottom enable maximum sample recovery
- 8 tubes per strip
- Height: 20.84 mm
- Pitch: 9 mm

Ordering information

0.2 mL tube strips

W4316567	Optical	
Pack size: 125 tube strips		

Plates

W4309849 🔻



384-well plate with barcode

- Maximum well volume: 40 µL
- Cut corner: A24
- Height: 9.71 mm
- Pitch: 4.5 mm

Ordering information

384-well plate with barcode

W4309849 Optical Pack size: 50 plates

16

Plates cont.

W8010560 🔻



W4346907 W4346906



Sealing options

W8010535 W4323032 V



W4306311 W4311971 🔻





96-well plate with no barcode

- Validated to work with Applied Biosystems[™] 96-well qPCR systems and thermal cyclers for consistent, reliable results
- Optimized for well-to-well temperature uniformity
- Maximum well volume: 0.2 mL
- Cut corner: A12
- Height: 20.84 mm
- Pitch: 9 mm

Ordering information

96-well plate with no barcode

W8010560 Optical Pack size: 10 plates

Fast 96-well plate

- Validated to work with Applied Biosystems[™] Fast 96-well instruments
- Optimized for well-to-well temperature uniformity
- Maximum well volume: 0.1 mL
- Cut corner: A12
- Height: 15.94 mm
- Pitch: 9 mm

Ordering information

Fast 96-well plate Fast 96-well plate with barc	
W4346907 Optical	W4346906 Optical
Pack size: 10 plates	Pack size: 20 plates

8-cap strips

- Designed to fit on Applied Biosystems[™] MicroAmp[™] reaction tube strips and 96-well plates; the domed profile is suitable for endpoint PCR, and the optical profile cap strips can be used for both endpoint and qPCR applications
- Provide a tight seal to minimize evaporation

Ordering information

8-cap strips

W8010535	Domed caps	Clear	
W4323032	Optical caps	Clear	
Pack size: 300 strips			

Adhesive film

- Designed to fit on MicroAmp 96-well and 384-well plates
- Reduces the chance of well-to-well contamination and sample evaporation, and helps enable reliable PCR and qPCR results
- Available as Clear (standard PCR use) or Optical (for qPCR analysis)

Ordering information

Adhesive film

W4306311	PCR	
W4311971	qPCR	
Pack size: 10	0 seals	

Customer service

Because maintaining long-term relationships with customers is our goal, we focus on delivering the standard of service that only highly experienced staff members can provide. Committed to communication, we're responsive and we deliver on our promises.

- Your business will be assigned a team with the experience and organizational contacts to accomplish your requirements
- We provide prompt, accurate responses to questions, documentation requests, and technical support
- We take your confidentiality very seriously





Learn more at thermofisher.com/oemplastics

For Research Use Only. Not for use in diagnostic procedures. © 2016–2023 Thermo Fisher Scientific Inc. All rights reserved. All trademarks are the property of Thermo Fisher Scientific and its subsidiaries unless otherwise specified. SOLIDWORKS is a trademark of Dassault Systemes SolidWorks Corp. Mx3000P, Mx3005P, Mx4000, RoboCycler, Gradient Cycler, and SureCycler are trademarks of Agilent Technologies. Flexigene, Genius, Prime, PrimeQ, and Touchgene are trademarks of Bibby Scientific. T1, TAdvanced, TGradient, TOptical, TProfessional, and TRobot are trademarks of Biometra. CFX96, CFX384, iCycler, iCycler iQ, iQ, MiniOpticon, MJ Mini, MyCycler, MyiQ, Opticon, and PTC-100/200 are trademarks of Bio-Rad Laboratories. Mastercycler is a trademark of Eppendorf. Primus and The Q LifeCycler are trademarks of Eurofins Genomics. MegaBACE is a trademark of GE Healthcare. WAVE is a trademark of Transgenomic. BaseStation is a trademark of MJ Research. Palm-Cycler is a trademark of Corbett Life Science. **COL025133 0723**