
thermo scientific



The clear choice for high-quality imaging applications



Flexibility and consistency for cellular imaging and analysis

We offer a wide selection of cell culture consumables with high-quality glass or optical polymer bases for your imaging applications:

- Fluorescence microscopy
- Phase contrast microscopy
- Confocal microscopy
- Super-resolution microscopy
- Differential interference contrast (DIC) microscopy
- Live-cell imaging
- High-content imaging
- Cell-based fluorescence or luminescence assays





Chamber slides

Thermo Scientific™ Nunc™ Lab-Tek™ and Lab-Tek™ II Chamber Slide™ Systems feature removable chambers that allow you to seed, incubate, fix, and stain on a single microscope slide.

- Nunc Lab-Tek Glass Chamber Slide System—
 high-quality soda lime glass with six-stage, high-purity
 wash to facilitate cell attachment
- Nunc Lab-Tek Chamber Slide System, Permanox™
 Plastic—Thermo Scientific™ Nunclon™ Delta—treated
 polymer plastic slide allows reliable attachment of
 adherent cells
- Nunc Lab-Tek II Chamber Slide System, RS Glass highly optical soda lime glass with proprietary RS wash treatment, aids in the attachment of cells to slide
- Nunc Lab-Tek II Chamber Slide System, CC2[™]
 Glass—chemically modified glass provides a growth
 surface with a positive charge that mimics poly-D-lysine
 and aids in the attachment of fastidious cells





Chambered coverglass

Thermo Scientific™ Nunc™ Lab-Tek™ and Lab-Tek™ II Chambered Coverglass features chambers mounted to coverglass for high-magnification microscopy and confocal and live imaging.

- Nunc Lab-Tek Coverglass—1.0 borosilicate glass
- Nunc Lab-Tek II Coverglass—1.5 borosilicate glass



Flasks on slides

Thermo Scientific™ Nunc™ Lab-Tek™ Flasks on Slides are an ideal solution for cell karyotyping using single-cell autoradiography or single-cell immunofluorescence.

- Nunc Lab-Tek Flask on Slide, Flaskette[™] product attached to a glass slide with removable silicone barrier
- Nunc Lab-Tek Flask on Slide, SlideFlask product—ultrasonically welded flask on a removable polystyrene slide




Optical-bottom microplates

Thermo Scientific™ Nunc™ 96- and 384-well optical-bottom plates, with either a thin polymer film bottom or a 1.5 borosilicate glass coverslip bottom, are ideal for plate-based assays and imaging applications. Black microplates are recommended for fluorescence measurements, with minimum back-scattered light and background fluorescence. White plates are best for luminescence measurements, with maximum signal-to-noise (s/n) ratio.

Nunc optical-bottom plates are available with several surface treatment options:

- Nuncion Delta cell culture surface coating promotes cell attachment and is widely used for adherent cell culture
- Poly-D-lysine and collagen surface coatings are designed for primary cells and fastidious cells that are characterized by low adherence or slow growth
- The nontreated hydrophobic polystyrene surface coating is used for suspension cell cultures (e.g., T cells, B cells)





Glass-bottom dishes

Thermo Scientific™ Nunc™ glass-bottom dishes* give you the flexibility to convert your culture device into an imaging device. This means you keep the same seeding density, medium volume, and culture conditions.

The Nunc glass-bottom dish combines the convenience of a standard 35 mm cell culture dish with the imaging benefits of a coverslip to provide the optimum optical characteristics required for high-magnification microscopy and confocal image analysis.

Nunc glass-bottom dishes are ideal for observation at high magnification:

- Fluorescence microscopy
- Phase contrast microscopy
- Confocal microscopy
- Live-cell imaging





Ordering information

Product	No. of wells	Suggested working vol. (mL/well)	Culture area (cm²/well)	Bottom thickness (mm)	Units per pack/case	Cat. No.
	1	2.5-4.5	9.4	1.0-1.2	16/96	177372
Nunc Lab-Tek Chamber Slide System, glass	2	1.2-2.0	4.2	1.0-1.2	16/96	177380
	4	0.5-0.9	1.8	1.0-1.2	16/96	177399
Gyotom, glado	8	0.2-0.4	0.8	1.0-1.2	16/96	177402
	16	0.1-0.2	0.4	1.0-1.2	16/96	178599
	1	2.5-4.5	9.4	1.0-1.2	16/96	177410
Nunc Lab-Tek Chamber Slide	2	1.2-2.0	4.2	1.0-1.2	16/96	177429
System, Permanox plastic	4	0.5-0.9	1.8	1.0-1.2	16/96	177437
	8	0.2-0.4	0.8	1.0-1.2	16/96	177445
	1	2.0-4.5	8.6	1.0-1.2	16/96	154453
Nunc Lab-Tek II Chamber Slide	2	1.0-2.0	4.0	1.0-1.2	16/96	154461
System, RS glass	4	0.5–1.0	1.7	1.0-1.2	16/96	154526
	8	0.2-0.5	0.7	1.0-1.2	16/96	154534
	1	2.0-4.5	8.6	1.0-1.2	16/96	154739
Nunc Lab-Tek II CC2 Chamber	2	1.0-2.0	4.0	1.0-1.2	16/96	154852
Slide System, glass	4	0.5–1.0	1.7	1.0-1.2	16/96	154917
	8	0.2-0.5	0.7	1.0-1.2	16/96	154941
	1	2.5-4.5	9.4	0.13-0.17	16/96	155361
Nunc Lab-Tek Chambered	2	1.2-2.0	4.2	0.13-0.17	16/96	155380
Coverglass, 1.0 borosilicate glass	4	0.5-0.9	1.8	0.13-0.17	16/96	155383
	8	0.2-0.4	0.8	0.13-0.17	16/96	155411
	1	2.5-4.5	8.6	0.16-0.19	16/96	155360
Nunc Lab-Tek II Chambered	2	1.2-2.0	4.0	0.16-0.19	16/96	155379
Coverglass, 1.5 borosilicate glass	4	0.5-1.0	1.7	0.16-0.19	16/96	155382
	8	0.2-0.5	0.7	0.16-0.19	16/96	155409

Product	Description	Slide material	Suggested working vol. (mL/well)	Culture area (cm²/well)	Bottom thickness (mm)	Units per pack/case	Cat. No.
Nunc Lab-Tek Flask on Slide	Flaskette chamber	Glass	2.5-5.0	10	1.0-1.2	16/96	177453
	SlideFlask*	Polystyrene	2.5-5.0	9	1.0-1.2	5/50	170920

^{*} Nunclon Delta-certified.

Product	Description	Dimensions (mm)	Units per pack/case	Cat. No.
Accessory	Glass Coverslip for Cat. No. 178599	22 x 47	-/96	171080
	Glass Coverslip for Cat. No. 170920	18 x 50	100/1,000	171862

		Well		-	Total vol.	.		Bottom	Units per	
Product	Surface	design	Color	Bottom plate	(µL/well)	Sterile	Lid	(mm)	pack/case	Cat. No.
	Poly-D-lysine	96 F	White	Polymer	400	Yes*	Yes	0.25	5/20	152028
	Collagen I	96 F	Black	Polymer	400	Yes*	Yes	0.25	5/20	152036
	Poly-D-lysine	96 F	Black	Polymer	400	Yes*	Yes	0.25	5/20	152037
Nunc Microwell 96-Well Optical-Bottom Plates	Collagen I	96 F	White	Polymer	400	Yes*	Yes	0.25	5/20	152040
with Polymer Base	Cell culture	96 F	Black	Polymer	400	Yes	Yes	0.25	10/30	165305
-,	Cell culture	96 F	White	Polymer	400	Yes	Yes	0.25	10/30	165306
	Nontreated	96 F	Black	Polymer	400	No	No	0.25	10/30	265301
	Nontreated	96 F	White	Polymer	400	No	No	0.25	10/30	265302
	Cell culture	384 F	Black	Polymer	120	Yes	Yes	0.25	10/30	142761
Nunc Microwell 384-Well	Cell culture	384 F	White	Polymer	120	Yes	Yes	0.25	10/30	142762
Optical-Bottom Plates	Poly-D-lysine	384 F	Black	Polymer	120	Yes*	Yes	0.25	5/20	152029
with Polymer Base	Collagen I	384 F	Black	Polymer	120	Yes*	Yes	0.25	5/20	152041
	Nontreated	384 F	Black	Polymer	120	No	No	0.25	10/30	242764
	CC2	96 F	Black	1.5 Coverglass	400	Yes	Yes	0.16-0.19	6/30	160376
Nunc Microwell 96-Well	Cell culture	96 F	Black	1.5 Coverglass	400	Yes	Yes	0.16-0.19	6/30	164588
Optical-Bottom Plates with Coverglass Base	Cell culture	96 F	White	1.5 Coverglass	400	Yes	Yes	0.16-0.19	6/30	164590
	Nontreated	96 F	Black	1.5 Coverglass	400	No	No	0.16-0.19	5/30	265300
Nunc Microwell 384-Well Optical-Bottom Plates with Coverglass Base	Cell culture	384 F	Black	1.5 Coverglass	120	Yes	Yes	0.16-0.19	6/30	164586

^{*} Produced in a clean environment.

Product	Description	Bottom thickness (mm)	Units per pack/case	Cat. No.
Nunc Glass-Bottom Dishes*	12 mm diameter	0.16-0.19	1/20	150680
	27 mm diameter	0.16-0.19	1/20	150682

^{*} Nunc glass-bottom dishes are not available in Japan.

Product	Description	Size	Cat. No.
Cibas call sulture madium for live imaging	FluoroBrite DMEM	500 mL	A1896701
Gibco cell culture medium for live imaging	FluoroBrite DMEM	10 x 500 mL	A1896702

thermo scientific



