

Material No.: 3461-05 Revision No.: 0

## **Product Specification**

Meets B.P. Chemical Specifications, Meets E.P. Chemical Specifications, Meets F.C.C. Requirements, Meets J.P. Chemical Specifications, Meets U.S.P Requirements, GMP Manufactured Product

Test	Specification
USP – Assay (CH₃COONa) (dried basis)	99,0 - 101,0 %
USP - Calcium and Magnesium	Passes Test
USP – Chloride (Cl)	≤ 0,035 %
USP – Endotoxin Concentration (EU/g)	≤ 2,5
USP – Identification	Passes Test
USP – Insoluble Matter	≤ 0,05 %
USP – Loss on Drying	38,0 - 41,0 %
USP - pH of 5% Solution at 25°C	7,5 - 9,2
USP – Potassium (K)	Passes Test
USP – Sulfate (SO <sub>4</sub> )	≤ 0,005 %
EP/BP - Assay (CH₃COONa)	99,0 - 101,0 %
EP/BP – Identification A	Passes Test
EP/BP – Identification B	Passes Test
EP/BP – Identification C	Passes Test
EP/BP - Appearance of Solution	Passes Test
EP/BP - pH (1 in 20)	7,5 - 9,0
EP/BP – Reducing Substances	Passes Test
EP/BP - Chloride (Cl)	≤ 200 ppm
EP/BP - Sulfate (SO <sub>4</sub> )	≤ 200 ppm
EP/BP - Calcium and Magnesium	≤ 50 ppm
EP/BP - Iron (Fe)	≤ 10 ppm
EP/BP – Loss on Drying	39,0 - 40,5 %
JP - Assay (CH3COONa)	99,5 - 101,0 %
JP - Identification	Passes Test
JP - Clarity and Color of Solution	Passes Test
JP – Acidity or Alkalinity	Passes Test
JP – Chloride (Cl)	≤ 0,011 %
JP - Sulfate (SO <sub>4</sub> )	≤ 0,017 %

>>> Continued on page 2 >>>

Sodium Acetate, Trihydrate, Crystal, U.S.P. Multi-Compendial



Material No.: 3461-05

Test	Specification	
JP – Heavy Metals (as Pb)	≤ 10 ppm	
JP – Calcium and Magnesium	Passes Test	
JP – Arsenic (As)	≤ 2 ppm	
JP – Substances Reducing Permanganate	Passes Test	
JP – Loss on Drying	39,0 - 40,5 %	
FCC - Alkalinity	≤ 0,05 %	
FCC - Assay (CH <sub>3</sub> COONa) (dried basis)	99,0 - 101,0 %	
FCC - Identification A	Passes Test	
FCC - Identification B	Passes Test	
FCC – Lead (Pb)	≤ 2 mg/kg	
FCC – Loss on Drying	38,0 - 41,0 %	
FCC - Potassium Compounds	Passes Test	

**GMP Manufactured Product** Food GMP Manufactured Product **Bulk Food Chemical Bulk Pharmaceutical Chemical** 

CAUTION: For Manufacturing, processing or repackaging

No Class 1, 2, 3 or other solvent is likely to be present in the final product.

Elemental Impurities (USP 232, EP 5.20) - Information on elemental impurities for this product is available on the associated

Product Regulatory Data Sheet and elemental impurity profile report.

Storage Condition: Preserve in tight containers, store at room temperature.

Packaging Site: Paris Mfg Ctr & DC

