

PRODUCT SPECIFICATIONS

# Thermo Scientific AutoXP

## Single run gas and liquid flow computer

The Thermo Scientific™ AutoXP instrument is built on the field-proven AutoCONFIG platform. Designed for harsher environments across all oil and gas sectors.

### Features

- Custody transfer compliant
- Bluetooth connectivity
- Through glass keypad interface
- Designed to meet Class I Div 1 and Div 2 requirements

The Thermo Scientific AutoXP has been designed to provide ultimate flexibility by providing a complete suite of measurement calculations along with control functions that enable customers to gain control where they need it most. In addition this unit can be configured for both gas and liquid applications utilizing today's most common primary devices all while meeting Class I Div 1 and Div 2 requirements.

### Inputs/Outputs (Advanced Unit)

- (1) Analog Output
- (2) Analog Inputs
- (2) Pulse/Frequency Inputs
- (2) Digital Outputs
- (2) Digital Inputs
- (1) RTD 3 or 4 Wire




Thermo Scientific™ AutoXP



### AutoCONFIG Configuration Software

Thermo Scientific flow computers are built on an innovative field proven platform incorporating the latest measurement standards and calculations for hydrocarbon measurement. AutoCONFIG interface allows for simplified configuration eliminating need for in-depth programming. Control functions include Station Control, PID, Alarming, Event based logging and many more.



Thermo Scientific™ AutoCONFIG built-in software

## Thermo Scientific™ AutoXP

### General specifications

Processor	32-bit
Program memory	4 MB of flash memory
Data storage memory	SRAM, 2 MB, battery-backed
CPU board communication port	1 RS232, 1 RS232/1 RS485, 1 10Base-T Ethernet port
Input power	10 VDC to 30 VDC
Historical data storage	User configurable, defaulting to 65 days of daily, 35 days of hourly per meter run
Audit trails	User configurable, defaulting to 200 audit events
Alarm log storage	User configurable, defaulting to 200 alarm events
Keypad	4 IR through glass key input
Display	128x65 backlit LCD display; User programmable scroll list and menus

### Environmental specifications

Operating temperature	-40°C to +85°C (-40°F to +185°F)
Operating humidity	0-95% RH, non-condensing
Enclosure rating	NEMA 4X/IP67
Certifications	CSA/C-US Class I, Div 1, Groups B, C, D; ambient temperature range of -40°C to +85°C (-40°F to +185°F), temperature code T6 (-40°C to 75°C) T5 (-40°C to 85°C) EN 61326-1: 2013 (Industrial Criteria); FCC 47 CFR Part 15, Subpart B; ICES 003: 2016

### Natural gas calculations

Supercompressibility	(Fpv) AGA 8 Gross-1992; AGA 8 Detail-1992; AGA 8 Short-1988; NX-19; NX-19 Analysis; GERG
Differential meters	(DP, Orifice) AGA 3/ANSI/API 2530-1992 Method 2; AGA 3/ANSI/API 2530-1985; ISO 5167; Cone meters; Annubar; GOST
Linear meters	(Turbine) AGA 7; AGA 9; AGA 11
Energy	AGA 5; GPA 2172; ISO 6976
Diagnostic	AGA 10 SoS
Additional factors/equations	Fwv (manual, partial or full); Fws; Nist 14
Turbine meter linearization	10 Point Frequency/K-factor Table

### Liquid calculations

API tables	Table A (generalized crude oils); Table B (generalized products); Table C (thermal expansion properties); Old Table (NGL, range 0.425 to 0.650); Table 23/24 E (NGL, LPG); VCF (CH 11.1 2004); Propylene (CH 11.3.3.2); Ethylene (API 2565/CH 11.3.2.1);
LPG SG	Ethylene (NBS 1045)
Volume correction factor (VCF)	Consistent with API 2540/ASTM D1250-80/IP 200; 5/6 A/B; 23/24 A/B; 53/54 A/B; 6/24/54 C; CH 11.1 2004; Note: natural gas liquids (NGL) and liquefied petroleum gases (LPG); OLD 23/24, OLD 53/54; Table E is new replace OLD 23/24.
standard to	Ch 11.2.1/Ch 11.2.2; Ch 11.2.1M/Ch 11.2.2M (compressibility factors for hydrocarbons), equilibrium pressure
Correction for effect of pressure on liquid	API Ch 11.3.3.2
Propylene density	API 2565 (Ch 11.3.2.1); Ethylene NBS 1045
Ethylene density	Thermo Scientific Sarasota liquid density meter, Solartron, UGC, 4-20 mA
Live density input	

### Differential Pressure

400"/1500 psia

400"/4500 psig

Extended DP Range

Upper Range Limit (URL)	400" H <sub>2</sub> O	400" H <sub>2</sub> O
Turndown Ratio	400:1	400:1
Min/Max Span	1.0-400 H <sub>2</sub> O	1.0-400 H <sub>2</sub> O
Accuracy <sup>1</sup>	0.0525%	0.04%
Stability (%URL/Year)	.0625	.0625
Response Time	100ms	90ms

**COMING SOON**

### Static Pressure

400"/1500 psia

400"/4500 psig

Extended DP Range

Upper Range Limit (URL)	1500 psia	4500 psig
Turndown Ratio	15:1	75:1
Min/Max Span	100-1500 psia	60-4500 psig
Accuracy <sup>1</sup>	0.0550%	0.0375%
Stability (%URL/Year)	0.008	0.016
Response Time	100ms	90ms

**COMING SOON**

<sup>1</sup>Terminal based accuracy-Includes the combined effects for linearity, hysteresis and repeatability

#### USA

27 Forge Parkway  
Franklin, MA 02038  
Ph: (713) 272-0404  
Fax: (713) 272-2273  
orders.process.us@thermofisher.com

#### India

C/327, TTC Industrial Area  
MIDC Pawane  
New Mumbai 400 705, India  
Ph: +91 22 4157 8800  
india@thermofisher.com

#### China

8/F Bldg C of Global Trade Ctr,  
No.36, North 3rd Ring Road,  
Dong Cheng District  
Beijing, China 100013  
Ph: +86 10 84193588  
info.eid.china@thermofisher.com

#### Europe

Ion Path, Road Three,  
Winsford, Cheshire CW73GA UK  
Ph: +44 1606 548700  
Fax: +44 1606 548711  
sales.epm.uk@thermofisher.com

**ThermoFisher**  
SCIENTIFIC

Find out more at [thermofisher.com/autoxp](http://thermofisher.com/autoxp)