## **thermo**scientific

# Refining and petrochemical industry monitoring solutions

Faced with unprecedented demands to meet increasing customer process expectations, as well as clean air regulations while optimizing plant performance...you need a partner that understands the challenges you face and offers instrument and service solutions that work.



#### Refining

- Fuel Products Analysis
- Stack Gas / Emissions Monitoring
- Process Gas Analysis
- Particulate Measurement
- Flow Measurement and Control
- Leak Detection
- Field Service & Application Expertise



#### **Petrochemical manufacturing**

- Liquid & Gas Flow Measurement
- Field Service & Application Expertise

#### **Common applications**

- Opacity Monitoring
- Gas Analysis for Reaction Kinetics/Catalytic Cracking
- Sulfur Recovery Units
- Total Sulfur Analysis
- Flare Gas Monitoring
- Fence Line Ambient Air Quality Monitoring
- Fugitive Emissions Detection (EPA Method 21)
- SO<sub>2</sub>, NO<sub>3</sub>, CO & Acid Measurement
- Olefins (Ethylene) & Poly Olefins (PE, PP)
- Ethylene Oxide (EO/EG)
- Fuel Gas Processing
- Ammonia & Methanol Measurement
- Fischer Tropsch (gas-to-liquid)
- Coal Gasification/Coal Chemical
- Catalyst Cracking & Research
- Process Development & Catalyst Research
- Distillation Units
- Chemical Rearrangement Units
- Alkylation
- Continuous Platformers
- Purification Units
- Knock Out Drum Pump Out Vessels
- High Density Polyethylene Loop Reactor
- And many more!



## Additional Thermo Scientific Solutions

Sulfur Analyzers

X-Ray Fluorescence

Electron & Infrared Microscopes

Gas Chromatographs for Hydrocarbons

Laboratory Equipment & Consumables

Lab Information

Management System (LIMS)

Unity Lab Services™

Furniture and Fume Hoods

Water Analyzer, Monitors & Sensors

Handheld X-Ray Fluorescense



## **thermo**scientific

## Thermo Scientific<sup>™</sup> product solutions



Thermo Scientific Prima BT Analyzer

Thermo Scientific Prima PRO Process Analyzer

## Process monitoring Density Measurement

 Sarasota Series of Gas Density Gauges

#### **Mass Spectrometry**

- Sentinel PRO Environmental Analyzer
- Prima PRO Process Analyzer

#### Flow Measurement and Control

- AutoPILOT PRO
- AutoEXEC
- AutoXP

#### **Systems**

#### **Total Sulfur**

- SOLA iQ Sulfur On-line Analyzer
- SOLA iQ Trace Sulfur On-line Analyzer
- SOLA iQ Flare Sulfur On-line Analyzer

#### Continuous Emissions Monitoring Systems (CEMS)

- Dilution CEMS
- Extractive CEMS
- Particulate Matter CEMS



#### Service and support

#### On-Site

- Preventive Maintenance
- Emergency Repair
- Startup and Recommissioning

#### **Technical Training Courses**

- Factory Training Centers
- Customer Site
- E-learning

#### In the Factory

- Depot Repair Service
- Factory Acceptance Testing (FAT)
- Extended Warranty
- Calibration and Certification



Thermo Scientific SOLA iQ Sulfur On-line Analyzer

## Gas & Particulate Analyzers

Nitrogen Oxide (NO<sub>x</sub>) 42iQ Gas Analyzers

Sulfur Dioxide (SO<sub>2</sub>) 43iQ Gas Analyzers

Carbon Monoxide (CO) 48iQ Gas Analyzers

Carbon Dioxide (CO<sub>2</sub>)

410iQ Gas Analyzers

Hydrogen Sulfide/ Sulfur Dioxide Analyzer (H<sub>2</sub>S/SO<sub>2</sub>) 450iQ Gas Analyzers

**Total Hydrocarbon** 51i Gas Analyzer

Methane (NMHC)

55i Gas Analyzer

Toxic Vapor Leak Detection TVA2020 Toxic Vapor Analyzer MIC-6 (Multi-Instrument Calibrator)

Continuous Ambient Particulate 5014i Beta Monitor

Thermo Scientific TVA2020 Toxic Vapor Analyzer

#### USA

27 Forge Parkway Franklin, MA 02038 Ph: (866) 282-0430 Fax: (508) 520-2800 orders.aqi@thermofisher.com

#### India

C/327, TTC Industrial Area MIDC Pawane New Mumbai 400 705, India Ph: +91 22 4157 8800 india@thermofisher.com

#### China

8/F Bldg C of Global Trade Ctr, No.36, North 3rd Ring Road, Dong Cheng District Beijing, China 100013 Ph: +86 10 84193588 info.eid.china@thermofisher.com

#### Europe

Ion Path, Road Three, Winsford, Cheshire CW73GA UK Ph: +44 1606 548700 Fax: +44 1606 548711 sales.epm.uk@thermofisher.com



#### Find out more at thermofisher.com