




**1** Donor provides urine specimen in cup. If desired, cap can be held by operator to initiate the test at a later time.




**2** Once urine sample has been collected, screw cap **firmly** until you heard a click.




**3** Check urine temperature at 2-4 minutes by reading green color on temperature indicator strip.




**4** Donor dates and initials security seal. Operator checks cap for tightness and attaches security seal label over cap as shown (Optional).




**5** Remove peel-off label.



**6** Read adulteration strip pads between 2 minutes, if applicable.



**7** Read test results at 5 minutes. Refer to diagram below for result interpretation.



C T or C T  
NEGATIVE POSITIVE INVALID

	Normal	Abnormal
OXI	Negative	
SG	1,205 1,015 1,035	1,000 +1,035
pH	4.0 6.0 7.0 8.0	2.0 3.0 6.0 12.0
NIT	20mg/dL Negative	10mg/dL 100mg/dL
GLUT	Negative	
CREA	100mg/dL 20mg/dL	0mg/dL 10mg/dL

**8** Positive test results must be confirmed by another test method. Send cup and urine specimen with security seal label intact to a toxicology laboratory for confirmation.

